





PRODUCT NO.
10126115-XYHLF

LEAD FREE OPTION
NOTE 6, 7, 8

NO. OF POSITIONS
SEE TABLE
PIN PLATING
BASE P/N



mat'l. code		surface	tolerance	projection	product family	
ISO 1302		ISO 1302	ISO 406	ISO 1101	HEADER	
l	tr	ec	n	dr	date	tolerances unless otherwise specified
A	NEW	ZK	06/14/13	angles	linear	XXX±.01/XXX±0.3
				0°±2'		XXX±.005/XXX±0.13
						XXX±.002/XXX±0.06
				dr	ZK HU	06/14/13
				engr	ZK HU	06/14/13
				chr	RICK BIAN	06/14/13
				appd	RICK BIAN	06/14/13
sheet	revision	A	A			
index	sheet	1	2			

title	FRICION LATCH HEADER DOUBLE ROW, R/A	
dwg no	10126115	sheet 1 of 2
type	Product Customer Drawing	



FCIconnect.com

Copyright FCI

PRODUCT NUMBER	NO OF POS	MATING LENGTH DIM H	OVERALL LENGTH DIM K	DIM L	TAIL LENGTH DIM "M"
10126115-X06	2 X 3	.230/5.84	.300/7.62	.200/5.08	.120/3.05
↑ -X08	2 X 4	.230/5.84	.400/10.16	.300/7.62	↑
-X10	2 X 5	.230/5.84	.500/12.70	.400/10.16	
-X12	2 X 6	.230/5.84	.600/15.24	.500/12.70	
-X14	2 X 7	.230/5.84	.700/17.78	.600/15.24	
-X16	2 X 8	.230/5.84	.800/20.32	.700/17.78	
-X18	2 X 9	.230/5.84	.900/22.86	.800/20.32	
-X20	2 X 10	.230/5.84	1.000/25.40	.900/22.86	
-X22	2 X 11	.230/5.84	1.100/27.94	1.000/25.40	
-X24	2 X 12	.230/5.84	1.200/30.48	1.100/27.94	
-X26	2 X 13	.230/5.84	1.300/33.02	1.200/30.48	
↓ -X28	2 X 14	.230/5.84	1.400/35.56	1.300/33.02	↓
10126115-X30	2 X 15	.230/5.84	1.500/38.10	1.400/35.56	.120/3.05

PIN PLATING CODES

-1YY	30u"/.76u Au MIN. ON 50u"/1.27u Ni
-2YY	15u"/.38u Au MIN. ON 50u"/1.27u Ni

NOTES:

1. MOLDING MAT'L: GLASS REINFORCED PCT OR MINERAL FILLED LCP, COLOR: BLACK
FLAME RETARDANT PER UL 94 V-0
MAXIMUM OPERATING TEMPERATURE: 130° C.

2. PIN MATERIAL: 3/4 HD PHOS. BRZ.

③. NO SLOTS ON 2 X 5 POSITION OR SMALLER PRODUCT. THE CENTER KEY SLOT WILL BE ON ALL HEADERS REGARDLESS OF SIZE.

④. TWO NON-CRITICAL SIDES OF PIN TIP NOT PLATED, BOTH ENDS.


⑤. COMPANY LOGO MAY APPEAR IN THIS AREA.

⑥. ADD "HLF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.

⑦. PART NUMBERS WITH "H" SUFFIX WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 20 SECONDS IN WAVE SOLDER, INFRA-RED OR VAPOR PHASE SOLDER PROCESS.

PART NUMBERS WITHOUT "H" SUFFIX WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR WAVE SOLDER PROCESS.

⑧. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.



mat'l. code		surface	tolerance	projection	product family	
		ISO 1302 ✓	ISO 406 ISO 1101	ISO 1101	HEADER	
l	tr	ec	n	d	r	e
date		tolerances unless otherwise specified		title		
A				linear	FRICION LATCH HEADER	
				angles	DOUBLE ROW, R/A	
				0°±2'	scale 3:1	
				dr	ZK HU 06/14/13	
				engr	ZK HU 06/14/13	
				chr	RICK BIAN 06/14/13	
				appd	RICK BIAN 06/14/13	
sheet	revision				dwg no	
index	sheet				10126115	
					type Product Customer Drawing	
					sheet 2 of 2	
					size A3	