







LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	00		H1	REVISED PER ECR-12-011660	24JAN2013	KH	TM



1. PARTS COMPLY TO AMP SOLDERABILITY SPECIFICATION 109-11-3.
2. CONTACT IS PLATED OVERALL WITH 0.00127 [0.000050] NICKEL, THEN STRIPED WITH 0.00076 [0.000030] GOLD IN CONTACT AREA AND TIN-LEAD ON SOLDER TAIL END.
3. CIRCUIT IDENTIFICATION CHARACTERS ARE ADJACENT TO THE INDICATED CAVITIES, BUT LOCATION AND ORIENTATION MAY DIFFER FROM PRINT.
4. CONTACT IS PLATED OVERALL WITH 0.00127 [0.000050] NICKEL, THEN 0.00076 [0.000030] GOLDOVER CONTACT LENGTH INDICATED AND MATTE TIN ON SOLDER TAIL END.
5. SUPERSEDED BY 643424-3



SCALE 4:1

4	PHOSPOR BRONZE, GOLD	NYLON, UL94V-0	643424-3
5	PHOSPOR BRONZE, GOLD	NYLON, UL94V-0	643424-2
	PHOSPOR BRONZE, PRE-TIN	NYLON, UL94V-0	643424-1
	CONTACT	HOUSING	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER CHK S. RIDGILL APVD S. RIDGILL	13OCT2005 13OCT2005 13OCT2005	 TE Connectivity			
DIMENSIONS: mm[INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
		0 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±0°30'		SOCKET HEADER ASSEMBLY, POLARIZED, 6 CIRCUIT, UNIVERSAL MATE-N-LOK(TM)			
MATERIAL SEE TABLE		FINISH SEE TABLE					
						SIZE CAGE CODE DRAWING NO RESTRICTED TO	
						A100779C643424-	
				CUSTOMER DRAWING			
				SCALE 5:1 SHEET 1 OF 1 REV H1			

