







**Retaining Rings****Wave Springs****Hose Clamps****Installation Tools****Materials****Packaging****Finishes****Quality****Online Services****About Retaining Rings****Literature Downloads****Part Interchange****Terms & Conditions****Military Rings****Environmental****Small Qty. Orders****Help Center****News****Newsletter****Part Number:****Housing or Shaft:****Axial/Radial/SelfLocking:****Housing/Shaft Dia. (Dh/Ds):****Ring Weight (lbs per 1,000):****Ring Thickness Tol.:****Ring Thickness (T):****Ring Gap (A):****Hardness Ranges (ST):****Hardness Ranges (SS):****Hardness Ranges (BC):****Clearance Diameter (L2):****Clear Outside Dia. (G):****DE-3.2****Shaft****radial****(0.157 - 0.197) (3.99 mm - 5.00 mm)****0.194 (0.09 Kg)****0.001 (0.02 mm)****0.024 (0.61 mm)****0.106 (2.69 mm)****Scale: 30N / Rockwell: 65-72****Scale: 30N / Rockwell: 63-69.5****Scale: 30N / Rockwell: 56.5-62****0.298 (7.57 mm)****0.272 (6.91 mm)**

[\[Ring Data\]](#) [\[Performance Specs\]](#) [\[Tool Specs\]](#) [\[Shipping Info\]](#) [\[All Specs\]](#)

[\[Printable Version\]](#)

[\[Show Series\]](#) [\[Request Quote\]](#) [\[Request Samples\]](#)

Designation: DE - DIN 6799, Type: External (shafts & pins) - DIN Metric, Size Range: 0.8mm to 30mm, Description: External E ring manufactured to DIN standard. The three prongs make contact with the bottom of the groove and provide a shoulder for effective retention of assemblies.

International**Product Search****Enter Size**

Shaft or Housing

Shaft = External
Housing = Internal

Choose Type

[\[Advanced Search\]](#)

[\[Search by Part\]](#)

Part Notes: *SHARP CORNER ABUTMENT. ALL DIMENSIONS IN MILLIMETERS. The radius "R" on the load side must not exceed 0.1T. *** FOR PLATED RINGS, ADD 0.05 TO THE LISTED MAXIMUM THICKNESS. MAXIMUM RING THICKNESS WILL BE A MINIMUM OF 0.005 LESS THAN THE LISTED GROOVE WIDTH (W) MINIMUM.

[Home](#) | [Contact Us](#) | [Customer Links](#) | [About Us](#) | [Holidays](#) | [Directions](#) | [Facilities](#)

Rotor Clip Company, Inc. Copyright © 2009
Toll Free: 1-800-557-6867 • Phone: +1-732-469-7333 • Fax: +1-732-469-7898
All Rights Reserved