

# MIP5530MD

## Silicon MOS FET type integrated circuit

### ■ Features

- Possible to correspond to the output about 30 W by the world wide input.  
(with heat sink)
- Typical LED peak current : 1.5 A
- With built-in LED short-circuit protection function.
- Input voltage detecting function is used, and the protection at a low input voltage is possible.
- Possible to correspond to the PWM dimming method and the triac light dimmer.
- Over temperature protection for IPD (Auto-restart)

### ■ Applications

- LED-lighting
- HB-LED drive circuit

### ■ Package

- Code  
TO-220IPD7-A2
- Pin Name
 

1. VIN	5. VDD
2. EX	6. —
3. CL	7. DRAIN
4. SOURCE	


### ■ Marking Symbol: MIP553MD

### ■ Absolute Maximum Ratings $T_a = 25^{\circ}\text{C} \pm 3^{\circ}\text{C}$

Parameter	Symbol	Rating	Unit
DRAIN voltage	VD-S	-0.3 to +700	V
VIN voltage	VIN-S	-0.3 to +440	V
VDD voltage	VDD-S	-0.3 to +8.0	V
EX voltage	VEX-S	-0.3 to +7.2	V
CL voltage	VCL-S	-0.3 to +7.2	V
Peak drain current *	IDP	3.5	A
Channel temperature	Tch	150	°C
Storage temperature	Tstg	-55 to +150	°C

Note) \*: IDP is guaranteed at the pulse width narrower than MIN(PW).

### ■ Block Diagram



■ Electrical Characteristics  $T_a = 25^\circ\text{C} \pm 3^\circ\text{C}$ 

Parameter	Symbol	Conditions	Min	Typ	Max	Unit
Control functions						
Constant OFF time	Toff	VDD = VDD(ON) + 0.1 V, VD = 5 V, VIN = 50 V, IEX = 0 $\mu\text{A}$ , ICL = ICLmax + 50 $\mu\text{A}$	14.4	16	17.6	$\mu\text{s}$
Skip mode constant OFF time	Toff_skip		$3.75 \times \text{Toff}$	$5.0 \times \text{Toff}$	$6.25 \times \text{Toff}$	$\mu\text{s}$
Maximum ON time	MAXon		69.6	80	90.4	$\mu\text{s}$
VDD start voltage	VDD(ON)	VD = 5 V, VIN = 50 V, IEX = 0 $\mu\text{A}$ , ICL = ICLmax + 50 $\mu\text{A}$	6.00	6.50	7.00	V
VDD stop voltage	VDD(UV)		5.00	5.50	6.00	V
Circuit current before start	IS1	VDD = VDD(ON) - 0.2 V, VD = 5 V, VIN = 50 V, IEX = 0 $\mu\text{A}$ , ICL = ICLmax + 50 $\mu\text{A}$	0.61	1.02	1.43	$\mu\text{A}$
Circuit current under switching	IS2	VDD = VDD(ON) + 0.1 V, VD = 5 V, VIN = 50 V, IEX = 0 $\mu\text{A}$ , ICL = ICLmax + 50 $\mu\text{A}$	0.62	1.03	1.44	$\mu\text{A}$
EX pin current for setting ILIMITmin *	IEXH	VDD = VDD(ON) + 0.1 V, ICL = ICLmax + 50 $\mu\text{A}$ , VIN = 50 V, ILIMIT = ILIMITmin *Fig. 2		260		$\mu\text{A}$
EX pin current at oscillation stop	IEXoff	VDD = VDD(ON) + 0.1 V, ICL = ICLmax + 50 $\mu\text{A}$ , VIN = 50 V *Fig. 2	300	420	560	$\mu\text{A}$
EX pin current hysteresis at oscillation restart	IEXhys			50		$\mu\text{A}$
EX pin voltage	VEXM	VDD = VDD(ON) + 0.1 V, ICL = ICLmax + 50 $\mu\text{A}$ , IEX = 150 $\mu\text{A}$ , VIN = 50 V	1.94	2.55	3.16	V
	VEXH	VDD = VDD(ON) + 0.1 V, ICL = ICLmax + 50 $\mu\text{A}$ , IEX = IEXH, VIN = 50 V	2.08	2.75	3.42	V
	VEXoff	VDD = VDD(ON) + 0.1 V, ICL = ICLmax + 50 $\mu\text{A}$ , IEX = IEXoff, VIN = 50 V	2.43	3.20	3.97	V
EX pin short current	IEXSVDD	VDD = VDD(ON) + 0.1 V, ICL = ICLmax + 50 $\mu\text{A}$ , VEX = VDD, VIN = 50 V	0.52	0.95	1.38	mA
	IEX0	VDD = VDD(ON) + 0.1 V, ICL = ICLmax + 50 $\mu\text{A}$ , VEX = 0 V, VIN = 50 V		0		$\mu\text{A}$
CL pin current for setting ILIMITmax	ICLmax	VDD = VDD(ON) + 0.1 V, IEX = 0 $\mu\text{A}$ , VIN = 50 V, ILIMIT = ILIMITmax *Fig. 3	264	300	336	$\mu\text{A}$
CL Pin Voltage	VCLmax	VDD = VDD(ON) + 0.1 V, IEX = 0 $\mu\text{A}$ , VIN = 50 V, ICL = ICLmax	2.20	2.90	3.60	V
CL pin short current	ICLSVDD	VDD = VDD(ON) + 0.1 V, IEX = 0 $\mu\text{A}$ , VIN = 50 V, VCL = VDD	0.72	1.3	1.89	mA
	ICL0	VDD = VDD(ON) + 0.1 V, IEX = 0 $\mu\text{A}$ , VIN = 50 V, VCL = 0 V		0		$\mu\text{A}$

Note) \*: Design guaranteed item


■ Electrical Characteristics (continued)  $T_a = 25^\circ\text{C} \pm 3^\circ\text{C}$

Parameter	Symbol	Conditions	Min	Typ	Max	Unit
Circuit protections						
Maximum peak current LIMIT	ILIMITmax	VDD = VDD(ON) + 0.1 V, ICL = ICLmax + 50 $\mu\text{A}$ , VIN = 50 V, IEX = 0 $\mu\text{A}$ *Fig. 1, 2, 3	1.395	1.50	1.605	A
ILIMIT ICL100 *	ILIMITCLL	VDD = VDD(ON) + 0.1 V, IEX = 0 $\mu\text{A}$ , VIN = 50 V, ICL = 100 $\mu\text{A}$ *Fig. 1, 3		0.57		A
ILIMIT IEX150	ILIMITexm	VDD = VDD(ON) + 0.1 V, ICL = ICLmax + 50 $\mu\text{A}$ , VIN = 50 V, IEX = 150 $\mu\text{A}$ *Fig. 1, 2	0.69	0.75	0.81	A
Minimum clamp ILIMIT	ILIMITmin	VDD = VDD(ON) + 0.1 V, ICL = ICLmax + 50 $\mu\text{A}$ , VIN = 50 V, IEX = IEXH + 20 $\mu\text{A}$ *Fig. 1, 2	0.10	0.20	0.35	A
Leading edge blanking delay *	$t_{\text{on(BLK)}}$	VDD = VDD(ON) + 0.1 V, ICL = ICLmax + 50 $\mu\text{A}$ , VIN = 50 V, IEX = 0 $\mu\text{A}$	150	200	250	ns
Peak current limit delay *	$t_{\text{d(OC)}}$			200		ns
Minimum on-pulse width	MIN(PW)	VIN = 50 V, VD = 35 V, IEX = 0 $\mu\text{A}$ ,		410	570	ns
Skip detect on-pulse width *	Skip(PW)	ICL = ICLmax + 50 $\mu\text{A}$		MIN(PW) +100		ns
Thermal shutdown junction temperature *	TOTPJ		130	140	150	$^\circ\text{C}$
Thermal shutdown hysteresis *	TOTPJ(hys)			70		$^\circ\text{C}$
Output						
ON-state resistance	RDS(ON)	VDD = VDD(ON) + 0.1 V, ICL = ICLmax + 50 $\mu\text{A}$ , VIN = 50 V, IEX = 0 $\mu\text{A}$ , IDS = 300 mA		3.5	4.25	$\Omega$
OFF-state leakage current of DRAIN pin	IDSS	VDD = VDD(ON) + 0.1 V, IEX = IEXoff + 20 $\mu\text{A}$ , VD = 630 V		1.0	10	$\mu\text{A}$
Breakdown voltage of DRAIN pin	VDSS	VDD = VDD(ON) + 0.1 V, IEX = IEXoff + 20 $\mu\text{A}$ , ID = 100 $\mu\text{A}$	700			V
Rise time	$t_r$	VDD = VDD(ON) + 0.1 V, ICL = ICLmax + 50 $\mu\text{A}$ , VIN = 50 V, IEX = 0 $\mu\text{A}$ , VD = 5 V *Fig. 4		90		ns
Fall time	$t_f$			30		ns
High Voltage Input						
OFF-state leakage current of VIN pin	IIN(LEAK)	VDD = VDD(ON) + 0.1 V, IEX = IEXoff + 20 $\mu\text{A}$ , VIN = 400 V		26	50	$\mu\text{A}$
Breakdown voltage of VIN pin	BVVIN	VDD = VDD(ON) + 0.1 V, IEX = IEXoff + 20 $\mu\text{A}$ , IIN = 100 $\mu\text{A}$ ,	440			V
VDD charging current	CHRG10	VIN = 40 V, VDD = 0 V, EX, CL: open	-14.6	-10.0	-5.4	mA
	CHRG15	VIN = 40 V, VDD = 5 V, EX, CL: open	-9.8	-6.5	-3.3	mA
VIN start voltage	VINuv	VDD: open, VD = 5 V, IEX = 0 $\mu\text{A}$ ,	17	23	33	V
VIN start voltage hysteresis	VINhys	ICL = ICLmax + 50 $\mu\text{A}$ ,		4.0		V


Note) \*: Design guaranteed item

■ Electrical Characteristics (continued)  $T_a = 25^{\circ}\text{C} \pm 3^{\circ}\text{C}$

1. Measurement circuit




2. Figure.1 ILIMIT measurement





\*The load condition of ILIMIT measurement is  $L = 100 \mu\text{H}$ ,  $R_d = 130 \Omega$

Figure2 IEX-ILIMIT characteristic



## ■ Electrical Characteristics (continued) $T_a = 25^\circ\text{C} \pm 3^\circ\text{C}$

Figure. 3 ICL-ILIMIT characteristic

Figure. 4  $t_r$ ,  $t_f$  characteristic

## ■ Usage Notes

Connect a ceramic capacitor with value  $>1.0 \mu\text{F}$  between VDD pin and GND.

The IPD has risks for break-down or burst or giving off smoke in following conditions. Avoid the following use.

Fuse should be added at the input side or connect zener diode between control pin and GND, etc as a countermeasure to pass regulatory Safety Standard. Concrete countermeasure could be provided individually. However, customer should make the final judgment.

- (1) DRAIN pin short to low voltage pin (VDD, EX, CL).
- (2) VIN pin short to low voltage pin (VDD, EX, CL).
- (3) VIN pin short to DRAIN pin under switching.
- (4) DRAIN pin short to SOURCE pin.

## Request for your special attention and precautions in using the technical information and semiconductors described in this book

- (1) If any of the products or technical information described in this book is to be exported or provided to non-residents, the laws and regulations of the exporting country, especially, those with regard to security export control, must be observed.
- (2) The technical information described in this book is intended only to show the main characteristics and application circuit examples of the products. No license is granted in and to any intellectual property right or other right owned by Panasonic Corporation or any other company. Therefore, no responsibility is assumed by our company as to the infringement upon any such right owned by any other company which may arise as a result of the use of technical information described in this book.
- (3) The products described in this book are intended to be used for general applications (such as office equipment, communications equipment, measuring instruments and household appliances), or for specific applications as expressly stated in this book.  
Consult our sales staff in advance for information on the following applications:
  - Special applications (such as for airplanes, aerospace, automotive equipment, traffic signaling equipment, combustion equipment, life support systems and safety devices) in which exceptional quality and reliability are required, or if the failure or malfunction of the products may directly jeopardize life or harm the human body.
 It is to be understood that our company shall not be held responsible for any damage incurred as a result of or in connection with your using the products described in this book for any special application, unless our company agrees to your using the products in this book for any special application.
- (4) The products and product specifications described in this book are subject to change without notice for modification and/or improvement. At the final stage of your design, purchasing, or use of the products, therefore, ask for the most up-to-date Product Standards in advance to make sure that the latest specifications satisfy your requirements.
- (5) When designing your equipment, comply with the range of absolute maximum rating and the guaranteed operating conditions (operating power supply voltage and operating environment etc.). Especially, please be careful not to exceed the range of absolute maximum rating on the transient state, such as power-on, power-off and mode-switching. Otherwise, we will not be liable for any defect which may arise later in your equipment.  
Even when the products are used within the guaranteed values, take into the consideration of incidence of break down and failure mode, possible to occur to semiconductor products. Measures on the systems such as redundant design, arresting the spread of fire or preventing glitch are recommended in order to prevent physical injury, fire, social damages, for example, by using the products.
- (6) Comply with the instructions for use in order to prevent breakdown and characteristics change due to external factors (ESD, EOS, thermal stress and mechanical stress) at the time of handling, mounting or at customer's process. When using products for which damp-proof packing is required, satisfy the conditions, such as shelf life and the elapsed time since first opening the packages.
- (7) This book may be not reprinted or reproduced whether wholly or partially, without the prior written permission of our company.

## Precautions on the Sales of IPDs

- 1) The sale and/or the export of IPD products to customers located in certain countries is restricted by the Agreement made and executed by and between Power Integrations, Inc. and Panasonic Corporation. For details, refer to the following Attached table "IPD availability by customer."
- 2) IPD products purchased from our company, or its authorized agents, hereinafter referred to as our company, shall be used only for production purposes by those parties who have duly purchased IPD products. Those who have purchased IPD products shall not use such IPD products in unmodified form for re-sale, loan, or sample shipment for evaluation purposes to any other parties.
- 3) If a party who has duly purchased IPD products subcontracts its production to any other parties, including its subsidiaries or any other third parties inside and/or out of Japan, and the IPD products are consigned to such subcontracting parties thereat, such party is obligated to monitor and control the quantity of IPD products to prevent any of the aforementioned re-sale, loan or sample shipments from taking place.
- 4) In the event that any actual or threatened breach or violation of any of the above mentioned 2) or 3) has occurred or is about to occur, our company will hold all shipments of IPD products and may request the customer to disclose necessary documentation describing the status of our end-users and/or distribution channels.

Note) The products of MIP50\*\*, MIP51\*\*, and MIP7\*\* are excluded from above-mentioned precautions, 1) to 3).

Attached table "IPD availability by customer"

Parts No.			Companies/areas to which products can be sold	Companies/areas to which products cannot be sold	Application
MIP01** MIP2** MIP9A**	MIP02** MIP3** MIP9L**	MIP1** MIP4**	<ul style="list-style-type: none"> <li>• Japanese companies in Japan</li> <li>• Japanese companies in Asia (50% or more owned)</li> </ul>	<ul style="list-style-type: none"> <li>• Companies in European and American countries</li> <li>• Asian companies in Asia</li> <li>• Other local companies</li> </ul>	<ul style="list-style-type: none"> <li>• For power supply</li> <li>• For DC-DC converter</li> </ul>
MIP00** MIP55** MIP816/826	MIP52** MIP56** MIP9E**	MIP53** MIP803/804	<ul style="list-style-type: none"> <li>• Japanese companies in Japan</li> <li>• Japanese companies in Asia (50% or more owned)</li> <li>• Asian companies in Asia</li> </ul>	<ul style="list-style-type: none"> <li>• Companies in European and American countries</li> <li>• Other local companies</li> </ul>	<ul style="list-style-type: none"> <li>• For power supply</li> <li>• For EL driver</li> <li>• For LED lighting driver</li> </ul>
MIP50**	MIP51**	MIP7**	<ul style="list-style-type: none"> <li>• No restrictions in terms of contract</li> </ul>	<ul style="list-style-type: none"> <li>• No restrictions in terms of contract</li> </ul>	<ul style="list-style-type: none"> <li>• For lamp driver/ car electronics accessories</li> </ul>

Note) For details, contact our sales division.