


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS				DOC. NO. SPC-F005	Effective: 12/21/98				DCP No. 880
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE	
170	A	RELEASED	HYO	1/21/00	JJC	2/16/00	DJC	2/24/00	

Specifications:

1. Color: Black
2. Insulator: Polyacetal
3. Jack Body: Brass, nickel plated
4. Nut: Brass, nickel plated
5. Voltage: 500V
6. Current: 36A max.
7. Temperature: -20°C to +80°C



DISCLAIMER
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.



Tolerances Unless Otherwise Specified				DRAWING TITLE:			
Fractions ± 1/32	DRAWN BY:	DATE:		4mm Insulated Jack, Solder			
Decimals	HISHAM ODISH	1/21/00					
.XX ± .01	CHECKED BY:	DATE:					
.XXX ± .005	JOHN COLE	2/16/00					
	APPROVED BY:	DATE:					
	DANIEL CAREY	2/24/00					