


2SA1795

(TE5T4)

-5A PNP

OUTLINE DIMENSIONS



RATINGS

●Absolute Maximum Ratings


Item	Symbol	Conditions	Ratings	Unit
Storage Temperature	T _{stg}		-55~150	℃
Junction Temperature	T _j		150	℃
Collector to Base Voltage	V _{CBO}		-60	V
Collector to Emitter Voltage	V _{CEO}		-40	V
Emitter to Base Voltage	V _{EBO}		-7	V
Collector Current DC	I _C		-5	A
Collector Current Peak	I _{CP}		-10	A
Base Current DC	I _B		-1.5	A
Base Current Peak	I _{BP}		-2	A
Total Transistor Dissipation	P _T	T _c = 25℃	10	W

●Electrical Characteristics (T_c=25℃)


Item	Symbol	Conditions	Ratings	Unit
Collector to Emitter Sustaining Voltage	V _{CEO(sus)}	I _C = -0.05A	Min -40	V
Collector Cutoff Current	I _{CBO}	At rated Voltage	Max -0.1	mA
	I _{CEO}		Max -0.1	
Emitter Cutoff Current	I _{EBO}	At rated Voltage	Max -0.1	mA
DC Current Gain	h _{FE}	V _{CE} = -2V, I _C = -2.5A	Min 70	
Collector to Emitter Saturation Voltage	V _{CE(sat)}	I _C = -2.5A	Max -0.3	V
Base to Emitter Saturation Voltage	V _{BE(sat)}	I _B = -0.13A	Max -1.2	V
Thermal Resistance	θ _{jc}	Junction to case	Max 12.5	℃/W
Transition Frequency	f _T	V _{CE} = -10V, I _C = -0.5A	TYP 50	MHz
Turn on Time	ton	I _C = -2.5A I _{B1} = -0.25A, I _{B2} = -0.25A R _L = 12 Ω, V _{BB2} = -4V	Max 0.3	μ s
Storage Time	ts		Max 1.5	
Fall Time	tf		Max 0.5	

2SA1795

$h_{FE} - I_C$




2SA1795 Saturation Voltage




2SA1795

Switching Time - I_C




2SA1795

Switching Time - T_c




2SA1795 Transient Thermal Impedance



2SA1795

Forward Bias SOA



2SA1795 Collector Current Derating

