






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	L1	REVISED PER ECO-15-010630	27JUL2015	NK	MZ
	M	REVISED PER ECO-17-000037	15MAR2017	RS	MZ



RECOMMENDED PANEL CUTOUT

DETAIL A



DETAIL B

- 1 CAVITY IDENTIFICATION ON FRONT AND REAR FACE.
- 2 WILL ACCEPT THIRTY-SEVEN (37) MULTIMATE SOCKET CONTACTS.
- 3 NO 4 FASTENER RECOMMENDED FOR MOUNTING.
- 4 NYLON 6/6, NATURAL.
- 5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

OBSOLETE 5	STANDARD	NO	3.81 [.150] DIA HOLE	A	4 206306-8
	SMALL PACK	NO	3.81 [.150] DIA HOLE	A	206306-6
	STANDARD	NO	4-40 THREADED INSERT	A	206306-5
	STANDARD	YES	-	B	206306-4
	STANDARD	YES	3.81 [.150] DIA HOLE	A	206306-3
	STANDARD	NO	-	B	206306-2
	STANDARD	NO	3.81 [.150] DIA HOLE	A	206306-1
	PACKAGING	PERIPHERAL SEAL	C	SEE DETAIL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN D.GELTZ 07/26/93	 TE Connectivity				
DIMENSIONS: MM [INCHES]			CHK R.STONE 08/11/93					
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD A.FRANTUM 08/13/93	NAME RECEPTACLE HOUSING, REVERSE SEX, SHELL SIZE 23, CPC	SIZE CAGE CODE DRAWING NO RESTRICTED TO			
	1 P/LC	±	PRODUCT SPEC					
	2 P/LC	±	108-10024					
	3 P/LC	± 0.15 [.005]	APPLICATION SPEC					
	4 P/LC	±						
FINISH		±	WEIGHT	A1 00779 C=206306				
MATERIAL HOUSING: NYLON, BLACK INSERT: BRASS		-	0.000000	CUSTOMER DRAWING				
			SCALE	2:1	SHEET	1 OF 1	REV	M