

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

19195-1031

Status:

Active

Overview:

MagKrimp™ Connectors, Terminals and Splices

Description:

MagKrimp™ Round Ring with Ribbed Barrel, Stud Size 3/8" (M9), 165,000-230,000 Circular Mil Area, Plated

Documents:

Drawing (PDF)

Product Specification PS-19195-001 (PDF)

Product Specification PS-19902-011 (PDF)

Product Specification PS-19902-013 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E32244

General

Product Family

Series

Comments

Crimp Quality Equipment

Mil-Spec

Overview

Product Name

Type

UPC

Ring and Spade Terminals

19195

Ribbed Barrel for Reinforcement

Yes

N/A

MagKrimp™ Connectors, Terminals and Splices

MagKrimp™(Magnet Wire)

Ring

756054492529

Physical

Barrel Type

Insulation

Material - Plating Mating

Net Weight

Packaging Type

Plating min - Mating

Plating min - Termination

Stud Size

Temperature Range - Operating

Termination Interface: Style

Wire Size AWG

Open

None

Tin

57.008/g

Bag

2.540µm

2.540µm

3/8" (M9)

-40°C to +100°C

Crimp or Compression

N/A

Electrical

Voltage - Maximum

2000V

Material Info

Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-19195-001, PS-19902-011, PS-19902-013

SD-19195-005




image - Reference only

Series

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

19195Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
MagKrimp™ Tooling Kit - Round Dies, CMA Varies	0190780135

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION