

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20






BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED	14MAR'07	SC	JK
	B	REVISED PER ECR-09-011788	25MAY'09	SC	JK
	C	REVISED PER ECR-19-009721	01JUL2019	M.G	D.Z

- 1 THIS HOUSING ACCEPTS TAB TERMINAL:
-TAB CONTACT: 177917- (AWG#16-#20)
177916- (AWG#22-#26)
- 2 MATING CONN. P/N
-PLUG HSG: 368576- (AWG#16-#20)
177914- (AWG#22-#26)
- 3 APPLICABLE DOUBLE LOCK PLATE: 177919-1
* IT SHOULD BE USED CERTAINLY WHEN CABLE ASS'Y
- 4 GENERAL TOLERANCES: ±0.3
- 5 APPLICABLE PANEL THICKNESS: 0.8~2.0 (SEE FIG.1)
- 6 INSERT CONN. FROM PRESS DIRECTION SIDE FOR METAL PANEL.
- 7 EDGE OF THICKNESS MAY MUST DOT ROUND FOR MOLDED PANEL.
- 8 MATERIAL: PA66,UL94V-0
COMPLY WITH GLOW WIRE REQUIREMENT FOR PARTS OF
NON-METALLIC MATERIAL SUPPORTING A CURRENT-CARRYING
CONNECTION DETAILED IN IEC 60335-1, SECTION 30(GWT)



BLUE	368588-6
YELLOW	368588-4
NATURAL	368588-1
COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SC KIM	TE TE Connectivity			
DIMENSIONS: mm		CHK BW KANG				
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		APVD JK SONG				
MATERIAL 8		PRODUCT SPEC 108-5410				
		APPLICATION SPEC 114-5175	NAME PDL 6P CAP HSG 3.96mm D/R P/M (GWT)			
		WEIGHT -	SIZE A3	CAGE CODE 00779	DRAWING NO C-368588	RESTRICTED TO
		CUSTOMER DRAWING	SCALE 3:1	SHEET 1 OF 1	REV C	