

Duplex Multimode 62.5/125 Fiber Patch Cable (MTRJ/SC), 5M (16-ft.)

MODEL NUMBER: N310-05M



Highlights

- Premium PVC 62.5/125µm multimode patch cables
- Attenuation loss meets or exceeds the latest industry standards

System Requirements

- Any fiber optic hardware or NIC card requiring Multimode Duplex cable with MT-RJ/SC connectors

Package Includes

- 5-meter Duplex MMF Cable MTRJ/SC 62.5/125 Fiber

Description

Tripp Lite's 5-meter multimode duplex fiber optic MTRJ/SC patch cable is manufactured from 62.5/125 zipcord fiber. The cable has MTRJ to SC connectors, a PVC jacket and is FDDI and OFNR rated. Duplex multimode fiber is most commonly used in LAN applications.

Features

- Manufactured from 62.5/125 duplex (zipcord) fiber
- PVC jacket
- Length: 5-meters (16.4ft) Connectors: MTRJ to 2 SC
- Insertion loss testing performed on every connector (0.2db typical) and provided with cable
- Beveled edge on ends of glass makes insertion of plug a breeze
- Fiber made from glass (not a polymer)
- Color coded shrouds identify transmit and receive
- Duplex multimode fiber is most commonly used in LAN applications where links are typically 10 feet or less
- Fiber optic distributed data interface (FDDI) rated
- OFNR (riser rated)

Specifications

OVERVIEW	
Intended Application	Computer Networking (Fiber)
Network Speed	1Gbps
Style	Fiber Optic
Fiber Type	62.5/125 - OM1



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Model Type	MTRJ/SC
Cable Types	MULTIMODE 62.5/125 FIBER OPTIC
INPUT	
Cable Length (ft.)	16
Cable Length (m)	5
UPC ASSIGNMENT	
Unit Carton UPC#	037332123671
PHYSICAL	
Color	Orange
CONNECTIONS	
Connector A	MTRJ
Connector B	SC
Number of Connectors	3
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.