

PRODUCT NB	DIM"C"	DIM"D"	CAP	TAPE	TUBE	AVAILABILITY
95290-YXXLF	SEE SHEET 213 2/2		NO	NO	YES	SEE SHEET 213 2/2
95290-YXXALF			YES	YES	NO	SEE SHEET 213 2/2
95290-YXXBLF			YES	NO	YES	SEE SHEET 213 2/2
95290-YXXKLF			NO	YES	NO	SEE SHEET 213 2/2

PRODUCT NUMBER



95290-YXXZLF

PLATING CODE
SEE TABLE

RoHS COMPATIBLE, SEE NOTE 7 SHEET 2

OPTION LETTER (SEE TABLE & SHEET 2)

NUMBER OF POSITIONS, SHEET 2



NOTES:

- 1 - MATERIAL HOUSING: PCT HIGH TEMPERATURE, 30% GLASS FILLED COLOUR GREY, FLAME RETARDANT, PER UL-94-V0.
- 2 - MATERIAL TERMINAL: PHOSPHOR BRONZE EXTRA HARD

95290-4XX(Z)LF	5µm Sn	Sn
95290-3XX(Z)LF	0.76µm GOLD	Sn
PLATING CODE	CONTACT AREA	SOLDER TAIL
	PLATING THICKNESS OVER 1.27µm Ni	

mat'l. code SEE NOTES				surface ISO 1302	tolerance ISO 406 ISO 1101	projection mm	product family DX VCC DR
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm	title
R	B-19923	BVE	15.01.08	angles	linear		BtB RECEPT.
K	F07-027	LMU	07.12.06	±2°		scale 1/5	VERT DR SMT 8.5 mm
L	F09-0230	JCO	09.12.09	dr	D.LEGRAND	97.01.13	dwg no
M	B-19123	LMU	14.10.21	enr	P.NIZZI	97.01.13	sheet 1 of 2
N	B-19232	LMU	14.10.28	chr	D.LEGRAND	97.01.13	size
P	B-19535	BVE	14.11.24	appd	PNZ	97.01.13	95290
sheet index				revision	R	J	A3
sheet				1	2		type
							CUSTOMER
							Drawing

PRODUCT NUMBER	NUMBER OF POS.	DIM"C"	DIM"D"
95290-Y03(Z)LF	2 x 03	5.08	7.54
95290-Y04(Z)LF	2 x 04	7.62	10.08
95290-Y05(Z)LF	2 x 05	10.16	12.62
95290-Y06(Z)LF	2 x 06	12.70	15.16
95290-Y22(B)LF	2 x 22	53.34	55.80

- 6 - OTHERS POSITIONS, ON SPECIAL REQUEST.
7 - RoHS COMPATIBLE PRODUCT SPECIFICATIONS

a - PLATING:

- "LF" MEANS THE PRODUCT IS LEAD-FREE,
2µm MINIMUM MATTE TIN OVER 1.27µm
MINIMUM NICKEL UNDERPLATE.

b - MANUFACTURING PROCESS COMPATIBILITY

- THE HOUSING WILL WITHSTAND EXPOSURE TO
260°C PEAK TEMPERATURE FOR 30 SECONDS
MAX IN A CONVECTION, INFRA-RED OR VAPOR
PHASE OR REFLOW OVEN.

c - LABELING:

- MEETS PACKAGING SPECS AS PER GS-14-920

d - LEGAL STATEMENT: SEE GS-47-0004

mat'l. code SEE NOTES				surface ISO 1302 ☒ ISO 406 ISO 1101		tolerance ISO 406 ISO 1101		projection 		product family DX VCC DR				
ltr	ecn no	dr	date	tolerances unless otherwise specified						title				
E	F04-037	DLE	04.11.16	angles	linear	±x				BtB RECEPT. VERT DR SMT 8.5 mm				
F	F06-0204	DLE	06.06.28	linear	±xx	scale 1/5								
G	B-19123	LMU	14.10.21	0°±x'	±xxx									
H	B-19535	BVE	14.11.24	dr	D.LEGRAND	97.01.13				dwg no				
J	B-19923	BVE	15.01.08	enrg	P.NIZZI	97.01.13				sheet 2 of 2				
				chr	P.NIZZI	97.01.13				size A3				
				appd	P. NZ	97.01.13				type CUSTOMER Drawing				
sheet index		revision sheet												