

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By -

ALL RIGHTS RESERVED.


LOC
FT

DIST
0

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	J2	REVISED PER ECO-11-005027	12MAR11	RK	HMR

31.12±0.38 DIA
[1.225±.015]



SOCKET HOUSING

COUPLING RING
(-1 AND -2 ONLY)

RETAINER RING
(-1 AND -2 ONLY)

PLUG SHELL

SEAL
SEE TABLE

22.22 MAX DIA
[.875]

35.56 MAX
[1.400]

7/8-20 UNEF-2A

NOTES:

1. THIS CONNECTOR ACCEPTS FIVE (5) SIZE 16 MULTIMATE SOCKET CONTACTS, MAXIMUM WIRE INSULATION DIA = 3.43[.135].

2. THIS CONNECTOR MATES WITH AMP P/N 208719-1.

3. AMP P/N AND DATE CODE TO BE LOCATED ON COUPLING RING.


4 NICKEL PER QQ-N-290 OVER COPPER PER MIL-C-14550.

5 ZINC PER QQ-Z-363.

6 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES



MATERIAL
SKT HOUSING: THERMOPLASTIC, BLACK
SEAL: FLUROCARBON, ELASTOMER
RTNR RING: STAINLESS STEEL
CPLG RING: 6 PLUG SHELL: 6

FINISH
CPLG RING: 6
PLUG SHELL: 6

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

DWN
D.HARDY
05/23/94

CHK
R.STONE
05/26/94

APVD
-

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

PLUG ASSEMBLY, STANDARD SEX,
SERIES 1, 14-5, CMC

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-208718

RESTRICTED TO
-

SCALE
2:1

SHEET
1 OF 1

REV
J2

1470-19 (3/11)