

Distributed by:




JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242


The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 1962869

LOC	DIST	REVISIONS				
GP	00	P	LTR	DESCRIPTION	DATE	DWN
			B	REVISED PER ECO-08-008111	30JUN2008	ZMRCWR



SECTION X-X
INSULATION BARREL



SECTION Y-Y
WIRE BARREL

- 1

FOR MINI APPLICATOR.
- 2

FOR HAND TOOL USE ONLY.
3.

WIRE RANGE OF 22-28, INSULATION RANGE OF .030-.040.
- 4

.000050 MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.
.000100 MIN TIN ON WIRE AND INSULATION BARRELS. .000030 MIN GOLD ON LOCALIZED GOLD PLATE AREA.
OR
.000050 MIN NICKEL UNDERPLATE ON ENTIRE CONTACT,
.000100 MIN TIN ON WIRE AND INSULATION BARRELS, GOLD FLASH OVER PALLADIUM-NICKEL, .000030 MIN TOTAL ON LOCALIZED GOLD PLATE AREA.
- 5

PLATED WITH GOLD FLASH IN LOCALIZED GOLD PLATE AREA, .000100 MIN. TIN ON WIRE BARRELS, OVER .000050 MIN. NICKEL UNDERPLATE.

5	1658686-4	1658686-3
4	1658686-2	1658686-1
FINISH	LOOSE PIECE 2	PART NUMBER 1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. BAUM 02JAN04	Tyco Electronics Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: INCHES		CHK S. BOLASH 02JAN04				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD M. WALMSLEY 02JAN04	NAME SOCKET CONTACT,22-28 AWG,22 DF,AMPLIMITE			
	0 PLC ± -	PRODUCT SPEC 108-1268	-			
	1 PLC ± -	APPLICATION SPEC 114-10001	-			
MATERIAL PHOS BRONZE		WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C-1658686	RESTRICTED TO -
SEE TABLE		CUSTOMER DRAWING		SCALE 10:1	SHEET 1 OF 1	REV B