

Customer Information Sheet

DRAWING No.: M80-4C1XXXXSI, M80-4C1XXXXSI-00-000-00-000

SHT 2 OF 2

IF IN DOUBT - ASK

(C)

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm

SPECIFICATIONS:

MATERIAL:

MOULDING = GLASS-FILLED PPS, UL94V-0, BLACK
CONTACT CLIP = BERYLLIUM COPPER
CONTACT SHELL = BRASS
BACKSHELL = ALUMINIUM ALLOY
BANDIT TIE & J/SCREW = STAINLESS STEEL

FINISH:

CONTACTS
05 = 0.3µ GOLD CLIP, 0.25-0.3µ GOLD SHELL
42 = 0.3µ GOLD CLIP, 3.5-5.0µ 100% TIN SHELL
OVER NICKEL

BACKSHELL = NICKEL

ELECTRICAL:

RF ATTENUATION = 10kHz TO 400MHz @ >30dBs
IN GENERAL ACCORDANCE WITH MIL STD 1377 (1971)
CURRENT RATING AT 25°C = 3.0A MAX
CURRENT RATING AT 85°C = 2.2A MAX
WORKING VOLTAGE = 120V AC/DC
VOLTAGE PROOF = 360V AC/DC
CONTACT RESISTANCE = 25 mΩ MAX
INSULATION RESISTANCE = 100 MΩ MIN

MECHANICAL:

INSERTION FORCE (Ø0.5mm GAUGE) = 2.8N MAX
WITHDRAWAL FORCE (Ø0.5mm GAUGE) = 0.2N MIN
ENVIRONMENTAL:
TEMPERATURE RANGE = -55°C TO +121°C

PACKING:

SEE NOTES

FOR COMPLETE SPECIFICATION, SEE COMPONENT
SPECIFICATION C005XX (LATEST ISSUE) AND C042XX
(LATEST ISSUE)

NOTES:

- CONNECTOR IS SUPPLIED AS A KIT OF PARTS IN A BAG.
BAGS WILL BE BULK PACKED INTO BOXES.
- FOR EXTRA CONTACTS, USE PART No.'s.
M80-0130001 FOR M80-4C1XX42SI-00-000-00-000
M80-0130005 FOR M80-4C1XX05SI-00-000-00-000
- FOR M80-4C1XXXXSI-00-000-00-000 THE RECOMMENDED
WIRE TYPE = BS 3G 210 TYPE A, PTFE INSULATED
24-28 AWG. MAX INSULATION DIAMETER = Ø1.10mm,
STRIP WIRE BY 2.00mm.
- RECOMMENDED HAND CRIMP TOOL FOR ALL CONTACTS =
M22520/2-01 WITH POSITIONER T5747.
- CONTACT INSERTION & EXTRACTION TOOL = Z80-280.
- TO APPLY CIRCLIPS USE HARWIN TOOL = Z80-300.
- SEE TOOLING INSTRUCTION SHEET IS-32 FOR ASSEMBLY
DETAILS AVAILABLE AT:
<http://www.harwin.com/downloads/instructions/>
- ALL PART LABELLING TO BE AS ORDER CODE, EITHER
WITH TRAILING ZEROS OR LEFT BLANK AS PER ORDER
CODE EXAMPLES 1 AND 2.
- 1 BANDIT TIE SUPPLIED PER KIT

ORDER CODE:

M80-4C1XXXXSI-XX-XXX-XX-XXX

TOTAL No. OF CONTACTS
06, 10, 14, 20, 26

FINISH CODE

05 - GOLD CLIP, GOLD SHELL
42 - GOLD CLIP, 100% TIN OVER NICKEL SHELL

NUMBER OF SPECIAL CONTACTS




X's CAN BE DISPLAYED AS TRAILING ZEROS OR LEFT BLANK
SEE EXAMPLE ORDER CODES FOR EXPLANATION.

EXAMPLE ORDER CODE 1: CONNECTOR WITH 20 SMALL BORE
SIGNAL CONTACTS, GOLD CLIP AND GOLD SHELL


M80-4C12005SI-00-000-00-000

EXAMPLE ORDER CODE 2: CONNECTOR WITH 20 LARGE BORE
SIGNAL CONTACTS, GOLD CLIP AND 100% TIN SHELL

M80-4C12042SI



1 x METAL BACKSHELL
SUPPLIED LOOSE IN BAG



CONTACTS:
FOR M80-4C1 = M80-01300XX (QTY = TOTAL No. OF CONTACTS)
05 = FINISH CODE '05'
01 = FINISH CODE '42'

4 x CIRCLIP (2-OFF REQUIRED)
SUPPLIED LOOSE IN BAG
SEE NOTE 6

2 x M2 SLOTTED JACKSCREWS
SUPPLIED LOOSE IN BAG

SF	2	21.09.10	10944
NAME	ISS.	DATE	C/NOTE
APPROVED:	SF		
CHECKED:	RA		
DRAWN:	S.FLOWER		
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN

HARWIN USA TEL: 603 893 5376 FAX: 603 893 5396 mis@harwin.com	HARWIN Europe (UK) TEL: 023 9231 4545 FAX: 023 9231 4590 mis@harwin.co.uk	HARWIN Asia TEL: +65 6 779 4909 FAX: +65 6 779 3868 mis@harwin.com.sg
--	--	--

THIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.

TOLERANCES
X. = ±1mm
X.X = ±0.25mm
X.XX = ±0.10mm
X.XXX = ±0.01mm
ANGLES = ±5°
UNLESS STATED

MATERIAL:

SEE ABOVE

FINISH: SEE ABOVE

S/AREA:

TITLE: DATAMATE J-TEK
FEMALE CRIMP (SMALL BORE) ASSY
WITH METAL BACKSHELL

DRAWING NUMBER: **M80-4C1XXXXSI,
M80-4C1XXXXSI-00-000-00-000**

SHT
2 OF 2