




- 1 PARTS COMPLY TO AMP SOLDERABILITY SPECIFICATION 109-11-3.
- 2 CONTACT IS PLATED OVERALL WITH 0.00127[.000050] NICKEL, THEN 0.00076 [.000030] GOLD OVER CONTACT LENGTH INDICATED AND MATTE TIN LEAD ON SOLDER TAIL END.
- 3 CIRCUIT IDENTIFICATION CHARACTERS ARE ADJACENT TO THE INDICATED CAVITIES, BUT LOCATION AND ORIENTATION MAY DIFFER FROM PRINT.
- 4 DIMENSIONS IN BRACKETS ARE IN INCHES.
- 5 CONTACT IS PLATED OVERALL WITH 0.00127[.000050] NICKEL, THEN 0.00076 [.000030] GOLD OVER CONTACT LENGTH INDICATED AND MATTE TIN ON SOLDER TAIL END.
- 6 SUPERSEDED BY 641963-3

PHOSPHOR BRONZE, GOLD		NYLON,UL94V-2,NATURAL	641963-3
PHOSPHOR BRONZE, GOLD		NYLON,UL94V-2,NATURAL	641963-2
PHOSPHOR BRONZE, PRE-TIN		NYLON,UL94V-2,NATURAL	641963-1
PIN CONTACT MATERIAL AND FINISH		HOUSING MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. McEACHIN CHK K. COBLE APVD K. COBLE	07-JAN-2000 07-JUN-2000 07-JUN-2000	TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		0 PLC	± -	PRODUCT SPEC	
		1 PLC	± -	APPLICATION SPEC	
		2 PLC	± 0.13 [.005]		
		3 PLC	± -	SIZE	
MATERIAL SEE TABLE		4 PLC	± -	CAGE CODE	
		ANGLES	± 0°30'	DRAWING NO	
		FINISH	SEE TABLE	RESTRICTED TO	
		WEIGHT	-	A100779	
		CUSTOMER DRAWING		SCALE 5:1	
				SHEET 1 OF 1	
				REV K1	