



- 250 Vrms Isolation
- 100 mA Rated Current

Electrical Parameters @ 25°C


Inductance (mH $\pm$ 25%) @ 10 KHz, 0.1 Vrms	DCR (Ω Typ.)	Turns Ratio	SRF (MHz Typ.)
1.3	3.4	1:1	1.8
Pins 1-2, 4-3	Pins 1-2, 4-3	1-2:4-3	

Impedance Graph

Schematic



Package



Unless Otherwise Specified Dimensions are in Inches /mm $\pm$.010 / .25