

Surface Mount Bi-Directional Coupler

High Power, 50Ω

600 to 1100 MHz

NEW!

BDCA1-6-11




Maximum Ratings

Operating Temperature	-55°C to 100°C
Storage Temperature	-55°C to 100°C

Pin Connections

INPUT	1
OUTPUT	6
COUPLED (forward)	10
COUPLED (reverse)	5
GROUND	2,3,4,7,8,9

Outline Drawing




SUGGESTED LAYOUT FOR PCB LAND PATTERN

Outline Dimensions (inch/mm)

A	B	C	D	E	F	G	H
.30	.250	.045	.274	.050	.050	.024	.057
7.62	6.35	1.14	6.96	1.27	1.27	0.61	1.45
J	K	L	M	wt.			
.004	.085	.296	.030	grams			
0.10	2.16	7.52	0.76	0.25			

Demo Board MCL P/N: TB-115

Suggested PCB Layout (PL-004)



NOTE: TRACE WIDTH IS SHOWN FOR ROGERS RO4350 WITH DIELECTRIC THICKNESS 0.020" ± 0.0015". COPPER: 1/2 OZ. EACH SIDE. FOR OTHER MATERIALS TRACE WIDTH MAY NEED TO BE MODIFIED.


■ DENOTES PCB COPPER LAYOUT
■ DENOTES COPPER LAND PATTERN FREE OF SOLDER MASK

Features

- wideband, 600-1100 MHz
- excellent VSWR 1.1:1 typ. all ports
- solder plated leads
- excellent power handling capability, 42W (1 GHz)
- low temperature variation

Applications

- cellular
- CDMA
- ISM



BLUE CELL™

CASE STYLE: DZ944

PRICE: \$3.95 ea. QTY (10-49)

Bi-Directional Electrical Specifications





FREQ. RANGE (MHz)	COUPLING (dB)		MAINLINE LOSS** (dB)		DIRECTIVITY (dB)		VSWR (:1)	POWER INPUT* (W)
	Nom.	Max. Flatness	Typ.	Max.	Typ.	Min.		
600-1100								
600-700	6.3±0.5	±0.5	1.5	1.8	23	20	1.05	50
700-1000	6.0±0.4	±0.3	1.8	2.0	27	19	1.08	42
1000-1100	6.3±0.5	±0.5	1.8	2.0	21	15	1.10	38

* Derate linearly 1/3 at 100°C

** Includes theoretical coupled power loss of 1.25 dB at 6 dB coupling.

Typical Performance Data

Frequency (MHz)	Insertion Loss (dB) In-Out	Coupling (dB)		Directivity (dB)		Return Loss (dB)			
		In-CPL	Out-Term	Out-CPL	In-Term	In	Out	CPL	Term
600.00	1.48	6.66	6.66	22.85	23.34	33.43	33.64	37.94	35.02
700.00	1.65	6.16	6.16	25.61	26.35	40.51	41.11	45.74	43.29
800.00	1.77	5.94	5.95	28.77	29.60	37.91	37.28	31.81	35.75
900.00	1.83	5.95	5.93	28.02	27.46	29.51	29.10	25.64	28.92
1000.00	1.80	6.19	6.16	23.19	22.37	24.39	24.03	21.71	24.44
1100.00	1.70	6.64	6.63	18.67	17.98	20.63	20.33	18.77	21.12



Mini-Circuits®

Distribution Centers NORTH AMERICA 800-654-7949 • 417-335-5935 • Fax 417-335-5945 • EUROPE 44-1252-832600 • Fax 44-1252-837010

ISO 9001 CERTIFIED

INTERNET <http://www.minicircuits.com>

P.O. Box 350166, Brooklyn, New York 11235-0003 (718) 934-4500 Fax (718) 332-4661

REV. OR
M87149
ED-10880/1
BDCA1-6-11
LC/TD/CP
030528