



LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			G	REVISED PER ECO-14-000068	23APR2014	NK	MM

- 1 ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS.
- 2 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING
- 3 POINT OF MEASUREMENT FOR PLATING THICKNESS
- 4 BREAKAWAY NOTCH ANGLE CAN BE ORIENTED TO THE RIGHT (AS SHOWN) OR TO THE LEFT
- 5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED HOLE LAYOUT

			3.984	3.900	39	40	4-103148-0
	OBSOLETE		3.884	3.800	38	39	-3-103148-9
			3.784	3.700	37	38	-3-103148-8
			3.684	3.600	36	37	-3-103148-7
5	SUPERSEDED BY 8-146304-6		3.584	3.500	35	36	-3-103148-6
	OBSOLETE		3.484	3.400	34	35	-3-103148-5
			3.384	3.300	33	34	-3-103148-4
			3.284	3.200	32	33	-3-103148-3
			3.184	3.100	31	32	-3-103148-2
			3.084	3.000	30	31	-3-103148-1
			2.984	2.900	29	30	-3-103148-0
			2.884	2.800	28	29	-2-103148-9
			2.784	2.700	27	28	-2-103148-8
		2.684	2.600	26	27	-2-103148-7	
		2.584	2.500	25	26	-2-103148-6	
5	SUPERSEDED BY 7-146304-5		2.484	2.400	24	25	-2-103148-5
	OBSOLETE		2.384	2.300	23	24	-2-103148-4
			2.284	2.200	22	23	-2-103148-3
			2.184	2.100	21	22	-2-103148-2
			2.084	2.000	20	21	-2-103148-1
			1.984	1.900	19	20	-2-103148-0
			1.884	1.800	18	19	-1-103148-9
			1.784	1.700	17	18	-1-103148-8
			1.684	1.600	16	17	-1-103148-7
		1.584	1.500	15	16	1-103148-6	
	OBSOLETE		1.484	1.400	14	15	-1-103148-5
			1.384	1.300	13	14	-1-103148-4
			1.284	1.200	12	13	-1-103148-3
5	SUPERSEDED BY 6-146304-2		1.184	1.100	11	12	-1-103148-2
	OBSOLETE		1.084	1.000	10	11	-1-103148-1
			.984	.900	9	10	-1-103148-0
5	SUPERSEDED BY 5-146304-9		.884	.800	8	9	-103148-9
		.784	.700	7	8	103148-8	
	OBSOLETE		.684	.600	6	7	-103148-7
			.584	.500	5	6	103148-6
		.484	.400	4	5	103148-5	
	OBSOLETE		.384	.300	3	4	-103148-4
			.284	.200	2	3	103148-3
		.184	.100	1	2	103148-2	
	OBSOLETE	.084	—	—	1	-103148-1	
			C	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG H MOLL		230CT87		 TE Connectivity	
		CHK T. CLARK		230CT87			
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD T. CLARK		NAME	
		0 PLC ± -		PRODUCT SPEC		HEADER ASSY, MOD II, BREAKAWAY, SINGLE ROW, .100CL, RIGHT ANGLE, WITH .025 SQ POSTS	
		1 PLC ± -		—			
		2 PLC ± -		—			
		3 PLC ± .005		APPLICATION SPEC		SIZE	
		4 PLC ± -		—		CAGE CODE	
ANGLES ± -		FINISH : POSTS		WEIGHT		DRAWING NO	
MATERIAL		.000030 GOLD ON CONTACT AREA,		—		A2 00779	
HOUSING: FLAME RETARDANT		.000100—.000200 MATTE TIN—LEAD				C=103148	
THERMOPLASTIC:		ON SOLDER TAIL, ALL OVER				SCALE	
COLOR—BLACK		.000050 NICKEL		CUSTOMER DRAWING		SHEET	
POSTS: COPPER ALLOY						4:1	
						1 OF 1	
						REV	
						G	