




+ TERMINALS & SPLICES

CRIMP WIRE PINS, TABS & FERRULES



✓ Active

TE CONNECTIVITY (TE)

B-106-8401CS100

Raychem | TERMINAL , Terminator

CC2632-000

TE Internal Number: CC2632-000

Alias ID: B-106-8401CS100

Not Yet Reviewed for EU RoHS

Not Yet Reviewed for EU ELV

Terminal Type Bullet Receptacle

Wire Insulation Diameter (Max) 4.3 mm [.169 in]

Wire Insulation Diameter 1.4 – 4 mm [.06 – .157 in]

Heavy Duty No

Wire Size (AWG) 22 – 18

**PRODUCT DRAWING**

English

**DOCUMENTATION**

Product Drawings

**Duraseal Bullet Receptacle**

PDF

English

Catalog Pages/Data Sheets

**1654025\_Sec8\_B-106**

PDF

English

Product Specifications

Product Specification

**Installation Procedure For Duraseal Splices And Terminals**

PDF

English

## FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

### Product Type Features

**Barrel Type** Closed Barrel

**Insulated** Yes

**Support Style** Insulation Support

### Body Features

**Plating Material** Copper Alloy, Tin

**Insulation Material** Heat Shrinkable Nylon

**Double Wire** No

**Insulation Sleeve Material** Polyamide

### Contact Features

**Terminal Type** Bullet Receptacle

### Termination Features

**Bullet Terminal** With

**Bullet Diameter** 4 mm [.157 in]

### Dimensions

**Wire Insulation Diameter (Max)** 4.3 mm [.169 in]

**Wire Insulation Diameter** 1.4 – 4 mm [.06 – .157 in]

**Wire Size (AWG)** 22 – 18

**Wire Size (mm<sup>2</sup>)** .3 – .9

**Wire Size (CMA)** 509 – 1900

**Barrel Inside Diameter** 4 mm [.16 in]

**Overall Length** 30 mm [1.18 in]

### Operation/Application

**Heavy Duty** No

### Packaging Features

**Packaging Method** Loose Piece

**Packaging Quantity** 100

### Other

**Barrel Color** Red

## PRODUCT COMPLIANCE



Statement of Compliance

**Statement of Compliance**

PDF

---