

3M™ Aluminum Foil Tape 300PL

Product Description

3M™ Aluminum Foil Tape 300PL is an aluminum foil tape with a high performance acrylic pressure sensitive adhesive on one side.

3M 300PL Tape is designed to be an economical aluminum foil tape that will provide good EMI shielding performance while also providing excellent environmental resistance, sealing capability and surface protection.

3M 300PL Tape uses a high performance acrylic adhesive that will provide excellent shear holding strength and environmental resistance.

Construction

Property	Value
Adhesive Type:	Acrylic Pressure Sensitive
Release Liner:	Silicone-treated Paper liner
Approximate Thickness:	
Aluminum	0.047 mm (1.9 mil)
Adhesive	0.043 mm (1.6 mil)
Liner(s)	0.070 mm (2.9 mil)



3M™ Aluminum Foil Tape 300PL

Typical Physical Properties and Performance Characteristics

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Adhesive Properties:

Peel Adhesion Testing

180° peel, Test Method: modified ASTM D-3330 (units: N/100mm width)

Substrates	Initial Peel	Peel After 15 minute Dwell
Steel	85	100
PC	83	91
ABS	63	76
PS	75	84

Static Shear Holding Test

Test Method: modified ASTM D-3654

Test Conditions	Test Results
1000g @ 25°C	Tape applied to test substrate held 1000g vertically for > 10,000 minutes.
1000g @ 25°C	Tape applied to test substrate held 1000g vertically for > 10,000 minutes.
Temperature Performance ¹	Application Use Temperature: -40° to 95°C. Temperature performance can vary with environmental conditions. ¹
Shelf Life and Store Conditions	Tape in roll form: Shelf life 24 months from the date of manufacture when stored in original cartons at 21°C (70°F) and 50% relative humidity.

Tensile and Elongation	Test Results
Tensile Strength	260 N/100mm width (ASTM D-3759)
Elongation @ Break	3% with 0.047mm backing thickness (ASTM D-3652)

¹Application Use Temperature range of the 3M™ Aluminum Foil Tape 300PL is dictated by two primary items: 1) temperature / environmental conditions, and 2) substrates applied to. These items affect both long term and short term performance:

Item 1 Temperature/Environmental:

Basic long term (months) continuous temperature performance of 3M™ Aluminum Foil Tape 300PL acrylic adhesive is generally -40°C to 95°C depending on other environmental conditions (exposure to reactive or corrosive fluids, duration of maximum temperature exposure and cycles, typical operation temperature, humidity levels, etc.).


Short term exposures (minutes-hours) from 150°C to 200°C or higher can be achieved depending on the performance attributes desired from 3M 300PL Tape and the duration of each exposures (plus cumulative exposure times).

Item 2 Substrates Applied to:

Substrates characteristics such as high or low surface energy material, vapor transmission through substrate surface, cleanliness of the surface, smoothness of the surface, etc. will affect 3M 300PL Tape adhesion performance.

3M™ Aluminum Foil Tape 300PL

EMI Shielding Performance



EMI Shielding performance can vary depending on several factors, including items such as test method, edge overlap of 3M™ Aluminum Foil Tape 300PL as it covers a gap or aperture opening, geometric shape, and application details of 3M 300PL Tape.

Available Sizes

Slit Tape Width	Standard Length	Maximum Length
110 mm or 1100 mm	200 m	TBS

Application Techniques

Bonding

- To obtain maximum adhesion, the bonding surfaces must be clean and dry.
- Pressure must be applied to the bond line after assembly to wet the substrates with the adhesive used with the 3M™ Aluminum Foil Tape 300PL. Mechanical pressure (roller, metal bar) or finger pressure at 15 psi (0.10 Mpa) or greater is suggested. Heat may be applied simultaneously to improve wetting and final bond strength.
- 3M 300PL Tape should be applied between 60°F - 158°F (15°C - 70°C). Tape application below 50°F (10°C) is not recommended because the adhesive will be too firm to wet the surface of the substrate, resulting in low adhesion.
- Adhesion builds with time, up to 24 to 72 hours may be required to reach final adhesion values.

3M™ Aluminum Foil Tape 300PL

General Information

3M™ Aluminum Foil Tape 300PL is part of a family of products useful for EMI shielding applications. Custom EMI shielding tapes can be made by combining 3M conductive PSAs to various substrates.

Conductive PSA Adhesion Product Selection Guide

3M™ Electrically Conductive Adhesive Transfer Tape	SS	Alum	Cloth				Gasket Attachment / Grounding	Attributes		
9712		X	X	X	X	X		Acrylic	Scrim	5.0 mil
9713	X	X	X	X	X	X		Acrylic	Scrim	3.0 mil
9719	X	X	X	X	X	X		Silicone	Scrim	4.0 mil
9708/9709	X	X	X	X	X	X		Acrylic	Particle	2.0 mil
9705	X	X	X		X	X		Acrylic	Particle	2.0 mil

Application Ideas

3M™ Aluminum Foil Tape 300PL is ideal for EMI/RFI shielding applications. The foil backing also provides an excellent reflective surface for both heat and light.

3M™ Aluminum Foil Tape 300PL

Certification/Recognition

MSDS: Refer to Product Label and Material Safety Data Sheet for Health and Safety Information before using this product. For additional health and safety information, call 1-800-364-3577 or (651) 737-6501.

TSCA: This product is defined as an article under the Toxic Substances Control Act and therefore, it is exempt from inventory listing requirements.

RoHs Complaint/REACH Compliant: This product complies with the European Union's "Restriction of Hazardous Substances" (RoHs) initiative and with European REACH regulations 2002/95/EC and 2005/618/EC.

For Additional Information

To request additional product information or to arrange for sales assistance, call toll free 1-800-251-8634. Address correspondence to: 3M, Electronics Markets Materials Division, 3M Center, Building 225-3S-06, St. Paul, MN 55144-1000. Our fax number is 651-778-4244 or 1-877-369-2923. In Canada, phone: 1-800-364-3577. In Puerto Rico, phone: 1-787-750-3000. In Mexico, phone: 52-70-04-00.

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture at the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**



Electronics Markets Materials Division

3M Center, Building 225-3S-06

St. Paul, MN 55144-1000

1-800-251-8634 phone

651-778-4244 fax

www.3M.com/electronics

3M is a trademark of 3M Company.

Please recycle. Printed in U.S.A.

©3M 2010. All rights reserved.

60-5002-0142-5

