



SECTION X-X



RECOMMENDED HOLE LAYOUT

- 1 TYCO LOGO AND CSA LOGO ARE MOLDED INTO HOUSING
- 2 TOLERANCE NON-CUMULATIVE.
- 3 DUPLEX PLATED: .000030 GOLD IN CONTACT AREA, .000150-.000300 BRIGHT TIN-LEAD ON SOLDER LEADS, ALL OVER .000050 MIN NICKEL.
- 4 THESE DIMENSIONS PERTAIN TO CAVITY CENTERLINES ONLY. NOT TO CONTACT LOCATIONS.
- 6. PACKAGED IN SINGLE TUBES.
- 7 HOUSING: FLAME RETARDANT GLASS FILLED POLYESTER COLOR-BLACK, CONTACT: PHOS. BRONZE
- 8 POINT OF CONTACT DIMENSION.
- 9 POINT OF MEASUREMENT DIMENSION FOR PLATING THICKNESS (INSIDE CONTACT BEAMS).
- 10 DATE CODE AND PART NUMBER ARE MARKED IN APPROXIMATE LOCATION SHOWN"
- 11 DUPLEX PLATED: .000030 GOLD IN CONTACT AREA, .000150-.000300 MATTE TIN ON SOLDER LEADS, ALL OVER .000050 MINIMUM NICKEL"
- 12 ROHS 2002/95/EC COMPLIANT
- 13 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

13	12	OBSOLETE	3.200	3.100	64	-5-147065-1
		3.200	3.100	64	147065-1	
		FINISH	A	B	NUMBER OF POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		09FEB98	Tyco Electronics		Tyco Electronics Corporation
DIMENSIONS:	INCHES	09FEB98	J.HERRINGTON	09FEB98	Harrisburg, Pa 17105-3608
0 PLC	± -	J.HERRINGTON	J.HERRINGTON	09FEB98	ASSEMBLY, MOD II DOUBLE ROW,
2 PLC	± -	APVD	APVD	APVD	.100 X .100
3 PLC	± -	J.HERRINGTON	J.HERRINGTON	J.HERRINGTON	CLOSED ENTRY, SHORT PT. CONTACTS
4 PLC	± -	PRODUCT SPEC	APPLICATION SPEC	APPLICATION SPEC	
INCHES	± -	—	—	—	
MATERIAL	7	FINISH	3.11A	3.11A	SIZE CAGE CODE DRAWING NO
WEIGHT	—	A1	00779	147065	RESTRICTED TO
CUSTOMER DRAWING		5:1	1	1	REV A1