


# Specification Sheet

CK-20



High-Performance Plastic Optical Fiber

E s k a™

MITSUBISHI RAYON CO.,LTD.

ESKA OPTICAL FIBER DIVISION

6-41 Konan 1-Chome,Minato-ku,Tokyo,JAPAN

Phone :+81-3-5495-3060

Facsimile:+81-3-5495-3212

## 1. Scope

The specification covers basic requirements for the structure and optical performances of CK-20.


## 2. Structure

Table 1

CK-20

| Item               |                          | Specification |                               |      |      |
|--------------------|--------------------------|---------------|-------------------------------|------|------|
|                    |                          | Unit          | Min.                          | Typ. | Max. |
| Optical Fiber 1    | Core Material            | —             | Polymethyl-Methacrylate Resin |      |      |
|                    | Cladding Material        | —             | Fluorinated Polymer           |      |      |
|                    | Core Refractive Index    | —             | 1.49                          |      |      |
|                    | Refractive Index Profile | —             | Step Index                    |      |      |
|                    | Numerical Aperture       | —             | 0.5                           |      |      |
|                    | Core Diameter            | μm            | 455                           | 485  | 515  |
|                    | Cladding Diameter        | μm            | 470                           | 500  | 530  |
| Approximate Weight |                          | g/m           | 0.24                          |      |      |

Sectional View



## 3. Performances

Table 2

CK-20

| Item                          |                          | Acceptance Criterion<br>and/or<br>[ Test Condition ]                       | Specification |      |      |      |
|-------------------------------|--------------------------|----------------------------------------------------------------------------|---------------|------|------|------|
|                               |                          |                                                                            | Unit          | Min. | Typ. | Max. |
| Maximum<br>Rating             | Storage<br>Temperature   | No Physical Deterioration<br>[ in a Dry Atmosphere ]                       | ℃             | − 55 | −    | +70  |
|                               | Operation<br>Temperature | No Deterioration<br>in Optical Properties*<br>[ in a Dry Atmosphere ]      | ℃             | − 55 | −    | +70  |
|                               |                          | No Deterioration<br>in Optical Properties**<br>[ under 95%RH condition ]   | ℃             | −    | −    | +60  |
| Optical<br>Properties         | Transmission Loss        | [ 650nm Collimated Light ]<br>[ Standard condition ]<br>[ 10m-1m cutback ] | dB/km         | −    | −    | 250  |
| Mechanical<br>Characteristics | Minimum<br>Bend Radius   | Loss Increment $\leq 0.5\text{dB}$<br>[ A Quarter Bend ]                   | mm            | 10   | −    | −    |
|                               | Tensile Strength         | Tensile Force at 5%<br>Elongation; in Conformity<br>to the JIS C 6861 ]    | N             | 14   | −    | −    |

All tests are carried out under temperature of 25℃ unless otherwise specified.

\* Attenuation change shall be within +/- 10% after 1,000 hours.

\*\* Attenuation change shall be within +/- 10% after 1,000 hours, except that due to absorbed water.