





LOC	DIST	REVISIONS				
		F	LTR	DESCRIPTION	DATE	DWN APVD
GP	00	L1		REVISED PER ECO-06-020813	25/OCT/06	ZR CR

D


C

B

A



- 1 MOLDED PARTS: POLYESTER, UL RATED 94V-0, BLACK.
- CONTACTS: BERYLLIUM COPPER.
- 2 2.54μm [.000100] MIN TIN-LEAD ON TERMINATION END, 0.76μm [.000030] MIN GOLD ON CONTACT AREA, ALL OVER 1.27μm [.000050] MIN NICKEL.
- 3 POSITION TOLERANCE APPLIES 0.76 [.030] ABOVE DATUM V.
- 4 POSITION NUMBER 1 INDICATOR.
- 5 ELECTRICAL ENGAGEMENT ZONE.
- 6 RECOMMENDED 28 AWG RIBBON CABLE, 0.61 - 0.97 [.024 - .038] THICK PVC, 1.0000[.03937] PITCH. AMP LOGO ORIENTATION IS OPTIONAL.
- 7 RECESS ON EACH END, OPPOSITE CORNER.
- 8 0.13μm [.000005] MIN GOLD ON TERMINATION END, 0.76μm [.000030] MIN GOLD ON CONTACT AREA, ALL OVER 1.27μm [.000050] MIN NICKEL.
- 9 MOLD GATE PROJECTION ON EITHER END OF COVER TO BE EXCLUDED FROM DIMENSION 'B' MEASUREMENT.



	9	1.0000 [.03937]	12.40 [.488]	17.15 [.675]	11	12	3-111623-1
	9	1.0000 [.03937]	8.41 [.331]	13.18 [.519]	7	8	3-111623-0
	9	0.0000 [.00000]	22.40 [.882]	27.18 [1.070]	21	22	2-111623-9
	9	0.0000 [.00000]	34.42 [1.355]	39.17 [1.542]	33	34	2-111623-8
	9	1.0000 [.03937]	24.41 [.961]	29.18 [1.149]	23	24	2-111623-7
	9	0.0000 [.00000]	50.39 [1.984]	55.17 [2.172]	49	50	2-111623-6
	9	1.0000 [.03937]	44.40 [1.748]	49.17 [1.936]	43	44	2-111623-5
	9	1.0000 [.03937]	40.41 [1.591]	45.19 [1.779]	39	40	2-111623-4
	9	0.0000 [.00000]	30.40 [1.197]	35.18 [1.385]	29	30	2-111623-3
	9	0.0000 [.00000]	26.42 [1.040]	31.17 [1.227]	25	26	2-111623-2
	9	1.0000 [.03937]	20.40 [.803]	25.17 [.991]	19	20	2-111623-1
	9	1.0000 [.03937]	16.41 [.646]	21.18 [.834]	15	16	2-111623-0
	9	0.0000 [.00000]	14.40 [.567]	19.18 [.755]	13	14	1-111623-9
	9	0.0000 [.00000]	10.41 [.410]	15.16 [.597]	9	10	1-111623-8
OBSOLETE	2	1.0000 [.03937]	12.40 [.488]	17.15 [.675]	11	12	1-111623-7
OBSOLETE	2	1.0000 [.03937]	8.41 [.331]	13.18 [.519]	7	8	1-111623-6
	2	0.0000 [.00000]	22.40 [.882]	27.18 [1.070]	21	22	1-111623-5
OBSOLETE	2	1.0000 [.03937]	68.40 [2.693]	73.18 [2.881]	67	68	1-111623-4
OBSOLETE	2	1.0000 [.03937]	64.41 [2.536]	69.16 [2.723]	63	64	1-111623-3
OBSOLETE	2	1.0000 [.03937]	60.40 [2.378]	65.18 [2.566]	59	60	1-111623-2
	2	0.0000 [.00000]	50.39 [1.984]	55.17 [2.172]	49	50	1-111623-1
	2	1.0000 [.03937]	44.40 [1.748]	49.17 [1.936]	43	44	1-111623-0
OBSOLETE	2	1.0000 [.03937]	40.41 [1.591]	45.19 [1.779]	39	40	111623-9
OBSOLETE	2	0.0000 [.00000]	34.42 [1.355]	39.17 [1.542]	33	34	111623-8
OBSOLETE	2	0.0000 [.00000]	30.40 [1.197]	35.18 [1.385]	29	30	111623-7
OBSOLETE	2	0.0000 [.00000]	26.42 [1.040]	31.17 [1.227]	25	26	111623-6
OBSOLETE	2	1.0000 [.03937]	24.41 [.961]	29.18 [1.149]	23	24	111623-5
OBSOLETE	2	1.0000 [.03937]	20.40 [.803]	25.17 [.991]	19	20	111623-4
	2	1.0000 [.03937]	16.41 [.646]	21.18 [.834]	15	16	111623-3
OBSOLETE	2	0.0000 [.00000]	14.40 [.567]	19.18 [.755]	13	14	111623-2
	2	0.0000 [.00000]	10.41 [.410]	15.16 [.597]	9	10	111623-1
CONTACT FINISH		D	C	B	A	NO OF POSN	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

FINISH CONTACTS: SEE TABLE

DWN C. OBERMAN 02-21-92

CHK J. MCCLINTON 3-9-92

APVD

PRODUCT SPEC 108-1372

APPLICATION SPEC

WEIGHT

SIZE A1

CAGE CODE 00779

DRAWING NO 111623

RECEPTACLE ASSY, POLARIZED, 2mm CL, AMP-LATCH

RESTRICTED TO

CUSTOMER DRAWING

SCALE 10:1

SHEET 1 OF 1

REV L1

Tyco Electronics Corporation

Harriaburg, PA 17105-3608