




HF
 Halogen Free


NOTES:

1. MATERIAL:
 - 1.1 HOUSING: HIGH TEMPERATURE THERMOPLASTIC, UL94V-0, COLOR: BLACK.
 - 1.2. CONTACT: COPPER ALLOY.
 - 1.3. SOLDER PEG: STAINLESS STEEL.
2. FINISH:
 - 2.1 CONTACT:
 - UNDERPLATING NICKEL 50u" MIN OVERALL
 - MATING AREA: GOLD PLATING, THICKNESS SEE TABLE
 - SOLDER AREA: GOLD FLASH 1u" MIN.
 - 2.2 SOLDER PEG:
 - UNDERPLATING NICKEL 50u" MIN OVERALL
 - 80u" MIN MATTE TIN ON SURFACE
3. DATE CODE : YYWWDLX
 - YY: YEAR (09: 2009)
 - WW: WEEK (25: THE 25TH WEEK)
 - D: DAY (1~7: SUNDAY~SATURDAY)
 - L: LINE NUMBER OF ASSEMBLY (A: LINE A)
 - X: D OR N (D: DAY; N: NIGHT)
4. PRODUCT SPECIFICATION SEE FCI GS-12-1195
5. PART NUMBER DESCRIPTION:
 - 10128788-00XRFL

LF: LEAD FREE & RoHS COMPLIANCE

PACKAGE CODE:





R: TAPE & REEL PACKING

PLATING CODE:

1: GOLD FLASH ON CONTACT AREA

4: 15u" Min GOLD ON CONTACT AREA

5: 30u" Min GOLD ON CONTACT AREA


 MATING SIMILAR
 SCALE: 2:1

mat'l. code				surface	tolerance	projection	product family
ltr	ecn no	dr	date	tolerances unless otherwise specified		mm	title
A		BF	2013-04-18	angles	.X ±0.3		
B	ELX-T-19318	TAI	2014-11-10	linear	.XX ±0.25	scale	M.2 CONNECTOR 3.2H_STD_KEY E
C	ELX-T-20858	TAI	2015-05-11	X*±2"	.XXX ±0.05		
				dr	BEER FU	2013-05-02	dwg no
				enrg	BEER FU	2013-05-02	
				chr	BEER FU	2013-05-02	10128788
				appd	BEER FU	2013-05-02	
sheet index	revision	C	C	C			type
	sheet	1	2	3			Customer Drawing



30u" Au	10128788-005RLF
15u" Au	10128788-004RLF
GOLD FLASH	10128788-001RLF
CONTACT AREA	FCI P/N

~~PB~~



48

REEL

LABEL

ø380

PEELING ANGLE
165°~180°



1400	5	7000	7.85Kg	3.5Kg
PCS/ TAPE	REELS/ BOX	PCS/BOX	GROSS WEIGHT	NET WEIGHT