

T-1 3/4 (ϕ 5mm) PACKAGE SOLID STATE LAMP

MVL-564TG

Description

The MVL-564TG, a green source color device, is made with

InGaN (on SiC substrate) LED die.

The package is T-1 3/4 (ϕ 5mm) water clear plastic type.


Applications

- Full color displays & moving message signs
- Solid state incandescent replacement bulbs
- High ambient panel indicators
- Color printers & scanners
- Medical & Analytical instruments

Features

- High performance - 1.5mW (525nm)
- Superior SiC substrate technology
- Excellent chip to chip consistency
- High reliability

Package Dimensions



Notes :

1. Tolerance is ± 0.25 mm (.010") unless otherwise noted.
2. Protruded resin under flange is 0.8 mm (.031") max.
3. Lead spacing is measured where the leads emerge from the package.

@ $T_A=25$ °C

Parameter	Symbol	Maximum Rating	Unit
Peak Forward Current (1/10 Duty Cycle@1KHz)	I_{pf}	100	mA
Continuous Forward Current	I_{af}	30	mA
Reverse Voltage	V_R	5	V
Operating Temperature Range	T_{opr}	-20 °C to +80 °C	
Storage Temperature Range	T_{stg}	-30 °C to +100 °C	
Electrostatic Discharge Threshold	E_{ot}	1000	V

UNi

Unity Opto Technology Co., Ltd.

08/03/2000

Optical-Electrical Characteristics

@ $T_A=25\text{ }^{\circ}\text{C}$

Parameter	Test Conditions	Symbol	Min .	Typ .	Max .	Unit .
Luminous Intensity	$I_F=20\text{mA}$	I_V	550	1100	-	mcd
Forward Voltage	$I_F=20\text{mA}$	V_F	-	3.5	4.0	V
Reverse Current	$V_R=5\text{V}$	I_R	-	-	10	μA
Peak Emission Wavelength	$I_F=20\text{mA}$	λ_p	-	525	-	nm
Viewing Angle	$I_F=20\text{mA}$	$2\theta_{1/2}$	-	30	-	deg.

Typical Optical-Electrical Characteristic Curves




FIG.1 RELATIVE INTENSITY LUMINOUS VS. WAVELENGTH




FIG.2 FORWARD CURRENT VS. FORWARD VOLTAGE




FIG.3 FORWARD CURRENT VS. AMBIENT TEMPERATURE




FIG.4 RELATIVE LUMINOUS INTENSITY VS. FORWARD CURRENT




FIG.5 LUMINOUS INTENSITY VS. AMBIENT TEMPERATURE




FIG.6 RADIATION DIAGRAM