







PRODUCT NO.
SEE TABLE



mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101	projection INCH/MM	product family HEADERS			
ltr	ecn	no	dr	date	tolerances unless otherwise specified			title			
A	V12177	MSC	8/13/91		angles	.XX±.01/.3		RIGHT ANGLE 2 ROW GUIDE			
B	V50833	MSC	8/3/95		linear	.XXX±.005/.13		PIN HEADER WITH RETENTION			
C	M05-0167	ERE	8/22/05	0°±2'		.XXXX±.0020/.051	scale 2:1	dwg no			
D	M06-0289	AGS	7/29/06	dr	M. CLOUSER	8/13/91		sheet 1 of 6 size			
				enr	S. AURAND	8/13/91		87255			
				chr	S. AURAND	8/13/91		A3			
				appd	S. AURAND	8/13/91		type Product Customer Drawing			
sheet	revision	D	D	D	D	D	D				
index	sheet	1	2	3	4	5	6				

PRODUCT NO. NOTE 4	SIZE NOTE 4	PLATING REF	KINK POS.
87255-005 THRU 87255-100	2 X 5 THRU 2 X 100	30u"/.76u Au OVER 50u"/1.27u Ni	NOTE 3
87255-105 THRU 87255-200	2 X 5 THRU 2 X 100	15u"/.38u Au OVER 50u"/1.27u Ni	NOTE 3
87255-205 THRU 87255-300	2 X 5 THRU 2 X 100	30u"/.76u GXT OVER 50u"/1.27u Ni	NOTE 3
87255-305 THRU 87255-400	2 X 5 THRU 2 X 100	15u"/.38u GXT OVER 50u"/1.27u Ni	NOTE 3



NOTES:

- ① MOLDING MATERIAL: 20% MIN GLASS FLLD POLYESTER PER UL 94 V-0 COLOR-BLACK.
- ② PIN RETENTION TO BE 3 LBS / 1.36 KG MIN PER PIN IN EITHER DIRECTION
- ③ RETENTION FEATURE (KINK) LOCATED TWO PAIRS EACH END 2X25 AND LARGER. RETENTION FEATURE (KINK) LOCATED ON 2 PAIR OF PINS IN THE CENTER OF PARTS SMALLER THAN 2X25.
- ④ -XXX REPRESENTS NO. OF COLUMNS (i.e. 2 x 5 PART IS -005).
-001 THRU -004 ARE NOT AVAILABLE.
-005 THRU -100 ARE AVAILABLE.

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection INCH/MM	product family HEADERS
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title
D					angles linear	.XX±.01/.3 linear.XXX±.005/.13 INCH/MM	RIGHT ANGLE 2 ROW GUIDE PIN HEADER WITH RETENTION
					0°±2'	.XXXX±.0020/.051 scale 2:1	
			dr	M. CLOUSER	8/13/91	FCI	dwg no
			enr	S. AURAND	8/13/91		sheet2 of 6 size
			chr	S. AURAND	8/13/91		87255 A3
			appd	S. AURAND	8/13/91		type Product Customer Drawing
sheet index	revision sheet						



FCIconnect.com

Copyright FCI

PRODUCT NO.	SIZE	OVERALL LENGTH DIM L	DIM D	DIM E	DIM F
87255-X01	U N A V A I L A B L E				
-X02					
-X03					
-X04	U N A V A I L A B L E				
-X05	2 X 5	.88/22.35	.400/10.16	.80/20.32	.77/19.55
-X06	2 X 6	.98/24.89	.500/12.70	.90/22.86	.87/22.09
-X07	2 X 7	1.08/27.43	.600/15.24	1.00/25.40	.97/24.63
-X08	2 X 8	1.18/29.97	.700/17.78	1.10/27.94	1.07/27.17
-X09	2 X 9	1.28/32.51	.800/20.32	1.20/30.48	1.17/29.71
-X10	2 X 10	1.38/35.05	.900/22.86	1.30/33.02	1.27/32.25
-X11	2 X 11	1.48/37.59	1.000/25.40	1.40/35.56	1.37/34.79
-X12	2 X 12	1.58/40.13	1.100/27.94	1.50/38.10	1.47/37.33
-X13	2 X 13	1.68/42.67	1.200/30.48	1.60/40.64	1.57/39.87
-X14	2 X 14	1.78/45.21	1.300/33.02	1.70/43.18	1.67/42.41
-X15	2 X 15	1.88/47.75	1.400/35.56	1.80/45.72	1.77/44.95
-X16	2 X 16	1.98/50.29	1.500/38.10	1.90/48.26	1.87/47.49
-X17	2 X 17	2.08/52.83	1.600/40.64	2.00/50.80	1.97/50.03
-X18	2 X 18	2.18/55.37	1.700/43.18	2.10/53.34	2.07/52.57
-X19	2 X 19	2.28/57.91	1.800/45.72	2.20/55.88	2.17/55.11
-X20	2 X 20	2.38/60.45	1.900/48.26	2.30/58.42	2.27/57.65
-X21	2 X 21	2.48/62.99	2.000/50.80	2.40/60.96	2.37/60.19
-X22	2 X 22	2.58/65.53	2.100/53.34	2.50/63.50	2.47/62.73
-X23	2 X 23	2.68/68.07	2.200/55.88	2.60/66.04	2.57/65.27
-X24	2 X 24	2.78/70.61	2.300/58.42	2.70/68.58	2.67/67.81
87255-X25	2 X 25	2.88/73.15	2.400/60.96	2.80/71.12	2.77/70.35

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection 	product family HEADERS
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title
D					angles	.XX±.01/.3	RIGHT ANGLE 2 ROW GUIDE PIN HEADER WITH RETENTION
					linear	.XXX±.005/.13	
					0°±2'	.XXXX±.0020/.051	scale 2:1
					dr	M. CLOUSER 8/13/91	dwg no 87255 sheet 3 of 6 size A3
					enr	S. AURAND 8/13/91	
					chr	S. AURAND 8/13/91	
					appd	S. AURAND 8/13/91	
sheet index	revision sheet						type Product Customer Drawing

form: A3



FCIconnect.com

Copyright FCI

PRODUCT NO.	SIZE	OVERALL LENGTH DIM L	DIM D	DIM E	DIM F
87255-X26	2 X 26	2.98/75.69	2.500/63.50	2.90/73.66	2.87/72.89
-X27	2 X 27	3.08/78.23	2.600/66.04	3.00/76.20	2.97/75.43
-X28	2 X 28	3.18/80.77	2.700/68.58	3.10/78.74	3.07/77.97
-X29	2 X 29	3.28/83.31	2.800/71.12	3.20/81.28	3.17/80.51
-X30	2 X 30	3.38/85.85	2.900/73.66	3.30/83.82	3.27/83.05
-X31	2 X 31	3.48/88.39	3.000/76.20	3.40/86.36	3.37/85.59
-X32	2 X 32	3.58/90.93	3.100/78.74	3.50/88.90	3.47/88.13
-X33	2 X 33	3.68/93.47	3.200/81.28	3.60/91.44	3.57/90.67
-X34	2 X 34	3.78/96.01	3.300/83.82	3.70/93.98	3.67/93.21
-X35	2 X 35	3.88/98.55	3.400/86.36	3.80/96.52	3.77/95.75
-X36	2 X 36	3.98/101.09	3.500/88.90	3.90/99.06	3.87/98.29
-X37	2 X 37	4.08/103.63	3.600/91.44	4.00/101.60	3.97/100.83
-X38	2 X 38	4.18/106.17	3.700/93.98	4.10/104.14	4.07/103.37
-X39	2 X 39	4.28/108.71	3.800/96.52	4.20/106.68	4.17/105.91
-X40	2 X 40	4.38/111.25	3.900/99.06	4.30/109.22	4.27/108.45
-X41	2 X 41	4.48/113.79	4.000/101.60	4.40/111.76	4.37/110.99
-X42	2 X 42	4.58/116.33	4.100/104.14	4.50/114.30	4.47/113.53
-X43	2 X 43	4.68/118.87	4.200/106.68	4.60/116.84	4.57/116.07
-X44	2 X 44	4.78/121.41	4.300/109.22	4.70/119.38	4.67/118.61
-X45	2 X 45	4.88/123.95	4.400/111.76	4.80/121.92	4.77/121.15
-X46	2 X 46	4.98/126.49	4.500/114.30	4.90/124.46	4.87/123.69
-X47	2 X 47	5.08/129.03	4.600/116.84	5.00/127.00	4.97/126.23
-X48	2 X 48	5.18/131.57	4.700/119.38	5.10/129.54	5.07/128.77
-X49	2 X 49	5.28/134.11	4.800/121.92	5.20/132.08	5.17/131.31
87255-X50	2 X 50	5.38/136.65	4.900/124.46	5.30/134.62	5.27/133.85

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection 	product family HEADERS
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title
D					angles	.XX±.01/.3	RIGHT ANGLE 2 ROW GUIDE PIN HEADER WITH RETENTION
					linear	.XXX±.005/.13	
					0°±2'	.XXXX±.0020/.051	scale 2:1
					dr	M. CLOUSER 8/13/91	dwg no 87255 sheet 4 of 6 size A3
					enr	S. AURAND 8/13/91	
					chr	S. AURAND 8/13/91	
					appd	S. AURAND 8/13/91	
sheet index	revision sheet						type Product Customer Drawing

form: A3



FCIconnect.com

Copyright FCI

PRODUCT NO.	SIZE	OVERALL LENGTH DIM L	DIM D	DIM E	DIM F
87255-X51	2 X 51	5.48/139.19	5.000/127.00	5.40/137.16	5.37/136.39
-X52	2 X 52	5.58/141.73	5.100/129.54	5.50/139.70	5.47/138.93
-X53	2 X 53	5.68/144.27	5.200/132.08	5.60/142.24	5.57/141.47
-X54	2 X 54	5.78/146.81	5.300/134.62	5.70/144.78	5.67/144.01
-X55	2 X 55	5.88/149.35	5.400/137.16	5.80/147.32	5.77/146.55
-X56	2 X 56	5.98/151.89	5.500/139.70	5.90/149.86	5.87/149.09
-X57	2 X 57	6.08/154.43	5.600/142.24	6.00/152.40	5.97/151.63
-X58	2 X 58	6.18/156.97	5.700/144.78	6.10/154.94	6.07/154.17
-X59	2 X 59	6.28/159.51	5.800/147.32	6.20/157.48	6.17/156.71
-X60	2 X 60	6.38/162.05	5.900/149.86	6.30/160.02	6.27/159.25
-X61	2 X 61	6.48/164.59	6.000/152.40	6.40/162.56	6.37/161.79
-X62	2 X 62	6.58/167.13	6.100/154.94	6.50/165.10	6.47/164.33
-X63	2 X 63	6.68/169.67	6.200/157.48	6.60/167.64	6.57/166.87
-X64	2 X 64	6.78/172.21	6.300/160.02	6.70/170.18	6.67/169.41
-X65	2 X 65	6.88/174.75	6.400/162.56	6.80/172.72	6.77/171.95
-X66	2 X 66	6.98/177.29	6.500/165.10	6.90/175.26	6.87/174.49
-X67	2 X 67	7.08/179.83	6.600/167.64	7.00/177.80	6.97/177.03
-X68	2 X 68	7.18/182.37	6.700/170.18	7.10/180.34	7.07/179.57
-X69	2 X 69	7.28/184.91	6.800/172.72	7.20/182.88	7.17/182.11
-X70	2 X 70	7.38/187.45	6.900/175.26	7.30/185.42	7.27/184.65
-X71	2 X 71	7.48/189.99	7.000/177.80	7.40/187.96	6.37/161.79
-X72	2 X 72	7.58/192.53	7.100/180.34	7.50/190.50	6.47/164.33
-X73	2 X 73	7.68/195.07	7.200/182.88	7.60/193.04	6.57/166.87
-X74	2 X 74	7.78/197.61	7.300/185.42	7.70/195.58	6.67/169.41
87255-X75	2 X 75	7.88/200.15	7.400/187.96	7.80/198.12	6.77/171.95

mat'l. code		surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family HEADERS		
ltr	ecn no	dr	date	tolerances unless otherwise specified						
D				angles	linear		.XX±.01/.3 INCH/MM		title RIGHT ANGLE 2 ROW GUIDE PIN HEADER WITH RETENTION	
				0°±2'	.XXX±.005/.13 .XXXX±.0020/.051		scale 2:1			
				dr	M. CLOUSER	8/13/91			dwg no 87255	
				enr	S. AURAND	8/13/91				sheet 5 of 6 size A3
				chr	S. AURAND	8/13/91				
				appd	S. AURAND	8/13/91				
sheet index	revision sheet									

form: A3



FCIconnect.com

Copyright FCI

PRODUCT NO.	SIZE	OVERALL LENGTH DIM L	DIM D	DIM E	DIM F
87255-X76	2 X 76	7.98/202.69	7.500/190.50	7.90/200.66	6.87/174.49
-X77	2 X 77	8.08/205.23	7.600/193.04	8.00/203.20	6.97/177.03
-X78	2 X 78	8.18/207.77	7.700/195.58	8.10/205.74	7.07/179.57
-X79	2 X 79	8.28/210.31	7.800/198.12	8.20/208.28	7.17/182.11
-X80	2 X 80	8.38/212.85	7.900/200.66	8.30/210.82	7.27/184.65
-X81	2 X 81	8.48/215.39	8.000/203.20	8.40/213.36	7.37/187.19
-X82	2 X 82	8.58/217.93	8.100/205.74	8.50/215.90	7.47/189.73
-X83	2 X 83	8.68/220.47	8.200/208.28	8.60/218.44	7.57/192.27
-X84	2 X 84	8.78/223.01	8.300/210.82	8.70/220.98	7.67/194.81
-X85	2 X 85	8.88/225.55	8.400/213.36	8.80/223.52	7.77/197.35
-X86	2 X 86	8.98/228.09	8.500/215.90	8.90/226.06	7.87/199.89
-X87	2 X 87	9.08/230.63	8.600/218.44	9.00/228.60	7.97/202.43
-X88	2 X 88	9.18/233.17	8.700/220.98	9.10/231.14	8.07/204.97
-X89	2 X 89	9.28/235.71	8.800/223.52	9.20/233.68	8.17/207.51
-X90	2 X 90	9.38/238.25	8.900/226.06	9.30/236.22	8.27/210.05
-X91	2 X 91	9.48/240.79	9.000/228.60	9.40/238.76	8.37/212.59
-X92	2 X 92	9.58/243.33	9.100/231.14	9.50/241.30	8.47/215.13
-X93	2 X 93	9.68/245.87	9.200/233.68	9.60/243.84	8.57/217.67
-X94	2 X 94	9.78/248.41	9.300/236.22	9.70/246.38	8.67/220.21
-X95	2 X 95	9.88/250.95	9.400/238.76	9.80/248.92	8.77/222.75
-X96	2 X 96	9.98/253.49	9.500/241.30	9.90/251.46	8.87/225.29
-X97	2 X 97	10.08/256.03	9.600/243.84	10.00/254.00	8.97/227.83
-X98	2 X 98	10.18/258.57	9.700/246.38	10.10/256.54	9.07/230.37
-X99	2 X 99	10.28/261.11	9.800/248.92	10.20/259.08	9.17/232.91
87255-X00	2 X 100	10.38/263.65	9.900/251.46	10.30/261.62	9.27/235.45

mat'l. code				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection 	product family HEADERS
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title
D					angles	.XX±.01/.3	RIGHT ANGLE 2 ROW GUIDE PIN HEADER WITH RETENTION
					linear	.XXX±.005/.13	
					0°±2'	.XXXX±.0020/.051	scale 2:1
					dr	M. CLOUSER 8/13/91	dwg no 87255 sheet 6 of 6 size A3
					enr	S. AURAND 8/13/91	
					chr	S. AURAND 8/13/91	
					appd	S. AURAND 8/13/91	
sheet index	revision sheet						type Product Customer Drawing

form: A3