




LOC		DIST		REVISONS		DATE		DWG		APPRO	
CM		00		P		LWR		J		ECO-07-012876	
										15JUN07	
										KW	
										DB	

D



C



B

1. MATERIAL: CONNECTOR - NYLON UL94V-2 (BLUE).
CONTACTS - 0.30[.012] THICK COPPER ALLOY
0.00076 [0.00030] GOLD IN CONTACT
AREA WITH BRIGHT TIN-LEAD FOR
641231-2 THRU 2-641231-4,
MATTE WHISKER MITIGATED TIN FOR
3-641231-2 THRU 5-641231-4 OVER
NICKEL UNDERPLATE

2. CONTACTS ACCEPT 26 AWG WIRE WITH 2.41[.095] MAX
INSULATION DIAMETER.
3. CONTACTS MUST ACCEPT 1.14±0.03 [0.45±.001] SQUARE
POST AND REMAIN LOCKED IN POSITION.
4. IDENTIFICATION NUMBER FOR LAST CIRCUIT MAY
NOT APPEAR ON ALL ASSEMBLIES.
5. DIMENSIONS IN BRACKETS ARE IN INCHES.
6. HOUSING FEATURES ARE: FEED-THRU WITH LOCKING
RAMP.

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIM A		NO OF CIRCUITS		PART NO	
DWG	B. LEWIS	12 MAR 96	12 MAR 96	26	26	641231-2	641231-2
CHK	W. SWING	12 MAR 96	12 MAR 96	26	26	641231-2	641231-2
OTHER NAMES, UNLESS OTHERWISE SPECIFIED:		D. CLARK		MTA-156 CONNECTOR ASSEMBLY,		26 AWG, STANDARD	
DIMENSIONS:		108-1051		APPLICATION SPEC		SIZE	
mm [INCHES]		114-1020		WEIGHT		A2 00779	
FINISH		RESTRICTED TO		SCALE		4:1	
MATERIAL		CUSTOMER DRAWING		SHEET		1 OF 1	