


1) - 30u"/0.76um MIN GOLD PLATE IN SELECTED AREA 75u"/1.90um MIN TIN/LEAD PLATE IN SELECTED AREA BOTH OVER 50u"/1.25um MIN NICKEL OVERALL	4) - 30u"/0.76um MIN GOLD PLATE IN SELECTED AREA 75u"/1.90um MIN TIN PLATE IN SELECTED AREA BOTH OVER 50u"/1.25um MIN NICKEL OVERALL
2) - 15u"/0.38um MIN GOLD PLATE IN SELECTED AREA 75u"/1.90um MIN TIN/LEAD PLATE IN SELECTED AREA BOTH OVER 50u"/1.25um MIN NICKEL OVERALL	5) - 15u"/0.38um MIN GOLD PLATE IN SELECTED AREA 75u"/1.90um MIN TIN PLATE IN SELECTED AREA BOTH OVER 50u"/1.25um MIN NICKEL OVERALL
3) - 2u"/0.05um MIN GOLD PLATE IN SELECTED AREA 40u"/1.02um MIN TIN/LEAD PLATE IN SELECTED AREA BOTH OVER 40u"/1.02um MIN NICKEL OVERALL	6) - 2u"/0.05um MIN GOLD PLATE IN SELECTED AREA 40u"/1.02um MIN TIN PLATE IN SELECTED AREA BOTH OVER 40u"/1.02um MIN NICKEL OVERALL



tb_frame_A3_P_AM_T
Rev. D 2004/06/28

F

D

D

A

	10	9	8	7	6	5	4	3	2	1						
F	TIN OPTION										F					
E				P.C.TAIL DIMENSION 'C' = 3.00			P.C.TAIL DIMENSION 'C' = 1.91				E					
	CKT SIZE	DIM 'A'	DIM 'B'	PLATING OPTION 5		PLATING OPTION 4		PLATING OPTION 6		PLATING OPTION 5		PLATING OPTION 4		PLATING OPTION 6		
				ITEM NO.		ITEM NO.		ITEM NO.		ITEM NO.		ITEM NO.		ITEM NO.		
D	04	(4.19)	(2.00)		79107-7001		79107-7051	X	79107-7126		79107-7201		79107-7251	X	79107-7326	
	06	(6.19)	(4.00)		79107-7002		79107-7052	X	79107-7127		79107-7202		79107-7252	X	79107-7327	
	08	(8.19)	(6.00)		79107-7003		79107-7053	X	79107-7128		79107-7203		79107-7253	X	79107-7328	
	10	(10.19)	(8.00)		79107-7004		79107-7054	X	79107-7129		79107-7204		79107-7254	X	79107-7329	
	12	(12.19)	(10.00)		79107-7005		79107-7055		79107-7130		79107-7205		79107-7255		79107-7330	
	14	(14.19)	(12.00)		79107-7006		79107-7056	X	79107-7131		79107-7206		79107-7256	X	79107-7331	
	16	(16.19)	(14.00)		79107-7007		79107-7057	X	79107-7132		79107-7207		79107-7257	X	79107-7332	
	18	(18.19)	(16.00)		79107-7008		79107-7058	X	79107-7133		79107-7208		79107-7258	X	79107-7333	
	20	(20.19)	(18.00)		79107-7009		79107-7059	X	79107-7134		79107-7209		79107-7259	X	79107-7334	
	22	(22.19)	(20.00)		79107-7010		79107-7060	X	79107-7135		79107-7210		79107-7260	X	79107-7335	
C	24	(24.19)	(22.00)		79107-7011		79107-7061	X	79107-7136		79107-7211		79107-7261	X	79107-7336	
	26	(26.19)	(24.00)		79107-7012		79107-7062	X	79107-7137		79107-7212		79107-7262	X	79107-7337	
	28	(28.19)	(26.00)		79107-7013		79107-7063	X	79107-7138		79107-7213		79107-7263	X	79107-7338	
	30	(30.19)	(28.00)		79107-7014		79107-7064	X	79107-7139		79107-7214		79107-7264	X	79107-7339	
	32	(32.19)	(30.00)		79107-7015		79107-7065	X	79107-7140		79107-7215		79107-7265	X	79107-7340	
	34	(34.19)	(32.00)		79107-7016		79107-7066	X	79107-7141		79107-7216		79107-7266	X	79107-7341	
	36	(36.19)	(34.00)		79107-7017		79107-7067	X	79107-7142		79107-7217		79107-7267	X	79107-7342	
	38	(38.19)	(36.00)		79107-7018		79107-7068	X	79107-7143		79107-7218		79107-7268	X	79107-7343	
	40	(40.19)	(38.00)		79107-7019		79107-7069	X	79107-7144		79107-7219		79107-7269	X	79107-7344	
	42	(42.19)	(40.00)		79107-7020		79107-7070	X	79107-7145		79107-7220		79107-7270	X	79107-7345	
A	44	(44.19)	(42.00)		79107-7021		79107-7071	X	79107-7146		79107-7221		79107-7271	X	79107-7346	
	46	(46.19)	(44.00)		79107-7022		79107-7072	X	79107-7147		79107-7222		79107-7272	X	79107-7347	
	48	(48.19)	(46.00)		79107-7023		79107-7073	X	79107-7148		79107-7223		79107-7273	X	79107-7348	
	50	(50.19)	(48.00)		79107-7024		79107-7074	X	79107-7149		79107-7224		79107-7274	X	79107-7349	
X - DENOTES THE ITEM IS NOT AVAILABLE CURRENTLY.																
B																B
A				UPDATE TOLERANCE EC NO: S2006-0673 DRWN:YLOI/AO 2006/01/05 CHKD:BOKOK 2006/01/06 APPR:PTL/IM 2006/01/07	QUALITY SYMBOLS ▽=0 ▽C=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
						4 PLACES ± --- ± ---		DRAWN BY AAB		DATE 1989/05/15		TITLE 2MM DUAL ROW VERTICAL RECEPTACLE T/H				
						3 PLACES ± --- ± ---		CHECKED BY		DATE 1989/05/15						
						2 PLACES ± 0.25 ± ---		APPROVED BY		DATE 1989/05/15						
						ANGULAR ±1/2°			MATERIAL NO.		DOCUMENT NO.					
						DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE TABLE		SDA-79107-****					
									SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
ib_frame_A3_P_AM_T Rev. D 2004/06/28																
	9	8	7	6	5	4	3	2	1							

10987654321

F

E

D

C

B

A

ib_frame_A3_P_AM_T
Rev. D 2004/06/28

MOLDED VOID OPTION

ASSEMBLIES WITHOUT PEGS

CKT. SIZE	ASSEMBLY		VOID LOCATION(S) SEE SHEET 1 FOR CONVENTION		PLATING OPTION	DIM. "A"	DIM. "B"	P.C. TAIL DIM. "C"	PLATING OPTION
	ITEM NO.	ROW	CKT. NO.(s)						
24		79107-5001			2	(24.19)	(22.00)	(3.00)	TIN/LEAD
			ROW B	6					
10		79107-5002			2	(10.19)	(8.00)	(3.00)	
			ROW A	5					
26		79107-5003			2	(26.19)	(24.00)	(3.00)	
			ROW B	5					
24		79107-5101			5	(24.19)	(22.00)	(3.00)	TIN
			ROW B	6					
10		79107-5102			5	(10.19)	(8.00)	(3.00)	
			ROW A	5					
26		79107-5103			5	(26.19)	(24.00)	(3.00)	
			ROW B	5					

"X" - DENOTES THE ITEM IS NOT AVAILABLE CURRENTLY.

NOTES

1. TERMINALS WILL BE PRESENT IN VOIDED LOCATIONS HOWEVER, PIN WINDOWS WILL BE CLOSED.

2. VOIDS CANNOT BE PRESENT IN BOTH ROWS ON A CONNECTOR.

UPDATE TOLERANCE EC NO: S2006-0673 DRWN:YLOIAO 2006/01/05 CHKD:BOOK 2006/01/06 APPR:PTLIM 2006/01/07	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽C=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
			4 PLACES	mm	INCH	DRAWN BY AAB	DATE 1989/05/15	TITLE 2MM DUAL ROW VERTICAL RECEPTACLE T/H		
				3 PLACES	± ---	± ---	CHECKED BY MJM		DATE 1989/05/15	
					2 PLACES	± 0.25	± ---		APPROVED BY WAZ	DATE 1989/05/15
			1 PLACE	± 0.38	± ---	MATERIAL NO.		DOCUMENT NO.		SHEET NO.
			ANGULAR ±1/2°			SEE TABLE		SDA-79107-****		4 OF 4
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				

F

D

B

A

MOLDED VOID OPTION ASSEMBLIES WITHOUT PEGS

	ASSEMBLY		VOID LOCATION(S) SEE SHEET 1 FOR CONVENTION		PLATING OPTION	DIM. "A"	DIM. "B"	P.C. TAIL DIM. "C"	PLATING OPTION
CKT. SIZE	ITEM NO.		ROW	CKT. NO.(s)					
24		79107-5001			2	(24.19)	(22.00)	(3.00)	TIN/LEAD
			ROW B	6					
10		79107-5002			2	(10.19)	(8.00)	(3.00)	
			ROW A	5					
26		79107-5003			2	(26.19)	(24.00)	(3.00)	
			ROW B	5					
24		79107-5101			5	(24.19)	(22.00)	(3.00)	TIN
			ROW B	6					
10		79107-5102			5	(10.19)	(8.00)	(3.00)	
			ROW A	5					
26		79107-5103			5	(26.19)	(24.00)	(3.00)	
			ROW B	5					

"X" - DENOTES THE ITEM IS NOT AVAILABLE CURRENTLY.

NOTES

1. TERMINALS WILL BE PRESENT IN VOIDED LOCATIONS HOWEVER, PIN WINDOWS WILL BE CLOSED.
2. VOIDS CANNOT BE PRESENT IN BOTH ROWS ON A CONNECTOR.

CHANGE TOLERANCES EC NO: S2006-0225 DRWN:YLOI/AO CHKD:BO/KOK APPR:PTL/IM	QUALITY SYMBOLS ▽=0 ▽C=0	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION		
					DRAWN BY AAB	DATE 1989/05/15	TITLE SALES DRAWING 2MM DUAL ROW VERTICAL RECEPTACLE T/H				
					CHECKED BY MJM	DATE 1989/05/15					
					APPROVED BY WAZ	DATE 1989/05/15	MOLEX INCORPORATED				
					MATERIAL NO.					DOCUMENT NO.	
					SEE TABLE		SDA-79107-****				
					THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
F2	REV		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS								