



- ① ZINC PER QQ-Z-363.
- ② BERYLLIUM COPPER PER QQ-C-530.
- ③ PTFE PER MIL-P-19468.
- ④ NICKEL PLATE PER QQ-N-290,
3.81 μ m [.000150] MINIMUM THICK.
- ⑤ TIN PLATE PER ASTM-B-545,
3.04 μ m [.000120] MINIMUM THICK OVER
NICKEL PLATE PER MIL-C-26074,
7.62 μ m [.000300] MINIMUM THICK.
- ⑥ GOLD PLATE PER MIL-G-45204,
1.27 μ m [.000050] MINIMUM THICK.
7. INTERFACE PER MIL-C-39012.
- ⑧ POLYMETHYLPENTENE, GENERAL PURPOSE



PCB CONFIGURATION

OBSOLETE	3.33 [.131]			5413631-5
	3.33 [.131]			5413631-3
	4.34 [.171]			5413631-2
	4.34 [.171]			5413631-1
	A	FINISH: SHELL	MATERIAL: DIELECTRIC, FRONT	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B.MCMMASTER 03JAN05 CHK 03JAN05 J.LIPPERT APVD 03JAN05 J.LIPPERT PRODUCT SPEC APPLICATION SPEC —		 TE Connectivity	
DIMENSIONS: INCHES 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± 0.08 [0.003] 3 PLC ± — 4 PLC ± — ANGLES ± ± —		NAME JACK, RIGHT ANGLE, PCB, 50 OHM, SERIES BNC	
MATERIAL SEE NOTES 1-3		FINISH SEE NOTES 4-6			
		WEIGHT —		SIZE A2	CAGE CODE 00779
		CUSTOMER DRAWING		DRAWING NO C-5413631	RESTRICTED TO —
		SCALE 4:1		SHEET 1 of 1	REV C