



Features

- Protects one line or one I/O port
- Bidirectional configuration
- ESD protection 30 kV max.
- Low capacitance ~ 3 pF typ.
- Replaces 0805 MLV devices
- RoHS compliant*
- Halogen free**

Applications

- VDSL lines
- Modems
- Routers


CDSOD323-TxxC-DSL - TVS Diode Series

General Information

Portable communications and telecom equipment manufacturers are challenging the semiconductor industry to develop increasingly smaller electronic components for high-speed communication rates.

Bourns offers Transient Voltage Suppressor Diodes for surge and ESD protection applications in SOD323 package size format. The Transient Voltage Suppressor Diode series offers a choice of voltage types ranging from 12 V to 24 V in a bidirectional configuration. Bourns® Chip Diodes conform to JEDEC standards, are easy to handle on standard pick and place equipment and their flat configuration minimizes roll away.

The Bourns® device will assist compliance with IEC 61000-4-2 (ESD), IEC 61000-4-4 (EFT) and will assist in meeting IEC 61000-4-5 (Surge) requirements.



Absolute Maximum Ratings (@ $T_A = 25^\circ\text{C}$ Unless Otherwise Noted)

| Parameter | Symbol | CDSOD323- | | Unit |
|---|-----------|-------------|----------|------|
| | | T12C-DSL | T24C-DSL | |
| Peak Pulse Current ($t_p = 8/20 \mu\text{s}$) | I_{PPM} | 11 | 6 | A |
| Peak Pulse Power ($t_p = 8/20 \mu\text{s}$) | P_{PP} | 350 | | W |
| Operating Temperature | T_J | -55 to +150 | | °C |
| Storage Temperature | T_{STG} | -55 to +150 | | °C |
| ESD Protection (per IEC 61000-4-2) | | | | |
| Contact Discharge | | | | |
| Minimum | ESD | ± 8 | | kV |
| Maximum | ESD | ± 30 | | kV |
| Air Discharge | | | | |
| Minimum | ESD | ± 15 | | kV |
| Maximum | ESD | ± 30 | | kV |

Electrical & Thermal Characteristics (@ $T_A = 25^\circ\text{C}$ Unless Otherwise Noted)

| Parameter | Symbol | CDSOD323- | | Unit |
|--|----------|---------------|--------------|------|
| | | T12C-DSL | T24C-DSL | |
| Min. Breakdown Voltage @ 1 mA | V_{BR} | 13.3 | 26.7 | V |
| Working Peak Voltage | V_{WM} | 12.0 | 24.0 | V |
| Maximum Clamping Voltage @ $I_p = 1 \text{ A}$ | V_C | 19.0 | 43.0 | V |
| Typical Clamping Voltage @ 8/20 μs @ I_{PP} | V_C | 28.3 V @ 11 A | 56.0 V @ 6 A | V |
| Maximum Leakage Current @ V_{WM} | I_D | 1 | | nA |
| Typical Capacitance @ 0 V, 1 MHz | C_J | 3 | | pF |

Note: The electrical specifications apply in both polarities.

* RoHS Directive 2002/95/EC Jan. 27, 2003 including annex and RoHS Recast 2011/65/EU June 8, 2011.

** Bourns considers a product to be "halogen free" if (a) the Bromine (Br) content is 900 ppm or less; (b) the Chlorine (Cl) content is 900 ppm or less; and (c) the total Bromine (Br) and Chlorine (Cl) content is 1500 ppm or less.

SSpecifications are subject to change without notice.


The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time. Users should verify actual device performance in their specific applications.

CDSOD323-TxxC-DSL - TVS Diode Series


BOURNS®

Performance Graphs


Peak Pulse Power vs. Pulse Time



Pulse Waveform



Block Diagram



How to Order

CD SOD323 - T 12 C - DSL

Common Code
Chip Diode

Package
• SOD323 = SOD-323 Package

Model
T = Transient Voltage Suppressor

Working Peak Reverse Voltage
12 = 12 V_{RWM} (Volts)
24 = 24 V_{RWM} (Volts)

Suffix
C = Bidirectional Diode
-DSL = For use in VDSL applications

Environmental Specifications

Moisture Sensitivity Level 1
ESD Classification (HBM) 3B

Specifications are subject to change without notice.


The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time. Users should verify actual device performance in their specific applications.

CDSOD323-TxxC-DSL - TVS Diode Series

BOURNS®

Product Dimensions


This is a molded JEDEC SOD-323 package with lead free 100 % Sn plating on the terminations. It weighs approximately 30 mg and has a flammability rating of UL 94V-0.



| Dimensions | |
|------------|--------------------------------|
| A | 1.60 - 1.90 (0.063 - 0.075) |
| B | 1.15 - 1.45 (0.045 - 0.057) |
| C | 2.39 - 2.70 (0.094 - 0.106) |
| D | 0.92 - 1.14 (0.036 - 0.045) |
| E | 0.25 - 0.40 (0.010 - 0.016) |
| F | 0.08 - 0.20 (0.003 - 0.008) |
| H | 0.13 (0.005) MAX. |
| J | 0.30 - 0.45 (0.012 - 0.018) |

DIMENSIONS: $\frac{\text{MM}}{\text{(INCHES)}}$

Recommended Footprint



| Dimensions (Nominal) | |
|----------------------|-----------------|
| L | 0.80 (0.031) |
| S | 1.40 (0.055) |
| W | 0.50 (0.020) |

DIMENSIONS: $\frac{\text{MM}}{\text{(INCHES)}}$

Typical Part Marking

Each device has device marking outlined below.

CDSOD323-T12C-DSL 2D
CDSOD323-T24C-DSL 4D

Specifications are subject to change without notice.



The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time. Users should verify actual device performance in their specific applications.

CDSOD323-TxxC-DSL - TVS Diode Series

BOURNS®

Packaging Information

The surface mount product is packaged in an 8 mm x 4 mm tape and reel format per EIA-481 standard.



Devices are packed in accordance with EIA standard RS-481-A.

| Item | Symbol | SOD-323 |
|------------------------|----------------|--|
| Carrier Width | A | 1.55 ± 0.10 (0.061 ± 0.004) |
| Carrier Length | B | 2.90 ± 0.10 (0.114 ± 0.004) |
| Carrier Depth | C | 1.35 ± 0.10 (0.053 ± 0.004) |
| Sprocket Hole | d | 1.55 ± 0.05 (0.061 ± 0.002) |
| Reel Outside Diameter | D | 178 (7.008) |
| Reel Inner Diameter | D ₁ | 80.0 (3.150) Min. |
| Feed Hole Diameter | D ₂ | 13.0 ± 0.20 (0.512 ± 0.008) |
| Sprocket Hole Position | E | 1.75 ± 0.10 (0.069 ± 0.004) |
| Punch Hole Position | F | 3.50 ± 0.05 (0.138 ± 0.002) |
| Punch Hole Pitch | P | 4.00 ± 0.10 (0.157 ± 0.004) |
| Sprocket Hole Pitch | P ₀ | 4.00 ± 0.10 (0.157 ± 0.004) |
| Embossment Center | P ₁ | 2.00 ± 0.05 (0.079 ± 0.002) |
| Overall Tape Thickness | T | 0.20 ± 0.10 (0.008 ± 0.004) |
| Tape Width | W | 8.00 ± 0.20 (0.315 ± 0.008) |
| Reel Width | W ₁ | 13.5 (0.531) Max. |
| Quantity per Reel | -- | 3,000 |

REV. 01/18

Specifications are subject to change without notice.

The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time. Users should verify actual device performance in their specific applications.