





LOC	DIST	REVISIONS					
CM	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			K	REVISED PER ECO-12-016930	050CT12	KH	SM




RECOMMENDED MOUNTING HOLE PATTERN
FOR .063 THICK P.C. BOARD

		.700	17.78
.060	1.52	.468	11.89
.051	1.30	.450	11.43
.046	1.17	.425	10.80
.045	1.14	.412	7.92
.030	0.76	.300	7.62
.015	0.38	.180	4.57
.012	0.30	.175	4.45
.010	0.25	.156	3.96
.008	0.20	.125	3.18
.005	0.13	.078	1.98
.003	0.08	.068	1.73
.001	0.03	.063	1.60
[IN]	MM	[IN]	MM

CONVERSION TABLE

643960-1 SHOWN

OBSOLETE	3	643960-2
	2	643960-1
	POST NUMBER OMITTED	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIM S. HOOVER CHK D. BOSSI 07NOV02 07NOV02		 TE Connectivity	
DIMENSIONS: INCHES		TOLERANCES UNLESS SPECIFIED: 07NOV02		NAME MTA-156 HEADER ASSEMBLY, FRICTION LOCK, STRAIGHT .045 ROUND POST, TIN PLATED, 3 POSITION, OMITTED POST	
		APVD D. BOSSI PROD. SPECI — APPLICATION SPEC —		SIZE CAGE CODE DRAWING NO A1 00779 C-643960	
MATERIAL 		FINISH 		RESTRICTED TO —	
CUSTOMER DRAWING				SCALE 5:1 SHEET 1 OF 1 REV K	