

**AS85049/56 and AS85049/57**  
**Straight and 45° Qwik-Ty Strain Reliefs**  
 Optional Self-Locking • Optional Ground Lug



AS85049

**CONNECTOR DESIGNATOR:**

**F** MIL-DTL-38999 Series I and II

**Configuration**

*N* = Non-Detented  
*G* = Self-Locking with Ground Lug  
*H* = Non-Detented with Ground Lug  
*S* = Self-Locking without Ground Lug  
 — = Non Self-Locking

**Finish**

*A* = Anodize, Black  
*N* = Electroless Nickel  
*W* = 1,000 Hour Cadmium Olive Drab over Electroless Nickel  
*X* = Nickel Fluorocarbon Polymer  
*Y* = Pure Dense Electrodeposited Aluminum  
*Z* = Zinc-Nickel, Black

**Basic Part Number**

*M85049/56* = Straight  
*M85049/57* = 45°

**M85049/57**

**G**


**16**

**W**

**OPTIONAL  
SELF-LOCKING  
COUPLING**

**B**

Shell  
Size



**TABLE I: Shell Size, Thread, Cable Entry and Backshell Dimensions**

| Shell Size<br>Series II | Series I<br>Shell Size<br>Ref. | A Thread<br>Class 2B | C Dia<br>Max | E Dia<br>Max | F<br>Cable Entry | G<br>Max     | H<br>Max     |
|-------------------------|--------------------------------|----------------------|--------------|--------------|------------------|--------------|--------------|
| 8                       | 9                              | .438-28 UNEF         | .750 (19.1)  | .860 (21.8)  | .264 (6.7)       | .895 (22.7)  | 1.210 (30.7) |
| 10                      | 11                             | .562-24 UNEF         | .850 (21.6)  | .980 (24.9)  | .392 (10.0)      | .895 (22.7)  | 1.210 (30.7) |
| 12                      | 13                             | .688-24 UNEF         | 1.000 (25.4) | 1.160 (29.5) | .506 (12.9)      | .955 (24.3)  | 1.390 (35.3) |
| 14                      | 15                             | .813-20 UNEF         | 1.100 (27.9) | 1.280 (32.5) | .631 (16.0)      | 1.135 (28.8) | 1.390 (35.3) |
| 16                      | 17                             | .938-20 UNEF         | 1.250 (31.8) | 1.410 (35.8) | .756 (19.2)      | 1.135 (28.8) | 1.390 (35.3) |
| 18                      | 19                             | 1.063-18 UNEF        | 1.400 (35.6) | 1.520 (38.6) | .845 (21.5)      | 1.195 (30.4) | 1.390 (35.3) |
| 20                      | 21                             | 1.188-18 UNEF        | 1.500 (38.1) | 1.640 (41.7) | .970 (24.6)      | 1.325 (33.7) | 1.390 (35.3) |
| 22                      | 23                             | 1.313-18 UNEF        | 1.650 (41.9) | 1.770 (45.0) | 1.095 (27.8)     | 1.445 (36.7) | 1.390 (35.3) |
| 24                      | 25                             | 1.438-18 UNEF        | 1.750 (44.5) | 1.890 (48.0) | 1.220 (31.0)     | 1.585 (40.3) | 1.390 (35.3) |

**APPLICATION NOTES**

1. Assembly identified with manufacturer's name and part number, space permitting.
2. For complete dimensions, see the applicable Military Specification.
3. Cable entry is defined as the accommodation range for the wire bundle or cable. Dimensions shown are not intended for inspection criteria.
4. Metric dimensions (mm) are in parentheses.

Dimensions in inches (millimeters) and are subject to change without notice.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Glenair:

|                                      |                                      |                                       |                                      |                                      |                                      |
|--------------------------------------|--------------------------------------|---------------------------------------|--------------------------------------|--------------------------------------|--------------------------------------|
| <a href="#"><u>M85049/57S24N</u></a> | <a href="#"><u>M85049/55G22W</u></a> | <a href="#"><u>M85049/55G-08W</u></a> | <a href="#"><u>M85049/55S16W</u></a> | <a href="#"><u>M85049/56-08W</u></a> | <a href="#"><u>M85049/57S12W</u></a> |
| <a href="#"><u>M85049/57S16W</u></a> | <a href="#"><u>M85049/55-03N</u></a> | <a href="#"><u>M85049/55-24N</u></a>  | <a href="#"><u>M85049/55G08N</u></a> | <a href="#"><u>M85049/55G10N</u></a> | <a href="#"><u>M85049/55G12N</u></a> |
| <a href="#"><u>M85049/55G14N</u></a> | <a href="#"><u>M85049/55G16N</u></a> | <a href="#"><u>M85049/55G18N</u></a>  | <a href="#"><u>M85049/55G20N</u></a> | <a href="#"><u>M85049/55G22N</u></a> | <a href="#"><u>M85049/55G24N</u></a> |
| <a href="#"><u>M85049/55G28N</u></a> | <a href="#"><u>M85049/55H08A</u></a> | <a href="#"><u>M85049/55H08N</u></a>  | <a href="#"><u>M85049/55H08W</u></a> | <a href="#"><u>M85049/55H10A</u></a> | <a href="#"><u>M85049/55H10N</u></a> |
| <a href="#"><u>M85049/55H10W</u></a> | <a href="#"><u>M85049/55H12A</u></a> | <a href="#"><u>M85049/55H12N</u></a>  | <a href="#"><u>M85049/55H12W</u></a> | <a href="#"><u>M85049/55H14A</u></a> | <a href="#"><u>M85049/55H14N</u></a> |
| <a href="#"><u>M85049/55H14W</u></a> | <a href="#"><u>M85049/55H16A</u></a> | <a href="#"><u>M85049/55H16N</u></a>  | <a href="#"><u>M85049/55H16W</u></a> | <a href="#"><u>M85049/55H18A</u></a> | <a href="#"><u>M85049/55H18N</u></a> |
| <a href="#"><u>M85049/55H18W</u></a> | <a href="#"><u>M85049/55H20A</u></a> | <a href="#"><u>M85049/55H20N</u></a>  | <a href="#"><u>M85049/55H20W</u></a> | <a href="#"><u>M85049/55H22A</u></a> | <a href="#"><u>M85049/55H22N</u></a> |
| <a href="#"><u>M85049/55H22W</u></a> | <a href="#"><u>M85049/55H24A</u></a> | <a href="#"><u>M85049/55H24N</u></a>  | <a href="#"><u>M85049/55H24W</u></a> | <a href="#"><u>M85049/55H28A</u></a> | <a href="#"><u>M85049/55H28N</u></a> |
| <a href="#"><u>M85049/55H28W</u></a> | <a href="#"><u>M85049/55N08A</u></a> | <a href="#"><u>M85049/55N08N</u></a>  | <a href="#"><u>M85049/55N08W</u></a> | <a href="#"><u>M85049/55N10A</u></a> | <a href="#"><u>M85049/55N10N</u></a> |
| <a href="#"><u>M85049/55N10W</u></a> | <a href="#"><u>M85049/55N12A</u></a> | <a href="#"><u>M85049/55N12N</u></a>  | <a href="#"><u>M85049/55N12W</u></a> | <a href="#"><u>M85049/55N14A</u></a> | <a href="#"><u>M85049/55N14N</u></a> |
| <a href="#"><u>M85049/55N14W</u></a> | <a href="#"><u>M85049/55N16A</u></a> | <a href="#"><u>M85049/55N16N</u></a>  | <a href="#"><u>M85049/55N16W</u></a> | <a href="#"><u>M85049/55N18A</u></a> | <a href="#"><u>M85049/55N18N</u></a> |
| <a href="#"><u>M85049/55N18W</u></a> | <a href="#"><u>M85049/55N20A</u></a> | <a href="#"><u>M85049/55N20N</u></a>  | <a href="#"><u>M85049/55N20W</u></a> | <a href="#"><u>M85049/55N22A</u></a> | <a href="#"><u>M85049/55N22N</u></a> |
| <a href="#"><u>M85049/55N22W</u></a> | <a href="#"><u>M85049/55N24A</u></a> | <a href="#"><u>M85049/55N24N</u></a>  | <a href="#"><u>M85049/55N24W</u></a> | <a href="#"><u>M85049/55N28A</u></a> | <a href="#"><u>M85049/55N28N</u></a> |
| <a href="#"><u>M85049/55N28W</u></a> | <a href="#"><u>M85049/55S08A</u></a> | <a href="#"><u>M85049/55S08N</u></a>  | <a href="#"><u>M85049/55S10N</u></a> | <a href="#"><u>M85049/55S12N</u></a> | <a href="#"><u>M85049/55S14N</u></a> |
| <a href="#"><u>M85049/55S16A</u></a> | <a href="#"><u>M85049/55S16N</u></a> | <a href="#"><u>M85049/55S18A</u></a>  | <a href="#"><u>M85049/55S20A</u></a> | <a href="#"><u>M85049/55S20N</u></a> | <a href="#"><u>M85049/55S22A</u></a> |
| <a href="#"><u>M85049/55S24A</u></a> | <a href="#"><u>M85049/55S24N</u></a> | <a href="#"><u>M85049/55S28A</u></a>  | <a href="#"><u>M85049/55S28N</u></a> | <a href="#"><u>M85049/55T08A</u></a> | <a href="#"><u>M85049/55T08N</u></a> |
| <a href="#"><u>M85049/55T08W</u></a> | <a href="#"><u>M85049/55T10A</u></a> | <a href="#"><u>M85049/55T10N</u></a>  | <a href="#"><u>M85049/55T10W</u></a> |                                      |                                      |