

CATALOG

➔ Cross Reference

[Competitive Products](#)
[Military Spec P/Ns](#)
[Tyco Brand P/Ns](#)

- ➔ [Part Number Search](#)
- ➔ [Document Search](#)
- ➔ [Product Type Search](#)
- ➔ [Product Family Search](#)
- ➔ [Alphabetical Search](#)
- ➔ [RoHS/ELV Compliance & Alternates](#)
- ➔ [CAD Model Search](#)
- ➔ [Brand Search](#)
- ➔ [Tool Search](#)
- ➔ [Multiple Part Comparison](#)
- ➔ [Lead Free Solutions](#)
- ➔ [Help/Glossary](#)

[Home](#)

e-bulletin newsletter
SUBSCRIBE NOW!
 click here

Terminal Block Products

➔ NEMA Terminal Blocks

BUCHANAN 211  [Active](#)
**Directive 2002/95/EC
Compliant**
[RoHS Compliant](#)**(Corporate P/N: 2-1437390-7)**[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information

General Information	eCommerce	Related Part Information
✦ General Info ✦ Sales Info	✦ Pricing ✦ Product Availability	✦ Tooling

Searchable Features:

Brand:	Buchanan
RoHS/ELV Compliance:	RoHS compliant, ELV compliant
Lead Free Solder Processes:	Not relevant for lead free process
Block Series:	200 Series
Product Type:	Terminal Block
Block Type:	Flat Base
Application:	Heavy Duty
Mount Style:	Direct Mount (Flat Base)
Contact Type:	Strap Screw
Voltage Rating (VAC):	600
Housing Material:	Phenolic (Unpainted)

Other Properties:

RoHS/ELV Compliance History:	Always was RoHS compliant
Pitch (mm [in]):	14.22 [0.560]
Screw Size:	10-32 Slotted Binding Head
Amperes (Amps.):	35.0
Temperature, Max. (°C):	150
Terminals Per Foot:	20

Wire Range (Solid and Stranded) [MCM] (AWG):	22-10
Blown Fuse Indicator:	Without
Blown Fuse Indicator Type:	None

[Copyright](#) and [Privacy Statement](#)
Visit [Tyco International Ltd.](#)

[[Products](#) | [Catalog](#) | [Brands](#) | [Industries](#) | [Commerce](#) | [Supplier](#) | [Contact Us](#) | [About](#) | [Home](#)]

