





PRODUCT NUMBER
SEE SHEET 2





spec ref		-		dr		Andrew Yong		2010/10/25		projection				MM		size		A3		scale		12:1	
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED		eng		Guo-Min Sun		2014/08/26				ecn no		ELX-N-18628-1									
ISO 406				chr		-		-															
ISO 1101				appr		Rick Bian		2014/08/26				product family		-		rel level		Released					
surface				linear		0.X		± -				title		MINITEK II R/R		dwg no		10065491		rev		M	
ISO 1302				0.XX		±0.25																	
				0.XXX		± -																	
		angular		0°		±3°		www.fci.com		cat. no.		-		Product - Customer Drw		sheet 1 of 3							

NOTES:

1. MATERIAL:
BODY : GLASS FILLED PCT UL 94V-0 NATURAL (BEIGE)
PIN : PHOSPHOR BRONZE
2. TOLERANCE UNLESS OTHERWISE NOTED ± 0.25
3. DIM 1.0 ± 0.15 FOR MOLDED SIDE(S) ONLY. IF SIDE(S) ARE BROKEN, DIM 1.5 MAX APPLIES.
4. RECESS APPLIES TO MOLDED SIDE(S) ONLY.
5. POLARISATION BY OMISSION OF PIN. POSITION REFER TO TABLE.
6. P/N 10065491-XXXT TO BE PACKED IN TUBE.
7. P/N 10065491-XXXTC TO BE PACKED IN TUBE WITH PICK-UP CAP INSTALLED IN THE CENTRE OF THE PRODUCT. SEE FIG 1.
8. P/N 10065491-XXXTR TO BE PACKED IN TAPE & REEL WITH PICK-UP CAP INSTALLED IN THE CENTRE OF THE PRODUCT. SEE FIG 1.
9. P/N 10065491-XXXTRN TO BE PACKED IN TAPE & REEL WITHOUT PICK-UP CAP.
10. PRODUCT PART NUMBER DESCRIPTIONS:
10065491-XXX LF
 LEAD FREE. SEE NOTE 11
 NO. OF POSITIONS (RANDOM)
11. 10065491-XXXLF IS SAME TO 10065491-XXX. THE SUFFIX 'LF' IS ADDED JUST FOR EASY LEAD FREE IDENTIFICATION.
12. THE HOUSING WILL WITHSTAND EXPOSURE TO 255°C PEAK TEMPERATURE FOR 10 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.

13. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.57mm MINIMUM THICK CIRCUIT BOARD.
14. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
15. A $\triangle$ SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION.
16. DIM C=DIM B+4.0



RECOMMENDED PAD LAYOUT

spec ref		-		dr		Andrew Yong		2010/10/25		projection		MM		size		A3		scale		5:1			
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED		eng		Guo-Min Sun		2014/08/26						ecn no		ELX-N-18628-1							
chr				-		-																	
appr				Rick Bian		2014/08/26		product family						-		rel level						Released	
surface				linear				title		MINITEK II R/R		dwg no		10065491		rev		M					
																				0.X		±-	
																				0.XX		±0.25	
ISO 1302		angular		0°		±3°		www.fci.com		cat. no.		-		Product - Customer Drw		sheet 3 of 3							