

DATA SHEET

KS08 HIGH TEMPERATURE SURFACE PROBE TYPE 'K'

HIGH TEMPERATURE SURFACE PROBE - Type 'K'

Description

This probe uses the straight handle for fine control The probe is designed for the measurement of surface temperatures with a very high temperature range.

Construction

Surface probe with copper sensing tip protected by a sprung stainless steel draught shield.:
Stainless Steel 316 (Food Grade)
2M curly polyurethane cable with moulded connector.

Sensor Features

➤ **TOTAL ENCAPSULATION TECHNIQUE FOR MAXIMUM STRENGTH AND DURABILITY.**

This results in a solid handle as opposed to a hollow handle. This is particularly important as there is often damage to the handles caused by excess heat. With a hollow handle it is possible to puncture the outer plastic and damage the sensor irreparably.

➤ **WATERPROOF HANDLE**

Due to the total encapsulation method used, all TME probe handles are completely waterproof.

➤ **TOUGH POLYURETHANE CABLE**

- Polyurethane cables are used in place of the standard polyurethane for the following reasons :-
- Greater retractability
- Enhanced memory of it's curl
- Non-Toxic
- Greater mechanical strength for durability
- 12 X 0.2mm wires used internally for greater strength.
- PTFE inner insulation for strength and retractability.

➤ **HIGH ACCURACY THERMOCOUPLE MATERIAL THROUGHOUT**

Type 'K' Thermocouple : Class I ($\pm 0.1.5^{\circ}\text{C} \pm 0.25\%$)

➤ **POLYPROPYLENE HANDLES**

Polypropylene is an extremely tough and durable material, commonly used for milk crates, it has good low temperature performance and a relatively high melt temperature. It performs exceptionally well under chemical attack.

- | | |
|--|-----------------------|
| ➤ WIDE AMBIENT TEMPERATURE SPECIFICATION | : -30 TO 50 °C |
| ➤ TIME RESPONSE (96% of value on clean metal) | : 3.0 Secs |
| ➤ MEASUREMENT RANGE | : 0 TO 1100 °C |

Cross-reference for compatible instruments

Suitable instruments for use with this probe

TME PART No	DESCRIPTION	APPLICATION
MM2000	SINGLE INPUT INSTRUMENT	HIGH ACCURACY TEMPERATURE MEASUREMENT
MM2010	MAX / MIN HOLD INSTRUMENT	HIGH ACCURACY INSTRUMENT WITH MAX, MIN AND HOLD FEATURES
MM2020	DIFFERENTIAL INSTRUMENT	DUAL INPUT INSTRUMENT FOR DIFFERENTIAL MEASUREMENTS
MM2030	THERMOCOUPLE SIMULATOR	HIGH ACCURACY SIMULATOR WITH MEASUREMENT FACILITY