




PANEL THICKNESS	X dimension
0.75-1.25 [0.30-.049]	19.2-.02 [7.561]
1.25-2.0 [0.49-.079]	19.4-.02 [7.641]
2.0-3.0 [0.79-.118]	19.8-.02 [7.801]



CIRCUIT: DPST

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25

3. RATING:

6A @250VAC;9A @125VAC (UL, CSA, VDE)
4(1)A @250VAC

4. MATERIAL:

CONTACT SURFACE: Coin Silver, Silver Plate
TERMINAL: Copper Alloy W/ Silver Plate.

5. CONTACT RESISTANCE: 20MILLIOHMS TYP. INITIAL
6. INSULATION RESISTANCE: 1000MEGOHMS
7. DIELECTRIC STRENGTH:
>1500V RMS min. @SEA LEVEL
>3000V RMS @SEA LEVEL
8. MECHANICAL LIFE: 50,000 CYCLES.
9. ELECTRICAL LIFE: 10,000 CYCLES.

E-SWITCH®

B	11330	REVISED & REDRAWN	10/01/01	CJB	TITLE				
REV.	ECN No.	DESCRIPTION	DATE	CHKD	R1973B BLK BLK EFO				
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					SCALE	DATE	DR	DWG	REV
					1.5:1	10/01/01	CB	M400009	B