




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
A I	-		D7	REVISED PER ECR-17-014951	16OCT2017	BDA	KR

D


C

B

A




Montageausschnitt/PANEL CUT OUT
Bestückungsseite/LOADING SIDE



Bemerkungen
NOTES

- Geeignet für UMNL Stift- und Buchsenkontakte
BEEN SUITABLE FOR UMNL PIN- AND SOCKET CONTACTS
- Empfohlene Blechstärke 0.75 - 2.3 mm
RECOMMEND SHEET METAL THICKNESS 0.75 - 2.3 mm
- Gehäuse muß in Stanzrichtung eingeführt werden
HOUSING MUST BE INTRODUCED TO PUNCHING DIRECTION
- Für verschlüsseltes Einsetzen der Gehäuse
FOR CODED USING OF THE HOUSINGS
- Position von Kammer 1 bei verschlüsseltem Einsetzen
POSITION OF CAVITY 1 FOR CODED USING
- Neues Material (Phosphor und Halogen frei)
NEW MATERIAL (PHOSPHORUS AND HALOGENEOUS FREE)
- Hersteller-Logo und Ländercode
nach AMP-Spez. 115-18016
BRANDNAME AND MANUFACTURING LOCATION CODE
ACCORDING SPEC. 115-18016
- Nur für italienische Produktion
ITALIAN PRODUCTION ONLY
- Glühdrahtprüfung 750 ° (ohne Flamme) nach IEC 60335-1 Ausgabe 06/2001
GWT 750 ° (WITHOUT FLAME) ACC. 60335-1 EDITION 06/2001
- Schüttgut in Beutel und Versandkarton PN 973 057-2
BULK PACKAGING IN PLASTIC BAG AND CORRUGATED SHIPPING BOX PN 973 057-2
- Farbe der Gehäuse kann anhand klar, grün oder gelb wegen hygroskopischen Natur resin.
However es hat keinen Einfluss auf die Form, Passform und Funktion der Produktpalette.
COLOR OF HOUSINGS MAY RANGE FROM CLEAR TO GREEN OR YELLOW DUE TO HYGROSCOPIC NATURE OF RESIN.
HOWEVER IT DOESN'T AFFECT THE FORM, FIT AND FUNCTION OF THE PRODUCT.
- DIMENSIONS SHOWN REPRESENT PRODUCT IN DRY, AS MOLDED, CONDITION. ADDITIONAL 2% GROWTH DUE TO SUBSEQUENT MOISTURE ABSORPTION MAY OCCUR AND SHOULD BE ACCOUNTED FOR.



1:1

	926647-8/9	PA6 UL 94 V-2	natur/ NATURAL
OBSOLETE	926647-7/8	PA6.6 UL94 V-2	schwarz/BLACK
OBSOLETE	926647-6/8	PA6.6 UL94 V-2	grün/GREEN
OBSOLETE	926647-5/8	PA6.6 UL94 V-2	rot/RED
OBSOLETE	926647-4	PA6.6 UL94 V-0	natur/NATURAL
	926647-3	PA6.6 UL94 V-0	6 natur/NATURAL
	926647-2	PA6.6 UL94 V-0	6 schwarz/BLACK
	926647-1	PA6.6 UL94 V-2	11 natur/NATURAL
	PART NO.	MATERIAL	COLOR

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Abraham.G. 12MAY03	TE Connectivity			
		CHK Kampmann.H. 13MAY03				
		APVD Bleicher.M. 14APR2004	NAME 15-pol. UMNL Aufnahmegehäuse UMNL 15-WAY CAP HOUSING			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC 108-1031			
		0 PLC/ ± 1 PLC/ ± 2 PLC/ ±0.2 3 PLC/ ± 4 PLC/ ± ANGLES ±	APPLICATION SPEC 114-18011			
MATERIAL		FINISH	WEIGHT 11.5 g			
see table		see table	CUSTOMER DRAWING			
			SCALE 2:1	SHEET 1 OF 1	REV D7	