

Customer Information Sheet

DRAWING No.: P70-2200045

SHEET 2 OF 2


IF IN DOUBT - ASK

(C)


NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm

**NOTES:**

- IF ASSEMBLING PIN INTO MOULDING:
RECOMMENDED HOLE SIZE = $\phi 1.56$ MIN.
RECOMMENDED MATERIAL = GLASS FILLED PA46.
- ALL PRODUCTS ARE RoHS COMPLIANT.

**RECOMMENDED PCB
PAD LAYOUT****SPECIFICATION:****MATERIAL:**

BODY & PLUNGER = BRASS
SPRING = STAINLESS STEEL WIRE

PLATING:

BODY = 0.1μ GOLD OVER 1.4μ NICKEL
PLUNGER = 0.4μ GOLD OVER 1.4μ NICKEL

ELECTRICAL:

CONTACT RESISTANCE = $30m\Omega$ MAX
CURRENT RATING = 2.0A

MECHANICAL:


FORCE AT NORMAL HEIGHT = $0.98N \pm 0.19N$
DURABILITY = 10,000 CYCLES

ENVIRONMENTAL:


OPERATING TEMPERATURE = $-40^{\circ}C$ TO $85^{\circ}C$

PACKING:


BAG



MAXIMUM WORKING
HEIGHT



NORMAL WORKING
HEIGHT



MINIMUM WORKING
HEIGHT/MAX
ALLOWED TRAVEL

SB	I	07.04.16	-----
NAME	ISS.	DATE	C/NOTE
APPROVED:		S.BENNETT	
CHECKED:		M.PLESTED	
DRAWN:		S.BENNETT	
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN

www.harwin.com
technical@harwin.com

THIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.

TOLERANCES

X. = $\pm 1mm$
X.X = $\pm 0.50mm$
X.XX = $\pm 0.10mm$
X.XXX = $\pm 0.01mm$

ANGLES = $\pm 5^{\circ}$

UNLESS STATED

MATERIAL:

SEE ABOVE

FINISH: SEE ABOVE

S/AREA:

mm²

TITLE:

SMT SPRING LOADED POGO PIN
WITH PEG

DRAWING NUMBER:

P70-2200045

SHT
2
OF 2