

# EB51F3D20N-20.480M

[Click part number to visit Part Number Details page](#)

## REGULATORY COMPLIANCE (Data Sheet downloaded on May 19, 2017)



## ITEM DESCRIPTION

Temperature Compensated Quartz Crystal Clock Oscillators TCXO HCMOS/TTL (CMOS) 5.0Vdc 14-Pin DIP Metal Thru-Hole 20.480MHz  $\pm 2.0$ ppm Maximum -30°C to +75°C

## ELECTRICAL SPECIFICATIONS

|                                       |                                                                                                                           |
|---------------------------------------|---------------------------------------------------------------------------------------------------------------------------|
| Nominal Frequency                     | 20.480MHz                                                                                                                 |
| Frequency Stability                   | $\pm 2.0$ ppm Maximum (Inclusive of Operating Temperature Range)                                                          |
| Frequency Stability vs. Input Voltage | $\pm 0.3$ ppm Maximum ( $\pm 5\%$ )                                                                                       |
| Frequency Stability vs. Load          | $\pm 0.2$ ppm Maximum ( $\pm 2$ pF)                                                                                       |
| Aging at 25°C                         | $\pm 1$ ppm/Year Maximum                                                                                                  |
| Operating Temperature Range           | -30°C to +75°C                                                                                                            |
| Supply Voltage                        | 5.0Vdc $\pm 5\%$                                                                                                          |
| Input Current                         | 30mA Maximum                                                                                                              |
| Output Voltage Logic High (Voh)       | 2.4Vdc Minimum w/TTL Load, Vdd-0.5Vdc Minimum w/HCMOS Load                                                                |
| Output Voltage Logic Low (Vol)        | 0.4Vdc Maximum w/TTL Load, 0.5Vdc Maximum w/HCMOS Load                                                                    |
| Rise/Fall Time                        | 10nSec Maximum (Measured at 0.4Vdc to 2.4Vdc w/TTL Load, 20% to 80% of waveform w/HCMOS Load)                             |
| Duty Cycle                            | 50 $\pm 10$ (%) (Measured at 1.4Vdc w/TTL Load, at 50% of waveform w/HCMOS Load)                                          |
| Load Drive Capability                 | 10TTL Load or 15pF HCMOS Load Maximum                                                                                     |
| Output Logic Type                     | CMOS                                                                                                                      |
| Control Voltage                       | None (No Connect on Pin 1)                                                                                                |
| Internal Trim                         | $\pm 3$ ppm Minimum (Top of Can)                                                                                          |
| Modulation Bandwidth                  | 10kHz Minimum (Measured at -3dB with a Control Voltage of 2.5Vdc)                                                         |
| Input Impedance                       | 10kOhms Typical                                                                                                           |
| Phase Noise                           | -70dBc at 10Hz Offset, -100dBc at 100Hz Offset, -130dBc at 1kHz Offset, -140dBc at 10kHz Offset, -145dBc at 100kHz Offset |
| Storage Temperature Range             | -40°C to +85°C                                                                                                            |


## ENVIRONMENTAL & MECHANICAL SPECIFICATIONS

|                              |                                                              |
|------------------------------|--------------------------------------------------------------|
| Fine Leak Test               | MIL-STD-883, Method 1014 Condition A (Internal Crystal Only) |
| Gross Leak Test              | MIL-STD-883, Method 1014 Condition C (Internal Crystal Only) |
| Lead Integrity               | MIL-STD-883, Method 2004                                     |
| Mechanical Shock             | MIL-STD-202, Method 213 Condition C                          |
| Resistance to Soldering Heat | MIL-STD-202, Method 210                                      |
| Resistance to Solvents       | MIL-STD-202, Method 215                                      |
| Solderability                | MIL-STD-883, Method 2003                                     |
| Temperature Cycling          | MIL-STD-883, Method 1010                                     |
| Vibration                    | MIL-STD-883, Method 2007 Condition A                         |

EB51F3D20N-20.480M

[Click part number to visit Part Number Details page](#)

MECHANICAL DIMENSIONS (all dimensions in millimeters)



| PIN | CONNECTION     |
|-----|----------------|
| 1   | No Connect     |
| 2   | Case Ground    |
| 3   | Output         |
| 4   | Supply Voltage |

| LINE | MARKING                                                                                     |
|------|---------------------------------------------------------------------------------------------|
| 1    | ECLIPTEK                                                                                    |
| 2    | 20.480M                                                                                     |
| 3    | XXYYZZ<br>XX=Ecliptek Manufacturing Code<br>Y=Last Digit of the Year<br>ZZ=Week of the Year |

EB51F3D20N-20.480M [Click part number to visit Part Number Details page](#)



OUTPUT WAVEFORM



EB51F3D20N-20.480M

[Click part number to visit Part Number Details page](#)

Test Circuit for TTL Output

| Output Load Drive Capability | R <sub>L</sub> Value (Ohms) | C <sub>L</sub> Value (pF) |
|------------------------------|-----------------------------|---------------------------|
| 10TTL                        | 390                         | 15                        |
| 5TTL                         | 780                         | 15                        |
| 2TTL                         | 1100                        | 6                         |
| 10LSTTL                      | 2000                        | 15                        |
| 1TTL                         | 2200                        | 3                         |

Table 1: R<sub>L</sub> Resistance Value and C<sub>L</sub> Capacitance Value Vs. Output Load Drive Capability



- Note 1: An external 0.1μF low frequency tantalum bypass capacitor in parallel with a 0.01μF high frequency ceramic bypass capacitor close to the package ground and V<sub>DD</sub> pin is required.
- Note 2: A low capacitance (<12pF), 10X attenuation factor, high impedance (>10Mohms), and high bandwidth (>300MHz) passive probe is recommended.
- Note 3: Capacitance value C<sub>L</sub> includes sum of all probe and fixture capacitance.
- Note 4: Resistance value R<sub>L</sub> is shown in Table 1. See applicable specification sheet for 'Load Drive Capability'.
- Note 5: All diodes are MMBD7000, MMBD914, or equivalent.

**EB51F3D20N-20.480M** [Click part number to visit Part Number Details page](#)**Test Circuit for CMOS Output**

Note 1: An external 0.1 $\mu$ F low frequency tantalum bypass capacitor in parallel with a 0.01 $\mu$ F high frequency ceramic bypass capacitor close to the package ground and  $V_{DD}$  pin is required.

Note 2: A low capacitance (<12pF), 10X attenuation factor, high impedance (>10Mohms), and high bandwidth (>300MHz) passive probe is recommended.

Note 3: Capacitance value  $C_L$  includes sum of all probe and fixture capacitance.

EB51F3D20N-20.480M [Click part number to visit Part Number Details page](#)



Recommended Solder Reflow Methods



Low Temperature Solder Bath (Wave Solder)

|                                     |                                                       |
|-------------------------------------|-------------------------------------------------------|
| TS MAX to TL (Ramp-up Rate)         | 5°C/Second Maximum                                    |
| Preheat                             |                                                       |
| - Temperature Minimum (TS MIN)      | N/A                                                   |
| - Temperature Typical (TS TYP)      | 150°C                                                 |
| - Temperature Maximum (TS MAX)      | N/A                                                   |
| - Time (ts MIN)                     | 30 - 60 Seconds                                       |
| Ramp-up Rate (TL to TP)             | 5°C/Second Maximum                                    |
| Time Maintained Above:              |                                                       |
| - Temperature (TL)                  | 150°C                                                 |
| - Time (tL)                         | 200 Seconds Maximum                                   |
| Peak Temperature (TP)               | 245°C Maximum                                         |
| Target Peak Temperature (TP Target) | 245°C Maximum 1 Time / 235°C Maximum 2 Times          |
| Time within 5°C of actual peak (tP) | 5 Seconds Maximum 1 Time / 15 Seconds Maximum 2 Times |
| Ramp-down Rate                      | 5°C/Second Maximum                                    |
| Time 25°C to Peak Temperature (t)   | N/A                                                   |
| Moisture Sensitivity Level          | Level 1                                               |

Low Temperature Manual Soldering

185°C Maximum for 10 Seconds Maximum, 2 times Maximum. (Temperatures listed are applied to device leads only.)

High Temperature Manual Soldering

260°C Maximum for 5 Seconds Maximum, 2 times Maximum. (Temperatures listed are applied to device leads only.)

Low Temperature Solder Bath (Wave Solder) Note 1

Device is non-hermetic; Post reflow aqueous wash is not recommended

# EB51F3D20N-20.480M

[Click part number to visit Part Number Details page](#)

## Low Temperature Solder Bath (Wave Solder) Note 2

---

Temperatures shown are applied to back of PCB board and device leads only.