

OLED DISPLAY MODULE

Application Notes

PRODUCT NUMBER	DD-12833BE-1A with EVK board
-------------------	------------------------------




TABLE OF CONTENTS

1	EVK SCHEMATIC.....	4
2	SYMBOL DEFINITION	5
3	TIMING CHARACTERISTICS	6
3.1	MODE (I ² C INTERFACE).....	6
3.2	SERIAL PERIPHERAL INTERFACE.....	8
3.3	MODE 80-SERIES (PARALLEL INTERFACE).....	9
3.4	MODE 68-SERIES (PARALLEL INTERFACE).....	11
4	CONNECTION BETWEEN OLED AND EVK	13
5	POWER ON SEQUENCE:	15
6	HOW TO USE THE DD-12833BE-1A.....	16
6.1	RECOMMENDED INITIAL CODE	17

Product No.	DD-12833BE-1A	REV.B

Page	2 / 18
------	--------


REVISION RECORD

Rev.	Date	Page	Chapt.	Comment	ECR no.
A	16-Mar-06			First Issue	
B	13-OCT-06	4 6~11 17	1 3 6	Update Schematic ; The EVK can use 80xx 、 68xx 、 SPI and I2C IF Initial code update	ECR_DE054

Product No.	DD-12833BE-1A	REV.B

Page	3 / 18
------	--------

1 EVK Schematic



Product No.	DD-12833BE-1A	REV.B

Page	4 / 18
------	--------

2 Symbol Definition

D0-D7 : These pins are 8-bit bi-directional data bus to be connected to the MCU's data bus.

CS#: This pin is the chip select input. The chip is enabled for MCU communication only when CS is pulled low.

SEL0, SEL1: These input pins are to configure MCU interface selection by appropriate logic settings as follows:

SEL1	SEL2	Interface
0	0	I2C(Standard or fast)
0	1	Serial
1	0	Parallel(68xx)
1	1	Parallel(80xx)

Table 1: MCU Interface Selection Setting

E/RD# : This pin is MCU interface input. When interfacing to a 6800-series microprocessor, this pin is used as the Enable (E) signal. Read/write operation is initiated when this pin is pulled high and the chip is selected.

When connecting to an 8080-microprocessor, this pin receives the Read (RD) signal. Data read operation is initiated when this pin is pulled low and the chip is selected. When serial interface is selected, this pin E (RD) must be connected to VSS.

R/W# : This pin is MCU interface input. When interfacing to a 6800-series microprocessor, this pin is used as Read/Write (R/W) selection input. Read mode will be carried out when this pin is pulled high and write mode when low.

When 8080 interface mode is selected, this pin is the Write (WR) input. Data write operation is initiated when this pin is pulled low and the chip is selected. When serial interface is selected, this pin R/W must be connected to VSS.

D/C# : This pin is Data/Command control pin. When the pin is pulled high, the data at D0-D7 is treated as display data. When the pin is pulled low, the data at D0-D7 is transferred to the command register. For detail relationship to MCU interface signals, please refer to the timing characteristics diagrams at following pages and datasheet.

RES# : This pin is reset signal input. When the pin is low, initialization of the chip is executed.

HV : This is the most positive voltage supply pin of the chip.

LV : Power supply pin for logic operation of the driver.

GND : Power supply ground.

Product No.	DD-12833BE-1A	REV.B

Page	5 / 18
------	--------

3 Timing characteristics

3.1 Mode (I²C Interface)

Write Mode




Figure 1 : I²C Interface Timing Diagram for Register Write




Figure 2 : I²C Interface Timing Diagram for RAM Write

Item	Description	Min.	Typ.	Max.	Unit
Tscl_cycle		2.5			μs
Tscl_low / Tscl_high		100/100			ns
Tscl_rise / Tscl_fall				15/15	ns
Tdatas / Tdatah	Data setup & hold	100/100			ns
Tcs0s / Tcs0h	Chip Select setup & hold	120/120			ns

Table2: I²C Interface Write Timing

Product No.	DD-12833BE-1A	REV.B

Page	6 / 18
------	--------

Read Mode




Figure 3 : I²C Interface Read Timing Diagram (Register only)

Item	Description	Min.	Typ.	Max.	Unit
Tscl_cycle		2.5			μs
Tscl_low / Tscl_high		100/100			ns
Tscl_rise / Tscl_fall				15/15	ns
Tdatas / Tdatah	Data setup & hold	100/100			ns
Tcs0s / Tcs0h	Chip Select setup & hold	120/120			ns

Table3 : I²C Interface Read Timing (Register only)

Product No.	DD-12833BE-1A	REV.B

Page	7 / 18
------	--------

3.2 Serial Peripheral interface




Figure 4 : Serial Peripheral Interface Timing Diagram (Write Mode)




Figure 5 : Serial Peripheral Interface Timing (Write Mode)

Item	Description	Min.	Typ.	Max.	Unit
Tclk_cycle		250			ns
Tclk_low / Tclk_high		100/100			ns
Tclk_rise / Tclk_fall				15/15	ns
Tsdins / Tsdinh	SDIN setup & hold	100/100			ns
Tsdcs / Tsdch	SD/C setup & hold	150/150			ns
Tcs0s / Tcs0h	Chip Select setup & hold	150/150			ns

Table4 : Serial Peripheral Interface Timing (Write Mode)

Product No.	DD-12833BE-1A	REV.B

Page	8 / 18
------	--------

3.3 Mode 80-series (Parallel Interface)

Write Mode




Figure 6: 80-series MPU 8-bit parallel interface Timing Diagram (write Mode)

Item	Description	Min.	Typ.	Max.	Unit
Twr_low		60			ns
Twr-rise / Twr_fall				15/15	ns
Tdatas / Tdatah	Data Address setup & hold	25/25			ns
Tsdcs / Tsdch	SD/C setup & hold	TBD	60/60		ns
Tcs0s / Tcs0h	Chip Select setup & hold	TBD	120/60		ns

Table 5: 80-series MPU 8-bit parallel interface Timing Diagram (write Mode)

Product No.	DD-12833BE-1A	REV.B

Page	9 / 18
------	--------

Read Mode




Figure 7: 80-series MPU 8-bit parallel interface Timing Diagram (Read Mode)

Item	Description	Min.	Typ.	Max.	Unit
Trd_low		120			ns
Trd_rise / Trd_fall				15/15	ns
Trddatout	Data out from $\overline{RD}$ falling edge (with CL = 100pF)		20	TBD	ns
Trddathiz	Data Hiz from $\overline{RD}$ rising edge (with CL = 100pF)			TBD	ns
Tcs0dathiz	Data Hiz from $\overline{CS0}$ rising edge			TBD	
Tcs0s / Tcs0h	Chip Select setup & hold	120/60			ns

Table 6: 80-series MPU 8-bit parallel interface Timing Diagram (Read Mode)

Product No.	DD-12833BE-1A	REV.B

Page	10 / 18
------	---------

3.4 Mode 68-series (Parallel Interface)

Write Mode




Figure 8 : 8-Bit Parallel 68XX interface Timing Diagram (Write Mode)

Item	Description	Min.	Typ.	Max.	Unit
Te_cycle		300			ns
Te_low / Te_high		60/60			ns
Te_rise / Te_fall				15/15	ns
Twrs / Twrh	Write Data setup & hold	TBD	50/50		ns
Tdatas / Tdatah	Data Address setup & hold	25/25			ns
Tsdc / Tsdch	SD/C setup & hold	TBD	60/60		ns
Tcs0s / Tcs0h	Chip Select setup & hold	TBD	120/60		ns

Table7 : 8-bit Parallel 68XX Interface Timing (Write Mode)

Product No.	DD-12833BE-1A	REV.B

Page	11 / 18
------	---------

Read Mode




Figure 9: 8-Bit Parallel 68XX interface Timing Diagram for Register Read (only)

Item	Description	Min.	Typ.	Max.	Unit
Te_cycle		300			ns
Te_low / Te_high		120/60			ns
Te_rise / Te_fall				15/15	ns
Trds	READ setup to E rising edge (with CL = 100pF) A	TBD	50		ns
Trdh	READ hold from E falling edge (with CL = 100pF)	TBD	50		ns
Tedatout	Data out from E rising edge	-	20	TBD	ns
Tedathiz	Data Hiz from E falling edge	-		TBD	ns
Tcs0dathiz	Data Hiz from CS0 rising edge	-		TBD	ns
Tcs0s / Tcs0h	Chip Select setup & hold	120/60			ns

Table 15: 8-bit Parallel 68XX Interface Timing (Read Mode)




Figure 12: control MCU (not supplied) connected with EVK

Note 1 : It is the external most positive voltage supply. In this sample is connected to power supply.

Note 2: Pins SEL0 and SEL1 is to select different types of interface

Product No.	DD-12833BE-1A	REV.B


Page	14 / 18
------	---------

5 Power on Sequence:

To protect the OLED panel and extend the panel life time, the driver IC power up/down routine should include a delay period between high voltage and low voltage power sources during turn on/off. Such that panel has enough time to charge up or discharge before/after operation.


Power up Sequence:

1. Power up V_{DD_D}
2. Send Display off command
3. Driver IC initial Settings
4. Clear Screen
5. Power up V_{PP}
6. Delay 100ms (when V_{DD_D} is stable)
7. Send Display on command



Power down Sequence:


1. Send Display off command
2. Power down V_{PP}
3. Delay 100ms (when V_{PP} reaches 0 and panel is completely discharges)
4. Power down V_{DD_D}



Product No.	DD-12833BE-1A	REV.B

Page	15 / 18
------	---------

6 How to use the DD-12833BE-1A



Product No.	DD-12833BE-1A	REV.B

Page	16 / 18
------	---------

6.1 Recommended Initial code

```
void Initial_ic(void)
{
    E_RD=1;
    D_C=0;
    R_W=0;
    CS=0;
    Reset_ST8102();
    write_c (0xCE);
    write_c (0xFF);
    write_c (0x2b); //Set External MOS Enable
    write_c (0xC2); //Set Horizontal Left Shift Limit
    write_c (0x0); //no shift
    write_c (0xC0); //Set Horizontal Right Shift Limit
    write_c (0x0); //no shift
    write_c (0xC4); //Set Horizontal Shift Selection
    write_c (0x0); //no shift
    write_c (0x90); //Set Screen Saver Horizontal Speed
    write_c (0xA0); //Set Horizontal/Vertical Disable
    write_c (0xA2); //Set Inverse Disable
    write_c (0x80);
    write_c (0x13); //Set Clock Control,OSC Enable
    write_c (0xD6); //Use Test Pattern Disable
    write_c (0xD8); //Select Test Pattern
    write_c (0xB3); //Set Mirror Effect Selection: MSB is bit0,Right to Left,Top to Bottom
    write_c (0xD0);
    write_c (0x0); //Set Parallel,Selective discharge
    write_c (0x26); //Set Pre-charge & Dis-charge
    write_c (0x2C); //Set Internal Pre_charge Supply
    write_c (0xB8); //Set RAM Access in ROW Mode Disable
    write_c (0xCC); //Set Row Block Blanking
    write_c (0x1F); //Set Duty=40
    write_c (0x28); //Set In High Impedance state
    write_c (0x38); //Row Mapping Selection
    write_c (0x2E); //Set Internal row-off supply
    write_c (0xBA); //Set utonatic Scan row blocks
    write_c (0x18); //Set External supply on Vpp (No use DC-DC)
    write_c (0xC8); // 'Set Vertical Bottom Shift Limit is default
    write_c (0xC6); // 'Set Vertical Top Shift Limit is default
    write_c (0xA6); // 'Vpp Clamp Value=8
    write_c (0x14);
    write_c (0xCA); // 'Set Vertical Shift Selection is default
    write_c (0x0);
    write_c (0x98); // Set Screen Saver Vertical Speed is default
    write_c (0x0);
    write_c (0xAF); // 'Display On
}

void write_c(unsigned char out_command)
{
    R_W=0;
    CS=0;
    D_bus=out_command;
    D_C=0;
    R_W=1;
    CS=1;
    D_C=1;
}
```

Product No.	DD-12833BE-1A	REV.B

Page	17 / 18
------	---------

```

void write_d(unsigned char out_data)
{
    R_W=0;
    CS=0;
    D_bus=out_data;
    D_C=1;
    R_W=1;
    CS=1;
    D_C=0;
}
void Reset_ST8102(void)
{
    RES=0;
    Delay_1ms(100);
    RES=1;
}
void Delay_1ms(int Cycle)
{
    unsigned int i,k;
    for (i=0 ;i<Cycle;i++)
        for(k=0;k<0x5f;k++);
}
Write_c= Write Command

```

Product No.	DD-12833BE-1A	REV.B

Page	18 / 18
------	---------