





THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO CW INDUSTRIES INCORPORATED AND ITS AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN CW INDUSTRIES PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM CW INDUSTRIES INCORPORATED, SOUTHAMPTON, PENNSYLVANIA USA.

Rating		20A 125VAC 10A 250VAC 16A 125VAC 3/4HP 10A 277VAC 3/4HP 21A 14VDC	cULus	Mounting Hole		Circuit Diagram
Configured For		250VAC 277VAC				
Contact Resistance		50m ohm Max.	Thickness(mm)		X(mm)	Y(mm)
Insulation Resistance		DC 500V 100M ohm Min.	0.75~1.25		21.2+0.1	36.6 ^{+0.2} ₋₀
Dielectric Strength		AC 1500V 1 minute	1.25~2.0			36.8 ^{+0.2} ₋₀
Operation Temperature		-20°~85°	2.0~3.0			37.0 ^{+0.2} ₋₀
Switch Function		3P SPST ON-OFF LAMP Dependent				
Lamp Type		Neon 250VAC 277VAC w/resistor				



OFF ON



MATERIAL:



Frame: Nylon 66, Black

Actuator: Nylon 66 with 33%GF, Black

Lens: PC, Red

Lamp: Neon, Red

Water proof and dust proof to fit IP-56



Date Code

RoHS Compliant

3 Added Configured for to rating, Dependent to function & Lamp Type. 1/23/12.

2 20A 125VAC 10A 250VAC was 20A 125VAC 10A 25VAC in Rating. 1/24/11.

CW INDUSTRIES
Southampton, Pa. 18966
Tel 215.355.7080/www.cwind.com

Date Drawn: 1/24/11

Rev. 3

Unit: mm

Checked By: *G. Gold*

Title:
ROCKER SWITCH

CW P/N:
GRB260A401BBRN2