



## MATERIALS


BODY	BRASS NICKEL PLATED
CONTACT	GOLD PLATED
INSULATOR	PTFE




1. TRIM CABLE AS SHOWN. TIN CENTER CONDUCTOR. SLIDE NUT ONTO CABLE.





2. SLIDE COMPRESSION WASHER OVER THE BRAID UNTIL IT BOTTOMS OUT ON THE CABLE JACKET. FAN OUT BRAID RADIALLY AGAINST THE COMPRESSION WASHER BY ROTATING THE CABLE DIELECTRIC.



3. SLIDE FERRULE ONTO CABLE, OVER DIELECTRIC AND UNDER BRAID. PUSH INTO WASHER UNTIL IT STOPS. IF NECESSARY TRIM EXCESS BRAID FLUSH WITH SURFACE OF COMPRESSION WASHER AND FLANGE OF FERRULE.



4. INSTALL SMALL INSULATOR OVER CABLE DIELECTRIC. SOLDER CONTACT TO CENTER CONDUCTOR. INSERT CABLE ASSEMBLY INTO BODY AND TIGHTEN.



PASTERNACK ENTERPRISES, INC.

P.O BOX 16759, IRVINE, CA 92623  
PHONE (949) 261-1920 FAX (949) 261-7451

WEB ADDRESS: [www.pasterнак.com](http://www.pasterнак.com)  
E-MAIL ADDRESS: [sales@pasterнак.com](mailto:sales@pasterнак.com)

COAXIAL & FIBER OPTICS

DWG TITLE

**PE4268**

DES. SMB JACK, CLAMP ATTACHMENT FOR  
RG174, RG188 & RG316

REV. A FSCM NO. 53919

CAD FILE 050608

SCALE N/A

SIZE A 127

### NOTES:

1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES.