

NOTES:

1) MATERIAL:

"BLANK": NYLON 6/6, 94V-2, COLOR: NATURAL.

210 : NYLON 6/6, 94V-0, COLOR: NATURAL.

400 : NYLON 6/6, 94V-0, COLOR: BLACK.

2) FINISH: NOT APPLICABLE




3) PRODUCT SPECIFICATION: PS-5556-001

4) PACKAGING SPECIFICATION: PK-5557-002

5) PART MATES WITH MOLEX PLUG *5559-*, VERTICAL HEADER *5566-*, AND RIGHT-ANGLE HEADER *5569-*,.

6) PART IS FOR USE WITH MOLEX FEMALE TERMINAL *5556-*,.

7) PART CONFORMS TO CLASS "B" REQUIREMENTS OF COSMETIC SPECIFICATION PS-45499-002.

OPTIONAL ENGINEERING
NUMBER LOCATION



LEGEND:

CKT. SIZE
(02, 04-12)RECEPTACLE
(SINGLE ROW)MATERIAL OPTION:
(SEE NOTE 1)

COLOR:

"BLANK" = NATURAL

"BL" = BLACK



ADD TOL TO 6.0 DIM EC NO: UCP2014-0298 DRAWN: NGUYEN 2013/08/06 CHKD: J.BELL 2013/08/06 APPR: F.S.MITH 2013/08/16 REV	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE IN/MM		SCALE 4:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	MINI-FIT JR. RECEPTACLE (SINGLE ROW) molex DOCUMENT NO. SD-5557-NR2* SHEET NO. 1 OF 1	
			 F=0  F=0  F=0		mm	INCH	DRAWN BY KSS	DATE 2/15/89	TITLE			
				4 PLACES	± ---	± ---	CHECKED BY RJF	DATE 2/15/89				
				3 PLACES	± ---	± .010	APPROVED BY F.S.MITH	DATE 2012/05/04				
				2 PLACES	± .25	± .015	MATERIAL NO.					
				1 PLACE	± .38	± ---	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS					
			0 PLACE	± ---	± ---	SIZE C THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
			ANGULAR ±1/2°									