



## Features

- Carbon element
- Red, orange, green, amber and white LED colors
- Center detent option
- Assortment of resistance tapers
- Various travel lengths
- Various lever sizes



## PTL Series Slide Potentiometer w/LED

### Electrical Characteristics

|                                 |                           |
|---------------------------------|---------------------------|
| Standard Resistance Range       | ..... 1K ohms to 1 megohm |
| Standard Resistance Tolerance   | ... ±20 %                 |
| End Resistance                  |                           |
| 20 mm Travel                    | ..... 10 ohms max.        |
| 30 mm Travel                    | ..... 20 ohms max.        |
| 45 mm Travel                    | ..... 20 ohms max.        |
| 60 mm Travel                    | ..... 30 ohms max.        |
| Insulation Resistance @ 250 VDC | ..... 100 megohms min.    |
| Dielectric Withstanding Voltage | ..... 300 VAC             |
| Standard Taper                  | ..... Linear, Audio       |
| Power Rating - Linear           |                           |
| 20 mm Travel                    | ..... 0.05 watt           |
| 30 mm Travel                    | ..... 0.1 watt            |
| 45 mm Travel                    | ..... 0.125 watt          |
| 60 mm Travel                    | ..... 0.2 watt            |
| Power Rating - Audio            |                           |
| 20 mm Travel                    | ..... 0.025 watt          |
| 30 mm Travel                    | ..... 0.05 watt           |
| 45 mm Travel                    | ..... 0.06 watt           |
| 60 mm Travel                    | ..... 0.1 watt            |
| Slider Noise                    | ..... 200 mV max.         |

### Environmental Characteristics



|                             |                        |
|-----------------------------|------------------------|
| Operational Life            | ..... 15,000 cycles    |
| TR Shift                    | ..... ±15 %            |
| Operating Temperature Range | ..... -10 °C to +55 °C |
| Resistance to Solder Heat   | ..... ±5 %             |

### Mechanical Characteristics


|                     |                               |
|---------------------|-------------------------------|
| Mechanical Travel   | ..... Length ±0.5 mm          |
| Operating Force     | ..... 30 gf to 250 gf         |
| Center Detent Force | ..... 20 gf to 200 gf         |
| Stop Strength       | ..... 5 kgf min.              |
| Shaft Axial Force   | ..... 5 kgf min.              |
| Shaft Wobble        | ..... 2(2 x L/20) mm p-p max. |
| Soldering Condition |                               |
| Manual              | ..... 300 °C ±5 °C for 3 sec. |
| Wave                | ..... 260 °C ±5 °C for 5 sec. |
| Wash                | ..... Not recommended         |

### Product Dimensions

#### 20 mm Length of Travel




#### Mounting Hole Detail



| Lever Length   |
|----------------|
| 10.0<br>(.394) |
| 15.0<br>(.591) |
| 19.0<br>(.748) |


DIMENSIONS:  $\frac{\text{MM}}{\text{(INCHES)}}$



### Standard Resistance Table

| Resistance (Ohms) | Resistance Code |
|-------------------|-----------------|
| 1,000             | 102             |
| 2,000             | 202             |
| 5,000             | 502             |
| 10,000            | 103             |
| 20,000            | 203             |
| 50,000            | 503             |
| 100,000           | 104             |
| 200,000           | 204             |
| 500,000           | 504             |
| 1,000,000         | 105             |

### Schematic



## Applications


- Mixing consoles
- Drum machines
- Keyboards and synthesizers
- Equalizers

# PTL Series Slide Potentiometer w/LED


**BOURNS®**

## Product Dimensions


### 30 mm Length of Travel




### Mounting Hole Detail



### 45 mm Length of Travel



### Mounting Hole Detail




# PTL Series Slide Potentiometer w/LED


**BOURNS®**

## Product Dimensions




### 60 mm Length of Travel



### Mounting Hole Detail



## Tapers



Specifications are subject to change without notice.  
Customers should verify actual device performance in their specific applications.

# PTL Series Slide Potentiometer w/LED

**BOURNS®**

## LED Characteristics


| Emitter Color | Item                     | Symbol          | Test Conditions       | Min. | Typ.  | Max. | Unit |
|---------------|--------------------------|-----------------|-----------------------|------|-------|------|------|
| Red           | Forward Voltage          | $V_F$           | $I_F = 20 \text{ mA}$ |      | 2.1   | 2.5  | V    |
|               | Luminous Intensity       | $I_V$           |                       | 0.3  | 0.6   |      | mcd  |
|               | Peak Emission Wavelength | $\lambda_p$     |                       |      | 660   |      | nm   |
|               | Dominant Wavelength      | $\lambda_d$     |                       |      | 643   |      | nm   |
|               | Spectral Line Half Width | $\Delta\lambda$ |                       |      | 20    |      | nm   |
| Orange        | Forward Voltage          | $V_F$           | $I_F = 20 \text{ mA}$ |      | 2.2   | 2.5  | V    |
|               | Luminous Intensity       | $I_V$           |                       | 1.5  | 3.0   |      | mcd  |
|               | Peak Emission Wavelength | $\lambda_p$     |                       |      | 610   |      | nm   |
|               | Dominant Wavelength      | $\lambda_d$     |                       |      | 605   |      | nm   |
|               | Spectral Line Half Width | $\Delta\lambda$ |                       |      | 35    |      | nm   |
| Green         | Forward Voltage          | $V_F$           | $I_F = 20 \text{ mA}$ |      | 2.1   | 2.5  | V    |
|               | Luminous Intensity       | $I_V$           |                       | 0.6  | 1.2   |      | mcd  |
|               | Peak Emission Wavelength | $\lambda_p$     |                       |      | 530   |      | nm   |
|               | Dominant Wavelength      | $\lambda_d$     |                       |      | 35    |      | nm   |
|               | Spectral Line Half Width | $\Delta\lambda$ |                       |      | 160   |      | nm   |
| Amber         | Forward Voltage          | $V_F$           | $I_F = 20 \text{ mA}$ |      | 2.1   | 2.6  | V    |
|               | Luminous Intensity       | $I_V$           |                       |      | 5.0   |      | mcd  |
|               | Peak Emission Wavelength | $\lambda_p$     |                       |      | 585   |      | nm   |
|               | Dominant Wavelength      | $\lambda_d$     |                       | 582  | –     | 595  | nm   |
|               | Spectral Line Half Width | $\Delta\lambda$ |                       |      | 35    |      | nm   |
| White         | Forward Voltage          | $V_F$           | $I_F = 20 \text{ mA}$ |      | 3.5   | 4    | V    |
|               | Luminous Intensity       | $I_V$           |                       |      | 300.0 |      | mcd  |
|               | Peak Emission Wavelength | $\lambda_p$     |                       |      | 520   |      | nm   |
|               | Dominant Wavelength      | $\lambda_d$     |                       | 460  | –     | 470  | nm   |
|               | Spectral Line Half Width | $\Delta\lambda$ |                       |      | 35    |      | nm   |

## How To Order

**PTL 30 - 10 R 0 - 103 B2**

Model Number \_\_\_\_\_  
 Designator \_\_\_\_\_  
 PTL = Slide Potentiometer w/LED  
 Length of Travel \_\_\_\_\_  
 20 = 20 mm 45 = 45 mm  
 30 = 30 mm 60 = 60 mm  
 Lever Length \_\_\_\_\_  
 10 = 10 mm  
 15 = 15 mm  
 19 = 19 mm  
 LED Color \_\_\_\_\_  
 R = Red A = Amber  
 O = Orange W = White  
 G = Green  
 Detent Option \_\_\_\_\_  
 0 = No Detent  
 1 = Center Detent  
 Resistance Code \_\_\_\_\_  
 (See Standard Resistance Table)  
 Resistance Taper (See Taper Charts) \_\_\_\_\_  
 Taper Series followed by Curve Number

## Circuit



REV. 09/11

Specifications are subject to change without notice.  
 Customers should verify actual device performance in their specific applications.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Bourns:

[PTL45-15R0-202B2](#) [PTL60-10R0-203B2](#) [PTL30-10G1-204B2](#) [PTL20-10G1-204B2](#) [PTL60-10O0-105B2](#) [PTL60-10O1-105B2](#) [PTL20-10G0-204B2](#) [PTL30-10G0-204B2](#) [PTL45-15R1-202B2](#) [PTL60-10R1-203B2](#) [PTL45-19O1-105B2](#) [PTL20-19G1-102B2](#) [PTL30-15O1-104B2](#) [PTL20-15O1-104B2](#) [PTL30-19G1-102B2](#) [PTL60-15G0-202B2](#) [PTL60-15G1-202B2](#) [PTL45-19O0-105B2](#) [PTL20-15O0-104B2](#) [PTL30-19G0-102B2](#) [PTL20-19G0-102B2](#) [PTL30-15O0-104B2](#) [PTL30-15R1-103B2](#) [PTL30-15G0-104B2](#) [PTL20-15R1-103B2](#) [PTL20-15G0-104B2](#) [PTL45-10R0-105B2](#) [PTL20-10O0-204B2](#) [PTL30-10O0-204B2](#) [PTL45-19G0-105B2](#) [PTL20-15R0-103B2](#) [PTL30-10O1-204B2](#) [PTL45-19G1-105B2](#) [PTL20-10O1-204B2](#) [PTL30-15R0-103B2](#) [PTL30-15G1-104B2](#) [PTL20-15G1-104B2](#) [PTL45-10R1-105B2](#) [PTL20-19R0-104B2](#) [PTL60-15O1-202B2](#) [PTL30-19R0-104B2](#) [PTL30-19O0-102B2](#) [PTL20-19O0-102B2](#) [PTL60-10G0-105B2](#) [PTL20-19O1-102B2](#) [PTL60-10G1-105B2](#) [PTL30-19O1-102B2](#) [PTL60-15O0-202B2](#) [PTL20-19R1-104B2](#) [PTL30-19R1-104B2](#) [PTL20-15R0-202B2](#) [PTL20-19R0-502B2](#) [PTL30-10R1-503B2](#) [PTL20-10R1-503B2](#) [PTL30-15R0-202B2](#) [PTL30-19R0-502B2](#) [PTL45-19R0-203B2](#) [PTL20-10R0-503B2](#) [PTL30-10R0-503B2](#) [PTL45-19R1-203B2](#) [PTL20-15R1-202B2](#) [PTL20-19R1-502B2](#) [PTL30-15R1-202B2](#) [PTL30-19R1-502B2](#) [PTL45-19G1-503B2](#) [PTL60-19G0-203B2](#) [PTL30-15G1-502B2](#) [PTL20-15G1-502B2](#) [PTL45-10O1-103B2](#) [PTL45-10G0-504B2](#) [PTL45-10G1-504B2](#) [PTL45-19G0-503B2](#) [PTL20-15G0-502B2](#) [PTL45-10O0-103B2](#) [PTL30-15G0-502B2](#) [PTL60-19G1-203B2](#) [PTL45-10G0-103B2](#) [PTL45-10G1-103B2](#) [PTL30-15R0-504B2](#) [PTL45-10O1-504B2](#) [PTL20-15R0-504B2](#) [PTL45-19O0-503B2](#) [PTL20-15O0-502B2](#) [PTL30-10R0-102B2](#) [PTL20-10R0-102B2](#) [PTL30-15O0-502B2](#) [PTL60-19O1-203B2](#) [PTL20-10R1-102B2](#) [PTL30-15O1-502B2](#) [PTL20-15O1-502B2](#) [PTL30-10R1-102B2](#) [PTL45-10O0-504B2](#) [PTL30-15R1-504B2](#) [PTL60-19O0-203B2](#) [PTL20-15R1-504B2](#) [PTL45-19O1-503B2](#) [PTL45-10G1-203B2](#) [PTL60-15O1-102B2](#) [PTL60-15G0-503B2](#) [PTL45-10G0-203B2](#)