






LOC		DIST		REVISIONS				
P	LYR	DESCRIPTION			DATE	DWN	APVD	
	A	REVISED PER ECO-12-011334			28SEP2012	KH	JE	



- 2 PHOSPHOR BRONZE
- 3 LCP, UL94V-0
- 4 FINISH:
CONTACT MATING AREA MEETS THE PERFORMANCE REQUIREMENTS OF
TE CONNECTIVITY PRODUCT SPECIFICATION 108-1957; BASED ON
TELCORDIA GR-1217-CORE; APPLICATIONS IN UNCONTROLLED ENVIRONMENTS.
COMPLIANT PIN AREA: 0.5µm MIN MATTE TIN OVER BASE PLATING.
- 5 CONNECTOR MARKED WITH PART NUMBER AND DATE CODE
- 6 REFERENCE APPLICATION SPEC 114-13020 FOR RECOMMENDED
PLATED THRU HOLE DIAMETER AND PLATING THICKNESS.
- 7 APPLICATION SEATING HEIGHT TO PRINTED CIRCUIT BOARD
- 8 DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER
- 9 CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT
TECHNICAL REFERENCE: GR-1217-CORE, ISSUE 1, NOVEMBER 1995



RECOMMENDED
PRINTED CIRCUIT BOARD
LAYOUT
COMPONENT SIDE OF PRINTED CIRCUIT BOARD



5.50	14.50	9.7	5120679-2
5.50	13.00	8.2	5120679-1
N	M	L	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN B. CARBO	07DEC04	TE Connectivity			
DIMENSIONS:		CHK R. PATTERSON	07DEC04				
mm		APVD R. PATTERSON	07DEC04	NAME			
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC			
		0 PLC ±		APPLICATION SPEC			
		1 PLC ±		SIZE			
		2 PLC ±0.13		CAGE CODE			
MATERIAL		3 PLC ±0.05		DRAWING NO		RESTRICTED TO	
HOUSING: 3		4 PLC ±		WEIGHT		A 1	
CONTACTS: 2		FINISH		00779		5120679	
SIGNAL CONTACT: 4		Customer Drawing		SCALE		5:1	
				SHEET		1 OF 1	
				REV		A	