


⊕ Ø 0.05 (S) X Y
ALL PLATED THRU HOLES



RECOMMENDED PC BOARD
LAYOUT, BACKPLANE,
COMPONENT SIDE SHOWN
SCALE 4:1

- ④ REFERENCE APPLICATION SPEC 114-13059 FOR RECOMMENDED PLATED THRU HOLE DIAMETER AND PLATING THICKNESSES.
- ⑤ MATERIAL: CONTACT AND SHIELD - PHOSPHOR BRONZE HOUSING - GLASS FILLED POLYESTER. UL 94V-0.
- ⑥ FINISH: SIGNAL AND GROUND CONTACTS: MATING AREA: MEETS THE PERFORMANCE REQUIREMENTS OF PRODUCT SPECIFICATION 108-2055; BASED ON TELCORDIA GR-1217-CORE, APPLICATIONS IN UNCONTROLLED ENVIRONMENTS
COMPLIANT PIN AREA: 0.5µm MIN BRIGHT TIN-LEAD OVER BASE PLATING
- ⑦ CONNECTOR MARKED WITH PART NUMBER AND DATE CODE.
- ⑧ DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- ⑨ THE FOUR GROUNDS IN EACH COLUMN ARE COMMONED.
- ⑩ CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT. TECHNICAL REFERENCE: GR-1217-CORE, ISSUE I, NOVEMBER 1995.
- ⑪ OBSOLETE

3.80	8	1469002-2
5.30		1469002-1
DIM M		PART NUMBER
15FEB2001		
K. KOEGEL		
16AUG2007		
R. PATTERSON		
02MAY01		
N. SCHROLL		
PRODUCT SPEC		
APPLICATION SPEC		
MATERIAL		
FINISH		
WEIGHT		
A 100779	1469002	
Customer Drawing		
3:1		
1		
REV F		