





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	Z1	REVISED PER ECO-11-005150	21MAR2011	RK	HMR
	Z2	NEW DRAWING CREATED IN CREO	26JUNE2014	JBH	BRUN
	Z3	NOTE 8 MODIFIED	18NOV2015	MAH.	BRUN
	Z4	TOLERANCES ADDED AT SECTION A-A AND B-B	21JAN2016	MAH.	BRUN

- NOTES:
- 1 UNDERCOATING: 0.8µm NICKEL OVERALL
CONTACT AREA: 0.8µm GOLD
CRIMP AREA: GOLDFLASH
 - 2 UNDERCOATING: 0.8µm NICKEL OVERALL
CONTACT AREA: 1.25µm GOLD
CRIMP AREA: GOLDFLASH
 - 3 SUITABLE FOR 0.64x0.64 POST
 - 6 UNDERCOATING: 0.8µm NICKEL OVERALL
CONTACT AREA: 0.4µm GOLD
CRIMP AREA: GOLDFLASH
 - 7 ADVANCED PROD. NRS. FOR DIN 41612 PART 5 SPEC
 - 8 PLATING: 2.0µm TIN OVER MIN. 0.5µm Ni OVERALL
 - 9 REVERSE REELED FOR USE WITH MINI APPLICATOR.
 - 10 STANDARD REELED FOR USE WITH STANDARD APPLICATOR.
 - 11 TRADE MARK.

WIRE RANGE: 20-24 (26) AWG
INSULATION RANGE: 1.40 MAX DIA.

166722-1	1	PHOSPHORBRONZE	1-166500-2	10	Z
166722-6	8		1-166500-1	10	Z
166722-6	8		166500-9	9	Z
166722-4	6		166500-7	9	W
166722-2	2		166500-4	9	Z
166722-1	1		166500-2	9	Z
LOOSE PIECE NUMBER	PLATING	MATERIAL	STRIPNUMBER	REV	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.Pfeilschifter 18JUL2000	 TE Connectivity		
		CHK V.Huhn 18JUL2000			
DIMENSIONS: mm		APVD -	NAME STANDARD TANDEM SPRING RECEPTACLE		
		PRODUCT SPEC -			
		APPLICATION SPEC -	SIZE A3		
MATERIAL -		WEIGHT -			
		CUSTOMER DRAWING	SCALE 10:1	SHEET 1 OF 1	REV Z4