



Circuit Board Indicators	Circuit Board Indicators - Through Hole Indicators	
Panel Mount Indicators	P/N# 5680714444F	3 mm Lens
Solid State Lighting	Description	3 mm Backlighting Quad-Level CBI Y/G-Y/G-Y/G-Y/G
Traffic Signals	Package Options	5 Pieces Per Bag
Vehicle Lighting	Product Type	Through Hole Indicators
Rail	Sub Product Type	with Quad Level Housing
Obstruction Lighting	Configuration	3 mm Lens
Hazardous Area Lighting	Viewing	Right Angle
Heliport Lighting	Viewing Angle	80
	Test Current (mA)	10mA

Absolute Maximum Ratings (Ta = 25 °)	
Solder Temp	260Â° for 5 sec
Operating Temp	-55 to +100° C
Storage Temp	-55 to +100° C

[how to purchase](#)

[sales contacts](#)
[stock check](#)

[search](#)

[Product Line Search](#)

Please select a Product Line to search.
Circuit Board Indicators

find

Part # / Text Search

Part No.:
Text Search:
search

[quick links](#)

[Dialight Corporate Video](#)

Presentation at LightFair 2007 - "Presentation of White LEDs" : by Ian Ferguson, Georgia Tech in conjunction with Dialight Corp. [View PDF File](#)

Application Notes
FAQs

Dialight Ltd (UK)
Dialight Garufo
Dialight BLP
LumiDrives



RoHS /pB Free
[view PDF](#)

Distributor Stock Check

Check stock with our distributors now.

5680714444F

check stock

Operating Characteristics	
LED Position	Found in position(s): 1-4
Color	Yellow / Green
Lamp Type	Bi-Color / Bi-Color
LED Type	
Intensity Min (mcd)	2.5 / 2.5
Intensity Typ (mcd)	4.3 / 6.3
Intensity Max (mcd)	
Fwd Voltage Min	
Fwd Voltage Typ	
Fwd Voltage Max	
Dom Wavelength Min (nm)	587 / 569
Dom Wavelength Typ (nm)	
Dom Wavelength Max (nm)	
Power Dissipation Max (mW)	60 / 100
Backlighting	
Pitch Between Vertical	
Pitch Between Horizontal	
Lum Intensity Min	
Lum Intensity Typ	
Lum Intensity Max	