





RECOMMENDED P.C. BOARD LAYOUT

- △ BODY-MATL: BRASS PER MIL-C-50.
FINISH: PLATED GOLD .000030 THK PER MIL-G-45204 FOR A LENGTH OF .200 MIN
FROM MATING END, .000100 MIN TIN-LEAD PER MIL-T-10727 IN WIRE BARREL
AREA, BOTH OVER NICKEL .000050 THK PER QQ-N-290.
SPRING-MATL: STAINLESS STEEL PER QQ-S-766.
POST-MATL: BRASS PER ASTM-B-134.
FINISH: PLATED MATTE TIN-LEAD PER MIL-T-10727 OVER NICKEL .000050 THK
PER QQ-N-290.
- △ BODY-MATL: BRASS PER MIL-C-50.
FINISH: PLATED GOLD .000030 THK PER MIL-G-45204 FOR A LENGTH OF .200 MIN
FROM MATING END, .000100 MIN TIN PER MIL-T-10727 IN WIRE BARREL AREA,
BOTH OVER NICKEL .000050 THK PER QQ-N-290.
SPRING-MATL: STAINLESS STEEL PER QQ-S-766.
POST-MATL: BRASS PER ASTM-B-134.
FINISH: PLATED MATTE TIN PER MIL-T-10727 OVER NICKEL .000050 THK PER QQ-N-290.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. HOFFECKER 5-12-86	tyco Electronics	Tyco Electronics Corporation Harriburg, Pa 17105-3608	
DIMENSIONS: INCHES		CHK L. LAWVER 5-12-86		NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD —	PRODUCT SPEC		
0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .010 4 PLC ± — ANGLES ± —		APPLICATION SPEC		SIZE A1	
MATERIAL SEE CALLOUTS		FINISH SEE CALLOUTS	WEIGHT —	CAGE CODE 00779	
CUSTOMER DRAWING			DRAWING NO 213289		
SCALE 2:1			SHEET 1 OF 1		
REV L			RESTRICTED TO —		

△	213289-2
△	213289-1
CONTACT FINISH	PART NUMBER