

Equipment Wires

pro-POWER



Specification:

Primary insulation material : PVC

Part Number Table

Colour	Conductor Make-up	Reel Length (mtrs)	Conductor Cross-sectional Area (mm ²)	Def Stan 61-12 Part 6	Current Rating (A)	Primary Insulation Thickness (mm)	Conductor Material	Voltage Rating (V AC)	Ex-ternal Dia. (mm)	Part Number
Black	10/0.1mm	100	0.078	Type 1 : -15°C to +85°C Type 2 : -15°C to +85°C Type 3 : -20°C to +85°C	0.5	0.3	Tinned Copper	1,000	1.05	MC10/0.1 TYPE 2 BLACK 100M
Brown										MC10/0.1 TYPE 2 BROWN 100M
Red										MC10/0.1 TYPE 2 RED 100M
Orange										MC10/0.1 TYPE 2 ORANGE 100M
Yellow										MC10/0.1 TYPE 2 YELLOW 100M
Green										MC10/0.1 TYPE 2 GRN 100M
Blue										MC10/0.1 TYPE 2 BLUE 100M
Pink										MC10/0.1 TYPE 2 PINK 100M
Grey										MC10/0.1 TYPE 2 GREY 100M
White										MC10/0.1 TYPE 2 WHT 100M
Violet										MC10/0.1 TYPE 2 VIOLET 100M
Red	7/0.2mm	500	0.22		1.4				1.2	MC10/0.1 TYPE 2 RED 500M
Elow										MC10/0.1 TYPE 2 YEL 500M
Green										MC10/0.1 TYPE 2 GRN 500M
Blue										MC10/0.1 TYPE 2 BLUE 500M
White										MC10/0.1 TYPE 2 WHT 500M
Black										MC7/0.2 TYPE 2 BLK 500M

Equipment Wires

pro-POWER

Colour	Conductor Make-up	Reel Length (mtrs)	Conductor Cross-sectional Area (mm ²)	Def Stan 61-12 Part 6	Current Rating (A)	Primary Insulation Thickness (mm)	Conductor Material	Voltage Rating (V AC)	Ex-ternal Dia. (mm)	Part Number
Brown	7/0.2mm	500	0.22	Type 1 : -15°C to +85°C Type 2 : -15°C to +85°C Type 3 : -20°C to +85°C	1.4	0.3	Tinned Copper	1,000	1.2	MC7/0.2 TYPE 2 BRN 500M
Red										MC7/0.2 TYPE 2 RED 500M
Orange										MC7/0.2 TYPE 2 ORANGE 500M
Yellow										MC7/0.2 TYPE 2 YEL 500M
Green										MC7/0.2 TYPE 2 GRN 500M
Blue										MC7/0.2 TYPE 2 BLUE 500M
Violet										MC7/0.2 TYPE 2 VIOLET 500M
Grey										MC7/0.2 TYPE 2 GREY 500M
White										MC7/0.2 TYPE 2 WHT 500M
Pink										MC7/0.2 TYPE 2 PINK 500M
Black to Pink		MCREEL KIT7/0.2 100M								
Red/ Black		MC6A-7/0.2T2-RDBK-100								
Red/ Brown		MC6A-7/0.2T2-RDBN-100								
Red/ Green		MC6A-7/0.2T2-RDGN-100								
Red/Blue		MC6A-7/0.2T2-RDBE-100								
Orange/ Black		MC6A-7/0.2T2-OEBK-100								
Orange/ Red		MC6A-7/0.2T2-OERD-100								
Yellow/ Black		MC6A-7/0.2T2-YWBK-100								
Yellow/ Red		MC6A-7/0.2T2-YWRD-100								
Yellow/ Green		MC6A-7/0.2T2-YWGN-100								
Green/ Red		MC6A-7/0.2T2-GNRD-100								

Equipment Wires

pro-POWER

Colour	Conductor Make-up	Reel Length (mtrs)	Conductor Cross-sectional Area (mm ²)	Def Stan 61-12 Part 6	Current Rating (A)	Primary Insulation Thickness (mm)	Conductor Material	Voltage Rating (V AC)	Ex-ternal Dia. (mm)	Part Number
Violet/ Red	7/0.2mm	100	0.22		1.4	0.3	Tinned Copper		1.2	MC6A-7/0.2T2-VTRD-100
Grey/ Black										MC6A-7/0.2T2-GYBK-100
Grey/ Blue										MC6A-7/0.2T2-GYBE-100
White/ Black										MC6A-7/0.2T2-WEBK-100
White/ Red										MC6A-7/0.2T2-WERD-100
Pink/ Black										MC6A-7/0.2T2-PKBK-100
Green/ Yellow										MC6A-7/0.2T2-GNYW-100
Purple/ Red						-				7/0.20 PUR/RED
Green/ Yellow		500				-	-			7/0.20 GRN/ YELL
Black	16/02mm	100	0.5	Type 1 : -15°C to +85°C Type 2 : -15°C to +85°C Type 3 : -20°C to +85°C	3	0.3	Tinned Copper	1,000	1.6	MC16/0.2 TYPE 2 BLK 100M
Brown										MC16/0.2 TYPE 2 BRN 100M
Red										MC16/0.2 TYPE 2 RED 100M
Orange										MC16/0.2 TYPE 2 ORNG 100M
Yellow										MC16/0.2 TYPE 2 YEL 100M
Green										MC16/0.2 TYPE 2 GRN 100M
Blue										MC16/0.2 TYPE 2 BLUE 100M
Violet										MC16/0.2 TYPE 2 VIOLET 100M
Grey										MC16/0.2 TYPE 2 GREY 100M
White										MC16/0.2 TYPE 2 WHT 100M
Pink										MC16/0.2 TYPE 2 PINK 100M
Black		500								MC16/0.2 TYPE 2 BLK 500M

Equipment Wires

pro-POWER

Colour	Conductor Make-up	Reel Length (mtrs)	Conductor Cross-sectional Area (mm ²)	Def Stan 61-12 Part 6	Current Rating (A)	Primary Insulation Thickness (mm)	Conductor Material	Voltage Rating (V AC)	Ex-ternal Dia. (mm)	Part Number
Brown	16/0.2mm	500	0.5	Type 1 : -15°C to +85°C Type 2 : -15°C to +85°C Type 3 : -20°C to +85°C	3	0.3	Tinned Copper	1,000	1.6	MC16/0.2 TYPE 2 BRN 500M
Red										MC16/0.2 TYPE 2 RED 500M
Orange										MC16/0.2 TYPE 2 ORNG 500M
Yellow										MC16/0.2 TYPE 2 YEL 500M
Green										MC16/0.2 TYPE 2 GRN 500M
Blue										MC16/0.2 TYPE 2 BLUE 500M
Violet										MC16/0.2 TYPE 2 VIOLET 500M
Grey										MC16/0.2 TYPE 2 GREY 500M
White										MC16/0.2 TYPE 2 WHT 500M
Pink										MC16/0.2 TYPE 2 PINK 500M
Black toPink (11Reels)		6A-16/0.2T2-BX-1F								
Red/Black		MC6A-16/0.2T2-RDBK-100								
Red/Brown		MC6A-16/0.2T2-RD/BN-100								
Red/Green		MC6A-16/0.2T2-RDGN-100								
Red/Blue		MC6A-16/0.2T2-RDBE-100								
Orange/Black		MC6A-16/0.2T2-OEBK-100								
Orange/Red		MC6A-16/0.2T2-OERD-100								
Yellow/Black		MC6A-16/0.2T2-YWBK-100								
Yellow/Red		MC6A-16/0.2T2-YWRD-100								
Yellow/Green		MC6A-16/0.2T2-YWGN-100								
Green/Red		MC6A-16/0.2T2-GNRD-100								

Equipment Wires

pro-POWER

Colour	Conductor Make-up	Reel Length (mtrs)	Conductor Cross-sectional Area (mm ²)	Def Stan 61-12 Part 6	Current Rating (A)	Primary Insulation Thickness (mm)	Conductor Material	Voltage Rating (V AC)	Ex-ternal Dia. (mm)	Part Number
Violet/ Red	16/0.2mm	100	0.5	Type 1 : -15°C to +85°C Type 2 : -15°C to +85°C Type 3 : -20°C to +85°C	3	0.3	Tinned Copper	1,000	1.6	MC6A-16/0.2T2-VTRD-100
Grey/ Black										MC6A-16/0.2T2-GBYK-100
Grey/ Blue										MC6A-16/0.2T2-GYBE-100
White/ Black										MC6A-16/0.2T2-WEBK-100
White/ Red										MC6A-16/0.2T2-WERD-100
Pink/ Black										MC6A-16/0.2T2-PKBK-100
Green/ Yellow										MC6A-16/0.2T2-GNYW-100
Purple/ Red										16/0.20 PUR/ RED 100M
Green/ Yellow		500			-	-	16/0.20 GRN/ YELL 500M			
Black		100			0.6	Tinned Copper	1,500	2.13	MC6A-16/0.2T3-BK-100	
Brown							1,500		MC6A-16/0.2T3-BN-100	
Red							1,500		MC6A-16/0.2T3-RD-100	
Orange							1,500		MC6A-16/0.2T3-OE-100	
Yellow							1,500		MC6A-16/0.2T3-YW-100	
Green							1,500		MC6A-16/0.2T3-GN-100	
Blue							1,500		MC6A-16/0.2T3-BE-100	
Violet							1,500		MC6A-16/0.2T3-VT-100	
Grey							1,500		MC6A-16/0.2T3-GY-100	
White							1,500		MC6A-16/0.2T3-WE-100	
Pink							1,500		MC6A-16/0.2T3-PK-100	
Green/ Yellow	1,500		MC6A-16/0.2T3-GNYW-100							

Equipment Wires

pro-POWER

Colour	Conductor Make-up	Reel Length (mtrs)	Conductor Cross-sectional Area (mm ²)	Def Stan 61-12 Part 6	Current Rating (A)	Primary Insulation Thickness (mm)	Conductor Material	Voltage Rating (V AC)	Ex-ternal Dia. (mm)	Part Number
Black	24/0.2mm	100	0.75	Type 1 : -15°C to +85°C Type 2 : -15°C to +85°C Type 3 : -20°C to +85°C	4.5	0.45	Tinned Copper	1,000	2.5	MC6A-24/0.2T2-BK-100
Brown										MC6A-24/0.2T2-BM-100
Red										MC6A-24/0.2T2-RD-100
Orange										MC6A-24/0.2T2-OE-100
Yellow										MC6A-24/0.2T2-YW-100
Green										MC6A-24/0.2T2-GN-100
Blue										MC6A-24/0.2T2-BE-100
White										MC6A-24/0.2T2-WE-100
Pink										MC6A-24/0.2T2-PK-100
Green/Yellow										MC6A-24/0.2T2-GNYW-100
Yellow/Green										24/0.20 YELL/GRN
Black	24/0.2mm	500	0.75	Type 1 : -15°C to +85°C Type 2 : -15°C to +85°C Type 3 : -20°C to +85°C	4.5	0.45	Tinned Copper	1,000	2.05	MC6A-24/0.2T2-BK-500
Red										MC6A-24/0.2T2-RD-500
Orange										MC6A-24/0.2T2-OE-500
Blue										MC6A-24/0.2T2-BE-500
Grey										MC6A-24/0.2T2-GY-500
White										MC6A-24/0.2T2-WE-500
Pink										24/0.20 PINK 500M
Violet										24/0.20 VIOLET 500M
Black										MC6A-24/0.2T3-BK-100
Brown										MC6A-24/0.2T3-BN-100

Equipment Wires

pro-POWER

Colour	Conductor Make-up	Reel Length (mtrs)	Conductor Cross-sectional Area (mm ²)	Def Stan 61-12 Part 6	Current Rating (A)	Primary Insulation Thickness (mm)	Conductor Material	Voltage Rating (V AC)	Ex-ternal Dia. (mm)	Part Number				
Red	24/0.2mm	100	0.75	Type 1 : -15°C to +85°C Type 2 : -15°C to +85°C Type 3 : -20°C to +85°C	4.5	0.6	Tinned Copper	1,500	2.34	MC6A-24/0.2T3-RD-100				
Orange										MC6A-24/0.2T3-OE-100				
Yellow										MC6A-24/0.2T3-YW-100				
Green										MC6A-24/0.2T3-GN-100				
Blue										MC6A-24/0.2T3-BE-100				
Violet										MC6A-24/0.2T3-VT-100				
Grey		MC6A-24/0.2T3-GY-100												
White		MC6A-24/0.2T3-WE-100												
Pink		MC6A-24/0.2T3-YW-100F												
Green/Yellow		MC6A-24/0.2T3-GNYW-100												
Black		MC6A-24/0.2T3-BK-500												
Red		MC6A-24/0.2T3-RD-500												
Yellow	MC6A-24/0.2T3-YW-500													
White	MC6A-24/0.2T3-WE-500													
Black	32/0.2mm	100			1				6				2.52	MC6A-32/0.2T3-BK-100M
Brown														MC6A-32/0.2T3-BN-100
Red														MC6A-32/0.2T3-RD-100
Orange														MC6A-32/0.2T3-OE-100
Yellow			MC6A-32/0.2T3-YW-100											
Green			MC6A-32/0.2T3-GN-100											
Blue			MC6A-32/0.2T3-BE-100											

Equipment Wires

pro-POWER

Colour	Conductor Make-up	Reel Length (mtrs)	Conductor Cross-sectional Area (mm ²)	Def Stan 61-12 Part 6	Current Rating (A)	Primary Insulation Thickness (mm)	Conductor Material	Voltage Rating (V AC)	Ex-ternal Dia. (mm)	Part Number
Violet	32/0.2mm	100	1	Type 1 : -15°C to +85°C Type 2 : -15°C to +85°C Type 3 : -20°C to +85°C	6	0.6	Tinned Copper	1,500	2.52	MC6A-32/0.2T3-VT-100
Grey										MC6A-32/0.2T3-GY-100
White										MC6A-32/0.2T3-WE-100
Pink										MC6A-32/0.2T3-PK-100
Green/ Yellow										MC6A-32/0.2T3-GNYW-100
Yellow/ Green										32/0.20 YEL-LOW/GREEN
Black		500				0.6				MC6A-32/0.2T3-BK-500
Red										MC6A-32/0.2T3-RD-500
White										MC6A-32/0.2T3-WE-500
Blue										32/0.20 BLUE 500M
Brown										32/0.20 BROWN 500M
Pink										32/0.20 PINK 500M
Yellow						32/0.20 YELLOW 500M				
Yellow/ Green						MC6A-32/0.2T3-GNYW-500				
Black	63/0.2mm	100	2	11	0.6	3	MC6A-63/0.2T3-BK-100			
Red						3	MC6A-63/0.2T3-RD-100			

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of the Group. © Premier Farnell plc 2012.

www.element14.com
www.farnell.com
www.newark.com
www.cpc.co.uk

pro-POWER